

KM 2010
Gas hob
with 4 burners




- Simple controls -single-handed operation via rotary dial control
- Professional design – 650 mm wide stainless steel trough
- Versatile – 4 burners
- Extremely safe – GasStop function
- Easy cleaning – dishwasher-safe ComfortClean pot rests

EAN: 4002514414041 / Material number: 07113300 / Old Material Number: 26201050GB

| | |
|---|-------------------|
| Heating type | |
| Heating type | Gas |
| Construction type | |
| Independent of cooker | • |
| Design | |
| Cast iron pot rests (matt black enamelled) | • |
| Stainless steel trough | • |
| Cooking zone details | |
| Number of cooking zones | 4 |
| Gas burner power rating | |
| Small burner in kW | 1,00 |
| Medium burner in kW | 1,75 |
| Large burner in kW | 2,60 |
| 1st cooking zone/cooking area | |
| Position | front left |
| Type | High-speed burner |
| 2nd cooking zone/cooking area | |
| Position | rear left |
| Type | Economy burner |
| 3rd cooking zone/cooking area | |
| Position | rear right |
| Type | Standard burner |
| 4th cooking zone/cooking area | |
| Position | front right |
| Type | Standard burner |
| User convenience | |
| Operation via knobs | • |
| Electronic ignition with single-hand operation | • |
| Cleaning and care | |
| Dishwasher-proof pot rests | • |
| PerfectClean burner | • |
| Safety | |
| GasStop | • |
| Technical data | |
| Dimensions (H x W x D) in mm | 90 x 650 x 520 |
| Dimensions in mm (width) | 650 |
| Dimensions in mm (height) | 90 |
| Dimensions in mm (depth) | 520 |
| Cutout dimensions in mm (width) with surface-mounted installation | 560 |
| Cutout dimensions in mm (depth) with surface-mounted installation | 480 |
| Weight in kg | 13 |
| Total rated load in kW | 7,10 |
| Length of supply lead in m | 1,4 |
| Voltage in V | 220-240 |
| Frequency in Hz | 50-60 |
| Accessories included | |
| Mains cable | No |

KM 2010
Gas hob
with 4 burners



KM2010G (Installation drawing)

1. Front, 2. Building-in depth, 3. Gas connection R 1/2 - ISO 7-1 (DIN EN 10226), 4. Mains connection box with mains connection cable, L = 2000 mm