

XKM RS 232

Communication module

With serial interface RS 232 for communication of commercial laundry machines.

EAN: 4002514610283 / Material number: 07467040 / Old Material Number: 50501001D



- For integration in a communication shaft

| Product category | |
|----------------------------|---|
| Washing machines | • |
| Tumble dryers | • |
| Machine/accessory category | |
| PT 5186 | • |
| PT 7186 | • |
| PT 7188 | • |
| PT 8203 | • |
| PT 8251 | • |
| PT 8251 COP | • |
| PT 8253 | • |
| PT 8257 | • |
| PT 8257 WP | • |
| PT 8301 | • |
| PT 8301 COP | • |
| PT 8303 | • |
| PT 8331 | • |
| PT 8331 COP | • |
| PT 8333 | • |
| PT 8333 HW | • |
| PT 8337 | • |
| PT 8337 HW | • |
| PT 8337 WP | • |
| PT 8401 | • |
| PT 8403 | • |
| PT 8403 HW | • |
| PT 8407 | • |
| PT 8407 HW | • |
| PT 8503 | • |
| PT 8503 HW | • |
| PT 8507 | • |
| PT 8507 HW | • |
| PT 8803 | • |
| PT 8803 HW | • |
| PT 8807 | • |
| PT 8807 HW | • |
| PW 5082 | • |
| PW 5105 Vario | • |
| PW 6080 | • |
| PW 6088 | • |
| PW 6107 | • |
| PW 6137 | • |
| PW 5136 | • |
| PW 6163 | • |
| PW 6167 | • |
| PW 6207 | • |
| PW 6241 | • |
| PW 6243 | • |
| PW 6321 | • |
| PW 6323 | • |

XKM RS 232

Communication module

With serial interface RS 232 for communication of commercial laundry machines.



EAN: 4002514610283 / Material number: 07467040 / Old Material Number: 50501001D

PWT 6089

Product category

Payment system

Dispenser system

Process documentation/operating documentation/
communication

Payment system accessories

Other accessories

Product properties

Electrical connection

OHNE

Dimensions and weight

External dimensions, net height in mm

50

External dimensions, net width in mm

220

External dimensions, net depth in mm

180

External dimensions, gross height in mm

58

External dimensions, gross width in mm

225

External dimensions, gross depth in mm

185

Net weight [kg]

0,15

Gross weight in kg

0,35

Standards, test certificates and symbols

CE