

## PG 8056 U [MK SPEEDplus]

Built-under fresh-water dishwasher

With baskets for hotels, restaurants and catering companies.



- Max. cleaning performance\*: 456 plates/h or 24 baskets/h
- Versatile processing of two wire or plastic baskets per cycle
- Simple to operate thanks to clear fascia panel design
- Always the right programme – item-specific solutions
- First-class results thanks to freshwater wash system

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.


EAN: 4002515250013 / Material number: 07878390 / Old Material Number: 61805610D

<b>Construction type and design</b>	
Construction type	Built-under dishwasher
Range	Professional
Model	Speedplus
Wash system	Fresh water front loader
Number of levels	2
Front	Lotus white
Side panels	Lotus White
Convertible to a freestanding appliance	Stand 1-80, white
<b>Application</b>	
Suitable for small restaurants/bars	•
Suitable for hospitality industry	•
Suitable for guesthouses	•
Suitable for canteens	•
Suitable for small businesses	•
Suitable for fast food restaurants	•
Suitable for sports clubs	•
<b>Performance data</b>	
Circulation pump Qmax in l/min.	390
Shortest programme duration in min.	5
Maximum final rinse temperature in °C	70
Cleaning performance, plates/h	456
Cleaning performance, baskets/h	24
Possible to wash plastic baskets on 2 levels	•
Service life in wash cycles	15000
<b>Controls</b>	
Control system	TouchControl
Programme selection	Touch on MSetal
Max. delay start in h	24
Time left display	•
Programmes [number]	13
Programme sequence indicator	•
Choice of display language	•
Language-neutral operation	•
<b>Standard electrical connection</b>	
Electrical connection	3N AC 400V 50HZ
Heater rating in kW	8,50
Total connected load in kW	8,90
Fuse rating in A	16
CEE plug	•
Length of mains connection cable in m	1,70
<b>Possible voltage variant 1</b>	
Electrical connection	AC 230V 50HZ
Heater rating in kW	3,00
Total connected load in kW	3,40
Fuse rating in A	16
<b>Water connection/drainage</b>	
Cold water [number]	1
Hot water [number]	1
Required flow pressure in bar	0,40-10,00

## PG 8056 U [MK SPEEDplus]

Built-under fresh-water dishwasher

With baskets for hotels, restaurants and catering companies.



EAN: 4002515250013 / Material number: 07878390 / Old Material Number: 61805610D

Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•
Maximum water hardness in mmol/l	10,70
Water protection system	Waterproof system
Water consumption per wash cycle in l	8,00
<b>Dimensions and weight</b>	
External dimensions, height in mm	820
External dimensions, net width in mm	598
External dimensions, net depth in mm	580
External dimensions, gross height in mm	940
External dimensions, gross width in mm	675
External dimensions, gross depth in mm	745
Usable space in wash cabinet, height in mm	559
Usable space in wash cabinet, width in mm	530
Usable space in wash cabinet, depth of upper basket	474
Usable space in wash cabinet, depth of lower basket in mm	505
In-feed height above floor in mm	216
Net weight [kg]	63
Gross weight in kg	69
Maximum floor loading in N	1200
<b>Emissions data</b>	
Emissions – sound pressure at workplace	47 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	59,0
Heat dissipation into the room in MJ/h	1,08
<b>Programmes</b>	
Universal	•
Super short	•
Short	•
Hygiene	•
Cold/Pre-wash	•
Glasses	•
Beer glasses	•
Cutlery	•
Plastics	•
Energy save/Eco	•
Intensive	•
Reactivation	•
Drainage	•
<b>Basket design</b>	
1 x O 891 upper basket for cups	•
1 x U 890 lower basket for inserts	•
1 x E 810 insert for dessert plates	•
2 x E 816 inserts for plates	•
2 x E 165 inserts for cutlery	•
Height-adjustable upper basket	•
<b>Features</b>	
Drying	without
1 combi dispenser in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made from high-quality stain	•

PG 8056 U [MK SPEEDplus]

Built-under fresh-water dishwasher

With baskets for hotels, restaurants and catering companies.



EAN: 4002515250013 / Material number: 07878390 / Old Material Number: 61805610D

In-door salt container	•
Perfect GlassCare	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Adjustable wash temperature	•
Adjustable rinse time	•
Optical interface	•
A wide range of accessories (optional)	•
<b>Connection options</b>	
External dispensing module for liquid detergent	•
External dispensing module for rinse aid	•
<b>Standards, certs, symbols</b>	
CE	•
Complies with Machinery Directive 2006/42/EC	•
EMC	•
Interference suppression	•
VDE	•
DIN 10512	•
EN 1717	•