

KFN 29233 D ws  
 XL freestanding fridge freezer  
 with DailyFresh and Frost free for more freshness and highest convenience.



- Large capacity drawer with adjustable moisture – DailyFresh
- Optimum and maintenance-free LED lighting in compartment
- No icing up of food and no need to defrost thanks to Frost free
- More space and convenience thanks to XL interior cabinet

EAN: 4002515597613 / Material number: 10153960 / Old Material Number: 38292335EU1

<b>Appliance category</b>	
Fridge-freezer	•
<b>Construction type</b>	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Casing colour	White
Front colour	White
Refrigeration section lighting	LED
<b>User convenience</b>	
Networking with Miele@home	•
Accessories required	XKS 3100 W
Freshness system	DailyFresh
ComfortClean	•
DynaCool	•
NoFrost	•
DuplexCool	•
XL interior	•
VarioRoom	•
Concealed door opener	Click2open
Silence system	•
<b>Controls</b>	
Operating concept	FreshTouch
Fridge compartment can be switched off	Yes
Independent temperature regulation of fridge and freezer zones	No
Automatic SuperCool	•
SuperFreeze	•
No. of temperature zones	2
Sabbath mode	•
Party mode	•
Holiday mode	•
QuickCool Timer	•
<b>Fridge/Fridge section</b>	
No. of shelves	4
Chrome-plated metal bottle rack	•
No. of crisper drawers	1
CompactCase	•
Number of inner door racks for tinned food	3
Door rack for bottles	1
Door shelves	4
<b>Freezer/Freezer section</b>	
Number of freezer drawers	3
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	D
Annual energy consumption in kWh	203,31
Energy consumption in 24 h in kWh	0,55
<b>Safety</b>	
Lock function	•


KFN 29233 D ws  
 XL freestanding fridge freezer  
 with DailyFresh and Frost free for more freshness and highest convenience.



EAN: 4002515597613 / Material number: 10153960 / Old Material Number: 38292335EU1


Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•
<b>Technical data</b>	
Appliance width in mm	600
Appliance height in mm	2010
Appliance depth in mm	675
Weight in kg	84,6
Climate class	SN-T
Refrigerator compartment in l	262
4* freezer compartment in l	104
Total usable capacity in l	365
Storage time in case of fault in h	16
Freezer capacity in kg/24 h	9,00
Noise class (A–D)	C
Sound power in dB(A) re 1 pW	36
Current consumption (mA)	1400
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2,2
Replacing lamps	Customer Service
<b>Accessories supplied</b>	
Egg tray	•
Ice packs	•
Ice cube tray	•

KFN 29233 D ws  
 XL freestanding fridge freezer  
 with DailyFresh and Frost free for more freshness and highest convenience.




KF29233, KFN29233, KFN29433, KF29283, KFN29283, KFN29483, top view, (sketch) (\*footnote)

\*To ensure that energy consumption as stated is achieved, machines should be used together with the enclosed spacer brackets. This increases the total depth of the unit by approx. 1.5 cm. , Machines are still fully functional when operated without these brackets but have a slightly higher energy consumption.,



KF29233, KFN29233, KFN29433, KF29283, KFN29283, KFN29483, edt/cs, Draufsicht, (Skizze) (\*Fußnote)

\*To ensure that energy consumption as stated is achieved, machines should be used together with the enclosed spacer brackets. This increases the total depth of the unit by approx. 1.5 cm. , Machines are still fully functional when operated without these brackets but have a slightly higher energy consumption.,



KFN29233D, KFN29243D, KFN29493DE, KF29283D, KFN29283D, KFN29483D, KFNS28463E, KWNS28462E , installation draw

\*To ensure that energy consumption as stated is achieved, machines should be used together with the enclosed spacer brackets. This increases the total depth of the unit by approx. 1.5 cm. , Machines are still fully functional when operated without these brackets but have a slightly higher energy consumption.