

PG 8583 CD [WW ADP CM]

Laboratory dishwasher

with pump for AD water, liquid dispensing, DryPlus & conductivity monitoring.



- Performance/cycle, e.g. 128 laboratory bottles
- Safety – Wash pressure, spray arm and conductivity monitoring
- 72 % less water consumption compared to predecessor model*
- Efficient hot air drying – DryPlus
- Total security – link to process documentation possible

* compared to standard programme for G 7883 CD

EAN: 4002515631140 / Material number: 10224900 / Old Material Number: 62858351ZA

Construction type and version	
Construction type	Freestanding, can be built-under, wide, without lid
Casing	Stainless steel
Can be built-under	•
AutoClose – automatic door lock	•
Buzzer, acoustic signal at end of programme	•
Service-friendly design	•
Application	
Suitable for laboratories	•
Capacity	
Laboratory flasks per cycle [number]	128
Pipettes per cycle [number]	98
Performance data	
Circulation pump, Qmax in l/min	500
Wash cabinet usable capacity in l	145,00
Shortest programme running time in min	20
Tested operating hours	15000
Maximum final rinse temperature in °C	93
Control system	
Control type	TouchControl
Programme selection	Touch on MSetal
Direct-access pushbuttons	•
Max. delay start in h	24
Programmability	programmable
Programmes [number]	15
Free programme positions [number]	2
A0 value controls	•
Automatic programme restart	•
Time left display	•
Programme sequence display	•
Selectable display languages	•
Standard electrical connection	
Electrical connection	3N AC 400V 50HZ
Electric heater rating in kW	8,50
Total rated load in kW	9,30
Fuse rating in A	16
Length of mains connection cable in m	1,80
Possible voltage variant 1	
Electrical connection	AC 230V 50HZ
Electric heater rating in kW	2,50
Total rated load in kW	3,30
Fuse rating in A	16
Water connection/drainage	
Cold water [number]	1
Cold water for steam condenser [number]	1
Hot water [number]	1
Required flow pressure in kPa	200-1000
Maximum delivery head for drain pump in cm	100
Maximum water hardness (cold water/hot water) in mmol/l	10,70

PG 8583 CD [WW ADP CM]

Laboratory dishwasher

with pump for AD water, liquid dispensing, DryPlus & conductivity monitoring.



EAN: 4002515631140 / Material number: 10224900 / Old Material Number: 62858351ZA

VEP – with feed pump for DI water [number]	1
Drain pump [DN]	22
Integrated water softener	•
Water protection system	Waterproof system
Dimensions and weight	
Net weight in kg	98
Drying unit	
Integrated drying unit	•
Fan in kW	0,30
Heater element in kW	2,20
Air throughput in m ³ /h	60
Time setting in 1-minute increments	0-120
HEPA filter class	H14
HEPA filter filtration efficiency (in accordance with DIN EN 1822) in %	99,99
Dimensions and weight	
External dimensions, net height in mm	820
External dimensions, net width in mm	900
External dimensions, net depth in mm	600
External dimensions, gross height in mm	1095
External dimensions, gross width in mm	1200
External dimensions, gross depth in mm	800
Wash cabinet, usable height in mm	520
Wash cabinet, usable width in mm	530
Wash cabinet, depth of upper basket in mm	474
Wash cabinet, depth of lower basket in mm	520
Gross weight in kg	133
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1,40
Features	
Additional integrated dispenser pumps (optional)	•
Interface for process documentation (optional)	•
Customer Service interface	•
Extensive components (option)	•
Features	
1 dispenser pump for liquid cleaning agent	•
1 dispenser pump for neutralising agent	•
Steam condenser	•
Spray pressure monitoring	•
Spray arm monitoring	•
Conductivity monitoring	•
Multi-component filter system	•
Variable-speed heater pump	•
Load carrier – direct coupling	•
DryPlus	•
In-door salt container	•
Setting options for process chemicals (3 x 5 l / 2 x 10 l)	•
Wash cabinet seamlessly welded using laser technology	•
Heater elements outside wash cabinet	•

PG 8583 CD [WW ADP CM]

Laboratory dishwasher

with pump for AD water, liquid dispensing, DryPlus & conductivity monitoring.



EAN: 4002515631140 / Material number: 10224900 / Old Material Number: 62858351ZA

Connection options	
RS 232 serial interface (optional)	•
WiFi via DataDiary (optional)	•
Ethernet interface (optional)	•
Standards, test certificates and symbols	
VDE (electrical safety)	•
IP safety class according to EN 60529: IP 20	•
EN 61010-2-040	•
RoHS guideline 2011/65/EU	•
Machinery Directive 2006/42/EC	•
Standards, test certificates and symbols	
EN 61010-1	•