

DA 6698 W Puristic Edition 6000

Wall mounted cooker hood

with energy-efficient LED lighting and touch controls for simple operation.



- Family design – based on Miele built-in appliances
- Unique user convenience – Con@ctivity
- Powerful – 640 m³/h in Booster level
- Energy-efficient and quiet – powerful ECO motor
- Pleasantly quiet – Miele Silence package

EAN: 4002515935965 / Material number: 10750330 /
Old Material Number: 28669840D

Construction type	
Wall mounted cooker hood	•
Appliance Colour	Obsidian black
Operating modes	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUW 20
Active charcoal filter (order separately)	DKF 12-P
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Touch controls	•
Miele@mobile app	•
Booster levels	1
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Active charcoal filter saturation indicator	•
Silence package	•
Efficiency and sustainability	
Annual energy consumption in kWh/year	24,6
Energy efficiency class (A+++ – D)	A++
ECO motor	•
PowerManagement system	•
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
Cleaning and care	
Easy-to-clean canopy interior – CleanCover	•
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	3
Lighting	
LED	•
Number x W	3 x 3 W
Light intensity in lx	670 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
Fan	
Dual-action fan	•
DC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	200
Air throughput in Level 2 (m ³ /h) according to EN 61591	300
Air throughput in Level 3 (m ³ /h) according to EN 61591	400
Air throughput in booster level 1 (m ³ /h)	640

DA 6698 W Puristic Edition 6000

Wall mounted cooker hood

with energy-efficient LED lighting and touch controls for simple operation.



EAN: 4002515935965 / Material number: 10750330 /
Old Material Number: 28669840D

Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	36,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	44,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	52,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	63,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	21,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	29,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	37,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	48,0
Recirculation	
Air throughput in Level 1 (m³/h) according to EN 61591	110
Air throughput in Level 2 (m³/h) according to EN 61591	185
Air throughput in Level 3 (m³/h) according to EN 61591	315
Air throughput in Booster level 1 (m³/h) according to EN 61591	460
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	45,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	53,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	63,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	72,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	30,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	38,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	48,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	57,0
Safety	
Safety switch-off	•
Single-ply safety glass (ESG)	•
Technical data	
Overall hood height for extraction mode and external in mm	710–1030
Overall hood height for recirculation and external in mm	840–1160
Overall height for vented and external in in. (mm)	710
Canopy width in mm	898
Overall height for extraction mode and external mode cooker hoods in mm	1030
Canopy height in mm	85
Overall height for recirculation in in. (mm)	840
Canopy depth in mm	500
Overall height for recirculation mode cooker hoods in mm	1160

DA 6698 W Puristic Edition 6000

Wall mounted cooker hood

with energy-efficient LED lighting and touch controls for simple operation.



EAN: 4002515935965 / Material number: 10750330 /
Old Material Number: 28669840D

Net weight in kg	26,0
Length of supply lead in m	1,5
Standard plug fitted	•
Minimum height above electric hobs in mm	450
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Total rated load in kW	0,08
Frequency in Hz	50
Installation notes	
Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Telescopic chimney	•
Combination with WiFi-enabled Miele hob	recommended
Accessories included	
Non-return flap	•
Optional accessories	
Active charcoal filter, can be reactivated	DKF 12-R

