

DA 6698 W Puristic Edition 6000

Wall mounted cooker hood

with energy-efficient LED lighting and touch controls for simple operation.



- Family design – based on Miele built-in appliances
- Unique user convenience – Con@ctivity
- Powerful – 640 m<sup>3</sup>/h in Booster level
- Energy-efficient and quiet – powerful ECO motor
- Pleasantly quiet – Miele Silence package

EAN: 4002515935965 / Material number: 10750330 / Old Material Number: 28669840D

<b>Construction type</b>	
Wall mounted cooker hood	•
<b>Operating modes</b>	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUW 20
Active charcoal filter (order separately)	DKF 12-P
<b>Design</b>	
Colour	Obsidian black
<b>User convenience</b>	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Touch controls	•
Miele@mobile app	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Silence package	•
Easy-to-clean canopy interior – CleanCover	•
<b>Efficiency and sustainability</b>	
Annual energy consumption in kWh/year	24,6
Energy efficiency class (A+++ – D)	A++
ECO motor	•
PowerManagement system	•
Annual energy consumption in kWh/year	24,6
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	3
<b>Lighting</b>	
LED	•
Number x W	3 x 3 W
Light intensity in lx	670 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
<b>Fan</b>	
Dual-action fan	•
DC motor	•
<b>Exhaust air</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	200
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	300
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	400
Air throughput in Booster level (m <sup>3</sup> /h) according to EN 61591	640
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	36,0

DA 6698 W Puristic Edition 6000

Wall mounted cooker hood

with energy-efficient LED lighting and touch controls for simple operation.



EAN: 4002515935965 / Material number: 10750330 / Old Material Number: 28669840D

Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	44,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	52,0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	63,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	21,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	29,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	37,0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	48,0
<b>Recirculation</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	110
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	185
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	315
Air throughput in Booster level 1 (m <sup>3</sup> /h) according to EN 61591	460
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	45,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	53,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	63,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	72,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	30,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	38,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	48,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	57,0
<b>Safety</b>	
Safety switch-off	•
Single-ply safety glass (ESG)	•
<b>Technical data</b>	
Overall hood height for extraction mode and external in mm	710–1030
Overall hood height for recirculation and external in mm	840–1160
Overall height for vented and external in in. (mm)	710
Canopy width in mm	898
Overall height for extraction mode and external mode cooker hoods in mm	1030
Canopy height in mm	85
Overall height for recirculation in in. (mm)	840
Canopy depth in mm	500
Overall height for recirculation mode cooker hoods in mm	1160
Minimum height above electric hobs in mm	450
Minimum height above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Net weight in kg	26,0

DA 6698 W Puristic Edition 6000

Wall mounted cooker hood

with energy-efficient LED lighting and touch controls for simple operation.




EAN: 4002515935965 / Material number: 10750330 / Old Material Number: 28669840D

Length of supply lead in m	1,5
Standard plug fitted	•
Total rated load in kW	0,08
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
<b>Installation notes</b>	
Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Telescopic chimney	•
Combination with WiFi-enabled Miele hob	recommended
<b>Accessories included</b>	
Non-return flap	•
<b>Optional accessories</b>	
Active charcoal filter	Nein
Active charcoal filter, can be reactivated	DKF 12-R

DA 6698 W Puristic Edition 6000

Wall mounted cooker hood

with energy-efficient LED lighting and touch controls for simple operation.



DA 6698 W, CLST (Installation drawing)

1. Extraction, 2. Recirculation, 3 Ventilation grilles at the top for recirculation, 4. + 5. Vent cut-out positions (Area 5 not required for recirculation)