

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



- Customised kitchen design – fully integrated in 880 mm width
- Unique user convenience – Con@ctivity
- Powerful – 640 m³/h in Booster level
- Energy-efficient and quiet – powerful ECO motor
- Elegant and efficient – edge extraction panels

EAN: 4002515935552 / Material number: 10751460 / Old Material Number: 28269855D

Construction type	
Integrated extractor	•
Operating modes	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
Active charcoal filter (order separately)	DKF 19-P
Design	
Colour	Stainless steel
Edge extraction	•
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Miele@mobile app	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Easy-to-clean canopy interior – CleanCover	•
Efficiency and sustainability	
Annual energy consumption in kWh/year	28,6
Energy efficiency class (A+++ – D)	A+
ECO motor	•
PowerManagement system	•
Annual energy consumption in kWh/year	28,6
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
Lighting	
LED	•
Number x W	4 x 3 W
Light intensity in Lx	650 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
Fan	
Dual-action fan	•
DC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	200
Air throughput in Level 2 (m ³ /h) according to EN 61591	300
Air throughput in Level 3 (m ³ /h) according to EN 61591	400
Air throughput in Booster level (m ³ /h) according to EN 61591	640
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	36,0

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515935552 / Material number: 10751460 / Old Material Number: 28269855D

Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	44,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	51,0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	62,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	22,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	30,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	37,0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	48,0
Recirculation	
Air throughput in Level 1 (m ³ /h) according to EN 61591	135
Air throughput in Level 2 (m ³ /h) according to EN 61591	220
Air throughput in Level 3 (m ³ /h) according to EN 61591	365
Air throughput in Booster level 1 (m ³ /h) according to EN 61591	535
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	47,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	55,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	62,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	74,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	41,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	48,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	59,0
Safety	
Safety switch-off	•
Technical data	
Canopy width in mm	880
Canopy height in mm	63
Canopy depth in mm	293
Minimum height above electric hobs in mm	450
Net weight in kg	14,0
Length of supply lead in m	1,5
Standard plug fitted	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0,09
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50

DA 2698

Extractor unit

with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515935552 / Material number: 10751460 / Old Material Number: 28269855D

Installation notes	
Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Combination with WiFi-enabled Miele hob	recommended
Accessories included	
Non-return flap	•
Optional accessories	
Active charcoal filter	Nein

