

## KM 6565 FR

Electric hob with onset controls

in maximum width for the ultimate in cooking and user convenience.



- Intuitive quick selection via number sequences – Smart Select
- Attractive design – 942 mm wide with all-round frame
- Particularly versatile – 4 cooking zones incl. 1 extended/2 Vario zones
- Unbeatably fast – 1 ExtraSpeed cooking zone
- Communication with the cooker hood – automatic Con@ctivity function

EAN: 4002515997628 / Material number: 10882070 / Old Material Number: 26656500D

Heating type	
Heating type	Electric
Construction type	
Independent of cooker	•
Design	
Elegant glass ceramic surface	•
Ceramic surface colour	Black
Stainless steel frame	•
Surface-mounted installation	•
Cooking zone details	
Number of cooking zones	4
1st cooking zone/cooking area	
Position	front left
Type	Single-circuit ring
Size in mm	Ø 145
Max. rating in W	1200
2nd cooking zone/cooking area	
Position	rear left
Type	Dual-circuit ring
Size in mm	Ø 120 / Ø 210
Max. rating in W	750/2200
3rd cooking zone/cooking area	
Position	rear centre
Type	ExtraSpeed
Size in mm	Ø 145 / Ø 210 / Ø 270
Max. rating in W	1050/2050/3200
4th cooking zone/cooking area	
Position	rear right
Type	Casserole area
Size in mm	Ø 170 / 170x290
Max. rating in W	1500/2600
User convenience	
Miele@home	•
Operation via sensor controls	Smart Select
Automatic function Con@ctivity 3.0	•
Extended cooking zone	•
Display colour	Yellow
Auto heat-up	•
Keeping warm	•
Stop & Go function	•
Recall function	•
Safety switch-off	•
Individual setting options (e.g. buzzers)	•
Wipe protection	•
Minute minder	•
Efficiency and sustainability	
Residual heat utilisation	•
Power rating in off mode in W	0,5
Power rating in standby mode in W	1,0
Power rating in networked standby in W	2,0

## KM 6565 FR

Electric hob with onset controls

in maximum width for the ultimate in cooking and user convenience.




EAN: 4002515997628 / Material number: 10882070 / Old Material Number: 26656500D

Time until automatic switch to off mode in min	20
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20
<b>Cleaning and care</b>	
Easy to clean ceramic glass	•
<b>Safety</b>	
Safety switch-off	•
Lock function	•
System lock	•
Overheating protection	•
Residual heat indicator	•
<b>Technical data</b>	
Dimensions (H x W x D) in mm	50 x 942 x 526
Dimensions in mm (width)	942
Dimensions in mm (height)	50
Dimensions in mm (depth)	526
Cutout dimensions in mm (width) with surface-mounted installation	916
Cutout dimensions in mm (depth) with surface-mounted installation	500
Casing height incl. connection box in mm	43
Weight in kg	13
Total rated load in kW	9,20
Length of supply lead in m	1,4
Voltage in V	230
Frequency in Hz	50-60
<b>Accessories included</b>	
Razor-blade scraper	•
Mains cable	Yes

## KM 6565 FR

Electric hob with onset controls

in maximum width for the ultimate in cooking and user convenience.



KM 6565 FR (Installation drawing)

1) Front, 2) Mains connection box. Built-in height = 40 mm, mains connection cable L = 1440 mm, 3) WLAN stick connection point, 4) Clamp springs