

## KM 6565 FR

Electric hob with onset controls

in maximum width for the ultimate in cooking and user convenience.



- Intuitive quick selection via number sequences – Smart Select
- Attractive design – 942 mm wide with all-round frame
- Particularly versatile – 4 cooking zones incl. 1 extended/2 Vario zones
- Unbeatably fast – 1 ExtraSpeed cooking zone
- Communication with the cooker hood – automatic Con@ctivity function


EAN: 4002515997628 / Material number: 10882070 /  
Old Material Number: 26656500D

Heating type	
Heating type	Electric
Construction type	
Independent of cooker	•
Design	
Elegant glass ceramic surface	•
Surface-mounted/flush-fit	–/–
Ceramic surface colour	Black
Stainless-steel frame	•
Surface-mounted installation	•
Cooking zone details	
Number of cooking zones	4
1st cooking zone/cooking area	
Position	front left
Type	Single-circuit ring
Size in mm	Ø 145
Max. rating in W	1200
2nd cooking zone/cooking area	
Position	rear left
Type	Dual-circuit ring
Size in mm	Ø 120 / Ø 210
Max. rating in W	750/2200
3rd cooking zone/cooking area	
Position	rear centre
Type	ExtraSpeed
Size in mm	Ø 145 / Ø 210 / Ø 270
Max. rating in W	1050/2050/3200
4th cooking zone/cooking area	
Position	rear right
Type	Casserole area
Size in mm	Ø 170 / 170x290
Max. rating in W	1500/2600
User convenience	
Networking with Miele@home	•
Automatic function Con@ctivity	•
Operation via sensor controls	Smart Select
Extended cooking zone	•
Display colour	Yellow
Stop & Go function	•
Wipe protection	•
Recall function	•
Minute minder	•
Safety switch-off	•
Auto heat-up	•
Keeping warm	•
Individual setting options (e.g. buzzers)	•
Efficiency and sustainability	
Residual heat utilisation	•

## KM 6565 FR

Electric hob with onset controls

in maximum width for the ultimate in cooking and user convenience.



EAN: 4002515997628 / Material number: 10882070 /

Old Material Number: 26656500D

Power rating in off mode in W	0,5
Power rating in standby mode in W	1,0
Power rating in networked standby in W	2,0
Time until automatic switch to off mode in min	20
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20

### Cleaning and care

Easy to clean ceramic glass	•
-----------------------------	---

### Safety

Safety switch-off	•
Lock function	•
System lock	•
Overheating protection	•
Residual heat indicator	•

### Technical data

Dimensions (H x W x D) in mm	50 x 942 x 526
Dimensions in mm (width)	942
Dimensions in mm (height)	50
Dimensions in mm (depth)	526
Cutout dimensions in mm (width) with surface-mounted installation	916 mm
Cutout dimensions in mm (depth) with surface-mounted installation	500 mm
Casing height incl. connection box in mm	43
Weight in kg	13
Total rated load in kW	9,20
Length of supply lead in m	1,4
Voltage in V	230
Frequency in Hz	50-60


### Accessories included

Razor-blade scraper	•
Mains cable	Yes

## KM 6565 FR

Electric hob with onset controls

in maximum width for the ultimate in cooking and user convenience.



KM 6565 FR (Installation drawing)

1) Front, 2) Mains connection box. Built-in height = 40 mm, mains connection cable L = 1440 mm, 3) WLAN stick connection point, 4) Clamp springs