

## PDR 507 [EL]

Professional vented dryer, Little Giants, electrically heated with extremely short programme running times. Performance 7.0 kg in 37 min.



- Drum volume 130.00 l, load size 7.0 kg
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Precision drying of all fabrics – PerfectDry

EAN: 4002516086390 / Material number: 11050510 / Old Material Number: 52507452D

Construction type and version	
Construction type	Front-loader, stackable
Range	Performance
Front	Stainless steel
Fascia color	Stainless steel
Load in kg	7,0
Drum volume in l	130,00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	5,50
Specific energy consumption in kWh/kg	0,50
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0,50
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0,42
Programme duration in min.	37
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	37
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	32
Control system	
Control system	M Select
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•

## PDR 507 [EL]

Professional vented dryer, Little Giants, electrically heated with extremely short programme running times. Performance 7.0 kg in 37 min.



EAN: 4002516086390 / Material number: 11050510 / Old Material Number: 52507452D

Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3N~ 400V 50/60HZ
Electric heater rating in kW	6,14
Total connected load in kW	6,40
Fuse rating in A	10
<b>Possible voltage variant 1</b>	
Electrical connection	230V~ 50/60HZ
Heater rating in kW	2,99
Total connected load in kW	3,24
Fuse rating in A	16
<b>Possible voltage variant 2</b>	
Electrical connection	3~ 230V 50/60HZ
Heater rating in kW	6,14
Total connected load in kW	6,40
Fuse rating in A	16
<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	850
External dimensions, width in mm	605
External dimensions, depth in mm	717
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	51,5
Gross weight in kg	57
Maximum floor load in N/m <sup>2</sup>	920
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	0,76
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Energy efficiency class	C
Annual energy consumption in kWh	546
Noise in dB(a) in the Cottons Normal dry standard programme with a full load	66
Duration in minutes in the standard programme	48
How it works	Vented
Load in kg	7,0

PDR 507 [EL]

Professional vented dryer, Little Giants, electrically heated with extremely short programme running times. Performance 7.0 kg in 37 min.



EAN: 4002516086390 / Material number: 11050510 / Old Material Number: 52507452D

<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•