

WWW980 WPS Passion

W1 front-loader washing machine

the economical all-rounder that meets the highest expectations.



- Tested for 20 years of perfect laundry care
- Save energy in the best energy efficiency class (A)
- M Touch – simple control by tapping or swiping
- SteamCare reduces ironing time by up to 50 % and freshens up your clothes
- Save up to 65 % on energy costs with an additional
- hot water connection

EAN: 4002516588795 / Material number: 11099100 / Old Material Number: 11WW9806ZA

| | |
|--|-----------------------------|
| Construction type | |
| Suitable for stacking | • |
| Side-by-side | • |
| Slot-in | • |
| Door hinge | right |
| Model | |
| Product brand | W1 White Edition |
| Front-loader | • |
| Spinning | |
| Max. spin speed | 1600 |
| Rinse hold | • |
| Without spin function | • |
| Design | |
| Appliance colour | Lotus white |
| Control panel colour | Lotus white |
| Door design | Alu silver with chrome ring |
| Control panel version | 5° inclined |
| Control type | Touch control |
| Display | MTouch |
| Cleaning performance | |
| Innovative PowerWash technology | • |
| TwinDos automatic detergent dispensing | • |
| CapDosing portioned dispensing | • |
| Stains option | • |
| Certified virus hygiene | • |
| Gentle laundry care | |
| Honeycomb drum | • |
| Load in kg | 9,0 |
| User convenience | |
| Networking with Miele@home | • |
| SteamCare steam system | • |
| Delay start up to 24 hours | • |
| Time left display | • |
| Time of day display | • |
| Programme sequence indicator | • |
| Washing assistant | • |
| Information text | • |
| Favourite programmes | • |
| Drum lighting | LED |
| MultiLingua | • |
| AutoClean detergent drawer | • |
| Load indicator and dispensing recommendation | • |
| AddLoad | • |
| Efficiency and sustainability | |
| Hot water connection | • |
| EcoFeedback | • |
| Low temperature wash "Cold" and "20 °C" | • |
| Automatic load control | • |
| Flow meter | • |
| Foam sensing | • |

WWV980 WPS Passion

W1 front-loader washing machine

the economical all-rounder that meets the highest expectations.



EAN: 4002516588795 / Material number: 11099100 / Old Material Number: 11WW9806ZA

| | |
|----------------------------------|-------------------|
| ProfiEco motor | • |
| Wash programmes | |
| QuickPowerWash | • |
| Automatic plus | • |
| Cottons (coloureds) | • |
| Minimum iron | • |
| Delicates | • |
| Shirts | • |
| Silk (hand-washable) | • |
| Woollens (hand-washable) | • |
| Express 20 | • |
| Dark garments | • |
| Denim | • |
| Outerwear | • |
| Proofing | • |
| Sportswear | • |
| Trainers | • |
| Down duvets | • |
| Pillows | • |
| Down | • |
| Curtains | • |
| Cottons hygiene | • |
| Freshen up (steam) | • |
| Steam care | • |
| Clean machine | • |
| Cottons arrow | • |
| First wash | • |
| Separate rinse | • |
| Starch | • |
| Drain / Spin | • |
| ECO 40-60 | • |
| Washing extras | |
| SingleWash | • |
| Short | • |
| Soak | • |
| Pre-wash | • |
| Water plus | • |
| Additional rinse cycle | • |
| Extra quiet | • |
| Steam smoothing | • |
| Pre-ironing with steam | • |
| Buzzer | • |
| AllergoWash | • |
| Quality | |
| Counterweights made of cast iron | • |
| Safety | |
| Water protection system | Waterproof-System |
| Safety lock | • |
| PIN-Code | • |
| Optical interface | • |

WWV980 WPS Passion

W1 front-loader washing machine

the economical all-rounder that meets the highest expectations.



EAN: 4002516588795 / Material number: 11099100 / Old Material Number: 11WW9806ZA

Technical data

| | |
|--|-----------|
| Dimensions in mm (width) | 596 |
| Dimensions in mm (height) | 850 |
| Dimensions in mm (depth) | 643 |
| Appliance depth in mm with opened door | 1077 |
| Weight in kg | 98 |
| Total rated load in kW | 2,10-2,40 |
| Voltage in V | 220-240 |
| Fuse rating in A | 10 |
| Frequency in Hz | 50 |
| Length of supply lead in m | 2 |
| Replacing lamps | Service |

Accessories included


| | |
|---|---|
| 3 Caps | • |
| UltraPhase 1 + 2 | • |
| Voucher for 5 Miele UltraPhase cartridges | • |

Available display languages


Available display languages via MultiLingua

bahasa malaysia, dansk, deutsch, english (AU), english (CA), english (GB), english (US), español, français (CA), français (FR), hrvatski, italiano, magyar, nederlands, norsk, polski, portugês, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,


WWW980 WPS Passion
W1 front-loader washing machine
the economical all-rounder that meets the highest expectations.




W1 drawing, facia 5 degree, measures in mm



W1 drawing, facia 5 degree, measures in mm



W1 drawing, facia 5 degree, measures in mm



W1 drawing, facia 5 degree, measures in mm