

DO 7860

Dialog oven

- from designer-level kitchen to star rated kitchen.



- Innovative cooking every day in your own home thanks to M Chef
- Improved results in terms of texture and uniformity
- Demanding dishes made easy with Gourmet Assistant and Gourmet Pro
- Multi-stage cooking with M Chef Menu
- Time savings of up to 70 % combined with excellent quality

EAN: 4002516160137 / Material number: 11108020 /  
Old Material Number: 20786045GB

<b>Construction type</b>	
Appliance Colour	Stainless steel/Clean Steel
<b>Construction type and design</b>	
Dialog cooker	•
PureLine	•
Back-lit M Chef logo	•
<b>Convenience features</b>	
M Chef innovative cooking	•
Private dining	•
Gourmet Pro	•
Gourmet Assistant	•
Pre-heating	•
Food probe	•
Keeping warm	•
Crisp function	•
<b>Operating modes</b>	
Fan plus	•
Conventional heat	•
Moisture plus	•
Moisture plus with Auto roast	•
Moisture plus with Fan plus	•
Moisture plus with Intensive bake	•
Moisture plus with Conventional heat	•
M Chef menu	•
M Chef + Fan plus	•
M Chef + Conventional heat	•
M Chef + Intensive bake	•
M Chef + Moisture plus	•
M Chef + Auto roast	•
M Chef + Fan grill	•
M Chef + Full grill	•
Extremely gentle defrosting	•
Intensive bake	•
Auto roast	•
Fan grill	•
Grill	•
Economy grill	•
Top heat	•
Bottom heat	•
Low temperature cooking	•
Special applications	•
<b>User convenience</b>	
Networking with Miele@home	•
Display	M Touch
MultiLingua	•
MyMiele	•
Time of day display	•
Date display	•

## DO 7860 Dialog oven

- from designer-level kitchen to star rated kitchen.



EAN: 4002516160137 / Material number: 11108020 /  
Old Material Number: 20786045GB

Minute minder	•
SoftOpen	•
Programmable cooking duration	•
Actual temperature display	•
Recommended temperature	•
Help function	•
Individual settings	•
Timed steam bursts programmable	•
Polyphonic buzzers	•
Clock synchronisation	•
Programmable start of cooking duration	•
Target temperature display	•
Buzzer when desired temperature is reached	•
Suggested Gourmet units	•
Sabbath programme	•
<b>Efficiency and sustainability</b>	
Residual heat utilisation	•
<b>Cleaning and care</b>	
Stainless steel/CleanSteel finish	•
Pyrolytic self-cleaning	•
Heated catalyser	•
<b>Safety</b>	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Door lock during pyrolytic cleaning	•
Sensor lock	•
<b>Technical data</b>	
Appliance width in mm	595
Oven compartment volume in l	50
No. of shelf levels	4
Oven light	BrilliantLight
Voltage in V	220-240
Fuse rating in A	16
Temperatures in °C	30–300
Number of phases	1
Temperatures min. in °C	30
Temperatures max. in °C	300
Niche width min. in mm	560
Niche width max. in mm	568
Niche height min. in mm	590
Niche height max. in mm	595
Niche depth in mm	550
Appliance height in mm	596
Appliance depth in mm	569
Weight in kg	60,8
Total rated load in kW	3,70
Frequency in Hz	50

DO 7860  
Dialog oven

- from designer-level kitchen to star rated kitchen.



EAN: 4002516160137 / Material number: 11108020 /  
Old Material Number: 20786045GB

Mains cable	•
Length of supply lead in m	2,00
Replacing lamps	Service

**Accessories included**


Baking tray with PerfectClean	1
Universal tray with PerfectClean	1
Baking and roasting rack PyroFit	1
Descaling tablets	2

**Available display languages**


Available display languages through MultiLingua

bahasa malaysia, dansk,  
deutsch, english, español,  
français, hrvatski, italiano,  
magyar, nederlands, norsk,  
polski, português, русский,  
română, slovenčina,  
slovenščina, srpski, suomi,  
svenska, türkçe, українська,  
čeština, ελληνικά, [?], [?]  
[?], [?], [?], [?], [?]


DO 7860  
 Dialog oven  
 - from designer-level kitchen to star rated kitchen.




DO7860, installation drawings  
 22 mm – glass, 23,3 mm – metal




DO7860, DO7860 C (CN), installation drawings, GB,  
 AUS, CN  
 22 mm – glass, 23.3 mm – metal




DO7860, DO7860C (CN), installation drawings




DO7860, DO7860C (CN), installation drawings



DO7860, installation drawings  
 1) Mains Connection cable, L = 1500 mm, 2) No connection in this area, 3) Lüftungsausschnitt min. 150 cm<sup>2</sup>



DO7860, DO7860 C (CN), installation drawings, GB,  
 AUS, CN  
 1) Mains connection cable, L = 1500 mm, 2) No connection in this area, 3) Lüftungsausschnitt min. 150 cm<sup>2</sup>



H7000 handle, installation drawing  
 1) 400 mm, 2) 360 mm, 3) 47 mm, 4) 24 mm, 5) 32.5 mm