

Complete C3 Pure Black PowerLine Cylinder vacuum cleaner

With maximum suction power and foot controls for thorough, convenient vacuuming.



- High suction power – 2000 W
- Versatile applications – universal floorhead
- Convenient and versatile with three integrated accessories
- Extremely convenient height adjustment thanks to a Comfort telescopic tube.
- Easy cleaning of larger areas thanks to 12 m operating radius

EAN: 4002516120735 / Material number: 11121570 / Old Material Number: 41GDA339ZA

Construction type	
Cylinder vacuum cleaner with dustbag	•
Product brand	Complete C3
Motor type	PowerLine
Product type	SGDA3
Appliance Colour	Obsidian black
User convenience	
Electronic suction power control	+/- footswitches
Illuminated power indicator	•
Ergonomic carrying handle	•
Ergonomic handle	•
Silence system	•
Suction tube	Comfort telescopic tube
Park system for pauses during vacuuming	•
Park system	on both sides
Comfort cable rewind	•
Efficiency and sustainability	
Nominal power consumption in W	1700
Mobility	
Castors with steel shaft, gentle on floors	•
3-point manoeuvrability	•
Operating radius in m	11
Cable length in m	8,5
Filter system	
Vacuum cleaner bag type	HyClean GN
Dustbag volume in l	4,5
Dustbag change indicator	•
Exhaust filter	AirClean filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic dustbag positioning	•
All-round furniture protection strip	•
Technical data	
Power	2000
Width in mm	496
Height in mm	227
Weight in kg	8,2
Accessories included	
Three-piece accessory set	Integrated
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush with synthetic bristles	•
SBD 365-3 floorhead	•
Filter	AirClean filter
Cleaning tool	No