

G 7310 SC AutoDos  
Freestanding dishwashers  
with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Innovative design and maximum convenience – 3D MultiFlex Tray
- Communication with the machine could not be easier – Miele@home
- Perfect results in less than one hour – QuickPowerWash
- Versatile and secure – ExtraComfort basket design

EAN: 4002516282839 / Material number: 11433800 / Old Material Number: 21731017ZA

<b>Model</b>	
Freestanding dishwasher	•
60 cm dishwasher	•
<b>Design</b>	
Control panel colour	Stainless steel/CleanSteel
Control panel version	Straight fascia
Control type	Softkeys
Display	1-line text display
Display colour	White
MultiLingua	•
<b>Convenience</b>	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	ComfortClose
Operating noise dB(A) re 1 pW	43
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	Display
Display language selection	•
<b>Efficiency and sustainability</b>	
Power rating in standby mode in W	0,30
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
<b>Quality of results</b>	
Fresh water dishwasher	•
SensorDry	•
Recirculation Turbothermic drying	•
Active condensation drying	•
BrilliantGlassCare	•
<b>Wash programmes</b>	
QuickPowerWash	•
ECO	•
Automatic	•
Intensive 75 °C	•
PowerWash	•
Gentle	•
Hygiene	•
SolarSave	•
ExtraQuiet 40 dB(A)	•
Appliance care	•
<b>Dishwashing options</b>	
AutoDos	•
IntenseZone	•
Express	•
Extra Clean	•
Extra dry	•

G 7310 SC AutoDos  
 Freestanding dishwashers  
 with automatic dispensing thanks to AutoDos with integrated PowerDisk.




EAN: 4002516282839 / Material number: 11433800 / Old Material Number: 21731017ZA

<b>Basket design</b>	
Cutlery loading	3D MultiFlex tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	ExtraComfort
<b>Safety</b>	
Waterproof system	•
Filter indicator light	•
Safety lock	•
<b>Technical data</b>	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	845
Niche height maximal in mm	880
Niche depth in mm	600
Appliance width in mm	598
Appliance height in mm	845
Appliance depth in mm	600
Depth with door open in cm	119,5
Net weight in kg	59,0
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,70
<b>Available display languages</b>	
Available display languages via MultiLingua	deutsch, english, español, français, italiano, nederlands, portugês, türkçe
<b>Accessories included</b>	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7310 SC AutoDos

Freestanding dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, free standing dishwasher, 60cm (installation drawing)