

## G 5000 SC Active

Freestanding dishwashers

in tried-and-tested Miele quality at an affordable entry-level price.



- Perfect results in less than one hour – QuickPowerWash
- Save up to 50 % more electricity – hot water connection
- Versatile and secure – comfort basket design
- Very easy door opening and closing – ComfortClose
- Maximum versatility – Height-adjustable upper basket

EAN: 4002516333784 / Material number: 11528600 / Old Material Number: 21500016ZA

<b>Model</b>	
Freestanding dishwasher	•
60 cm dishwasher	•
<b>Design</b>	
Control panel colour	Brilliant White
Control panel version	Straight fascia
Control type	Programme selector button
Display	3-digit 7-segment display
Display colour	Yellow
<b>Convenience</b>	
Door closing aid	ComfortClose
Operating noise dB(A) re 1 pW	45
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	acoustic
<b>Efficiency and sustainability</b>	
Drying class	A
Water consumption in the ECO programme in l	8,9
Annual water consumption in the ECO programme in l	2492
Annual energy consumption in ECO programme in kWh	266
Power rating in standby mode in W	0,30
Number of place settings	14
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
<b>Quality of results</b>	
Fresh water dishwasher	•
<b>Wash programmes</b>	
QuickPowerWash	•
ECO	•
Automatic	•
Intensive 75 °C	•
Gentle	•
<b>Dishwashing options</b>	
Express	•
Extra Clean	•
Extra dry	•
<b>Basket design</b>	
Cutlery loading	Cutlery tray
FlexCare cup rack	1
Basket design	Comfort
<b>Safety</b>	
Waterproof system	•
Safety lock	•
<b>Technical data</b>	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	845
Niche height maximal in mm	880
Niche depth in mm	600

## G 5000 SC Active

Freestanding dishwashers

in tried-and-tested Miele quality at an affordable entry-level price.



EAN: 4002516333784 / Material number: 11528600 / Old Material Number: 21500016ZA

Appliance width in mm	598
Appliance height in mm	845
Appliance depth in mm	600
Depth with door open in cm	119,5
Net weight in kg	53,5
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,70

### Accessories included

1 x UltraTabs box (20 tabs)

Voucher for 1 x box of UltraTabs (20 tabs) or 9 boxes at a reduced price

•

•