

## CM 6160 MilkPerfection Countertop coffee machine

With WiFiConn@ct and a wide selection of speciality coffees for maximum freedom.



- Creamy milk froth for a wide range of coffee specialities
- Perfect results and intense coffee flavour – AromaticSystem
- Two coffees at once at the touch of a button – OneTouch for Two
- Convenient cleaning and maintenance programmes
- Communication with the machine could not be easier – WiFi Conn@ct

EAN: 4002516362050 / Material number: 11590180 / Old Material Number: 29616001GBX

Construction type and design	
Freestanding bean-to-cup coffee machine	•
Colour	Lotus white
Convenience features	
AromaticSystem	•
OneTouch preparation	•
OneTouch for Two preparation	•
DoubleShot	•
Programmable User profiles	4
Aroma-friendly conical grinder	•
Selectable grinder setting	•
Additional coffee types in ground coffee form possible	•
Programmable amount of coffee	•
Programmable amount of water	•
Programmable water temperature	•
Amount of milk can be programmed	•
Programmable amount of milk froth	•
Pre-brewing programmable	•
TeaTimer	•
User convenience	
Networking with Miele@home	•
Display	DirectSensor
PerformanceMode	•
BrilliantLight	•
Expert mode	•
MultiLingua	•
No. of bean types	1
No. of bean containers	1
Capacity of bean container A in g	300
Bean container capacity, total in g	300
Capacity of water container in l	1,8
Capacity of waste container in capsules	10
Drip tray capacity	0,8
Easily accessible containers	•
Programmable standby time	•
Programmable settings	•
Beverages	
Selectable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•

CM 6160 MilkPerfection  
Countertop coffee machine

With WiFiConn@ct and a wide selection of speciality coffees for maximum freedom.



EAN: 4002516362050 / Material number: 11590180 / Old Material Number: 29616001GBX

Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Warm water, single	•
Hot water, single	•
Black tea, single	•
Herbal tea, single	•
Fruit tea, single	•
Green tea, single	•
White tea, single	•
Japanese tea, single	•
Coffee pot	•
<b>Efficiency and sustainability</b>	
Energy-saving eco-mode selectable	•
Power rating in standby mode in W	0,1
Power rating in networked standby in W	0,5
<b>Cleaning convenience</b>	
Manual descaling	•
Automatic rinsing of milk pipework with water from the water container	•
Convenient cleaning programmes	•
Automatic rinsing function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
Programmable water hardness	•
<b>Technical data</b>	
Height-adjustable serving spout in cm	14,0
Height-adjustable serving spout in cm	8,0
Appliance width in mm	251
Appliance height in mm	359
Appliance depth in mm	427
Total rated load in kW	1,45
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Pump pressure in bar	15
Length of supply lead in m	1,4
<b>Accessories supplied</b>	
Stainless steel milk tube	•

CM 6160 MilkPerfection

Countertop coffee machine

With WiFiConn@ct and a wide selection of speciality coffees for maximum freedom.



EAN: 4002516362050 / Material number: 11590180 / Old Material Number: 29616001GBX

Descaling tablets

•

Cleaning tablets

•

Brief operating instructions on rear of unit

•

#### Available display languages

Available display languages through MultiLingua

bahasa malaysia, dansk,  
deutsch, english, español,  
français, hrvatski, italiano,  
magyar, nederlands,  
norsk, polski, português,  
русский, română,  
slovenčina, slovenščina,  
srpski, suomi, svenska,  
türkçe, українська, čeština,  
ελληνικά,