

KFNS 7784 D

Built-in fridge-freezer combination

FlexiLight 2.0, DynaCool, NoFrost and FlexiTray for maximum convenience.



- Spacious drawer with moisture control – DailyFresh
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool
- Easy to remove items thanks to pivotable glass shelf – FlexiTray

EAN: 4002516420774 / Material number: 11738320 / Old Material Number: 38778401AUS

<b>Appliance category</b>	
Fridge-freezer	•
<b>Construction type</b>	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
Side-by-side enabled	•
<b>Design</b>	
Refrigeration section lighting	FlexiLight 2,0
Freezer compartment lighting	LED
Fan lighting	•
<b>User convenience</b>	
Networking with Miele@home	•
Freshness system	DailyFresh
Fine adjustment inner door	•
ComfortClean	•
DynaCool	•
NoFrost	•
DuplexCool	•
ComfortSize	•
VarioRoom	•
SoftClose	•
<b>Control system</b>	
Operating concept	FreshTouch
Fridge compartment can be switched off	Yes
Independent temperature regulation of fridge and freezer zones	Yes
Automatic SuperCool	•
SuperFreeze	•
No. of temperature zones	2
Sabbath mode	•
Party mode	•
Holiday mode	•
<b>Fridge/Fridge section</b>	
No. of shelves	5
of which illuminated	2
No. of crisper drawers	1
Dry back wall	CleanSteel
FlexiTray	•
Number of inner door racks for tinned food	3
Door rack for bottles	1
Door shelves	4
<b>Freezer/Freezer section</b>	
Number of freezer drawers	3
of which on runners	2
<b>Safety</b>	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm	•

KFNS 7784 D

Built-in fridge-freezer combination

FlexiLight 2.0, DynaCool, NoFrost and FlexiTray for maximum convenience.



EAN: 4002516420774 / Material number: 11738320 / Old Material Number: 38778401AUS

Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•
<b>Technical data</b>	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1770
Niche height in mm max.	1788
Niche depth in mm	550
Appliance width in mm	559
Appliance height in mm	1770
Appliance depth in mm	544
Weight in kg	67,9
Climate class	SN-T
Total usable capacity in l	243
Current consumption (mA)	0
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Replacing lamps	Service
<b>Accessories included</b>	
Egg tray	•