


DAS 4940
Slimline cooker hood
for installation in narrow wall units with EasySwitch controls




- Perfect combination with Con@ctivity-enabled hobs
- Light design – transparent glass panel, 90 cm wide
- LED strip for uniform lighting
- Efficient filtration- 10-ply stainless-steel grease filter
- Recirculation mode – Active AirClean or Longlife AirClean filter

EAN: 4002516496373 / Material number: 11862280 / Old Material Number: 28S4940TD

Construction type	
Slimline cooker hood	•
Operating modes	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
Active charcoal filter (order separately)	DKF 31-P, DKF 31-R
Design	
Colour	Transp. glass
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Touch-on-glass controls	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Easy-to-clean canopy interior – CleanCover	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A++
ECO motor	•
PowerManagement system	•
Annual energy consumption in kWh/year	24,8
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	B
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
Lighting	
LED	•
Number x W	1 x 3 W
Light intensity in lx	285 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
Fan	
Dual-action fan	•
DC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	200
Air throughput in Level 2 (m ³ /h) according to EN 61591	290
Air throughput in Level 3 (m ³ /h) according to EN 61591	400
Air throughput in Booster level (m ³ /h) according to EN 61591	625
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	36,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	44,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	51,0


DAS 4940
Slimline cooker hood
for installation in narrow wall units with EasySwitch controls



EAN: 4002516496373 / Material number: 11862280 / Old Material Number: 28S4940TD

Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	62,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	22,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	30,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	38,0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	48,0
Recirculation	
Air throughput in Level 1 (m ³ /h) according to EN 61591	175
Air throughput in Level 2 (m ³ /h) according to EN 61591	270
Air throughput in Level 3 (m ³ /h) according to EN 61591	425
Air throughput in Booster level 1 (m ³ /h) according to EN 61591	610
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	41,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	50,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	61,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	70,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	28,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	36,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	47,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	56,0
Safety	
Safety switch-off	•
Single-ply safety glass (ESG)	•
Technical data	
Canopy width in mm	861
Canopy height in mm	68
Canopy depth in mm	307
Minimum height above electric hobs in mm	450
Net weight in kg	15,0
Length of supply lead in m	1,5
Standard plug fitted	•
Total rated load in kW	0,08
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Installation notes	
Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Fitting template	•



DAS 4940
Slimline cooker hood
for installation in narrow wall units with EasySwitch controls



EAN: 4002516496373 / Material number: 11862280 / Old Material Number: 28S4940TD

Accessories included	
Non-return flap	•
Optional accessories	
Active charcoal filter	Nein

DAS 4940
Slimline cooker hood
for installation in narrow wall units with EasySwitch controls



DAS4940, Installation drawings

- 1) Extraction, recirculation with conversion kit DUU 150.,
- 2) Alternative ducting connection to the rear.,
- 3) Accessory DSM module.,
- 4) The wall unit can be fitted with a partition after installation. The slots for the grease filters and, in recirculation mode, for the odor filters must remain accessible., The height of the wall unit and the cut-out dimensions must take into account any accessories fitted (e.g. silencer, recirculation hood conversion kit, DSM module)