

B 4826 FashionMaster
Steam ironing system
with display and 2-level ironing board fan for perfect ironing results.



- Convenient and easy to set up/store – 1-2 lift system
- Convenient ironing thanks to fan power level 2
- Top-class ironing results thanks to active ironing board
- Professional results thanks to 4.0 bar steam pressure
- Uniform steam distribution – Miele honeycomb soleplate

EAN: 4002516526506 / Material number: 11977940 / Old Material Number: 13482621GB

Design	
Iron colour	Anthracite/lotus white
Ironing board cover colour	Tayberry red
Display	1-line text display
Perfect ironing results	
Honeycomb soleplate	•
Steam pressure in bar	4,0
Steam quantity in g/min	100
Vertical steam	•
Steam starting from temperature level	2
Steam burst	•
Continuous steam	•
Active ironing table (inflation and suction function)	•
Suction function	•
2-stage fan	•
Non-stick soleplate	•
Proven virus hygiene	•
Time-saving ironing	
Water container volume in l	1,25
Removable water container	•
Permanently refillable water container	•
Multi-layer ironing	•
User convenience	
All-in-one	•
1-2 Lift system	•
Variable height adjustment with gas pressure stay, in mm	830-1020
Castors gentle on the floor	•
Ironing board with Comfort Zone	•
Fan safety switch-on/switch-off	•
Fan memory function	•
Choice of language	•
Guided first-time use	•
Guided descaling	•
Automatic descaling	•
Automatic rinsing	•
Storage compartment for iron	•
Storage compartment for mains cable and accessories	•
Safety	
CoolDown function	•
AutoOff function	•
Technical data	
Dimensions in mm (width)	470
Dimensions in mm (height)	970
Dimensions in mm (depth)	1480
Dimensions in mm (width), folded	470
Dimensions in mm (height), folded	1280
Dimensions in mm (depth), folded	370
Frequency in Hz	50-60
Accessories included	
Non-stick soleplate	•

B 4826 FashionMaster
 Steam ironing system
 with display and 2-level ironing board fan for perfect ironing results.



EAN: 4002516526506 / Material number: 11977940 / Old Material Number: 13482621GB

Steam hose holder

•

Test strips for determining water hardness

•

Descaling tablets

•

Available display languages

Available display languages via MultiLingua

bahasa malaysia, dansk,
 deutsch, english (AU),
 english (GB), english
 (US), español, français,
 hrvatski, italiano, magyar,
 nederlands, norsk, polski,
 portugês, русский,
 română, slovenčina,
 slovenščina, srpski,
 suomi, svenska, türkçe,
 українська, čeština,
 ελληνικά,