

## PUR 98 D

### Island cooker hood

with energy-efficient LED lighting and light-touch switches for easy use.



- Timeless design – stainless steel canopy 898 mm wide
- Powerful – 650 m<sup>3</sup>/h in Booster level
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – for extraction or recirculation

EAN: 4002516585794 / Material number: 12050650 / Old Material Number: 28410858GB

|   |                    |
|---|--------------------|
| <b>Construction type</b>  |                    |
| Island cooker hood  | •                  |
| <b>Construction type and design</b>   |                    |
| Colour  | Stainless steel    |
| <b>Operating modes</b>  |                    |
| Type of air guide   | Can be retrofitted |
| <b>User convenience</b>   |                    |
| Electronic controls   | •                  |
| <b>Efficiency and sustainability</b>  |                    |
| Energy efficiency class (A+++ – D)  | A                  |
| Annual energy consumption in kWh/year                                       | 51,8               |
| Fluid dynamic efficiency class  | A                  |
| Lighting efficiency class   | A                  |
| Grease filtering efficiency class   | A                  |
| <b>Filter system</b>  |                    |
| Number of dishwasher-safe stainless steel grease filters (10-ply)           | 3                  |
| <b>Lighting</b>   |                    |
| Number x W  | 4 x 3 W            |
| Light intensity in lx   | 500 lx             |
| Colour temperature in K   | 3000 Kelvin        |
| <b>Fan</b>  |                    |
| Dual-action fan   | •                  |
| AC motor  | •                  |
| <b>Exhaust air</b>  |                    |
| Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591         | 280                |
| Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591         | 330                |
| Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591         | 400                |
| Air throughput in Booster level (m <sup>3</sup> /h) according to EN 61591   | 650                |
| Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3              | 48,0               |
| Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3              | 53,0               |
| Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3              | 57,0               |
| Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3             | 69,0               |
| Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13      | 31,0               |
| Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13      | 35,0               |
| Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13      | 39,0               |
| Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13     | 51,0               |
| <b>Recirculation</b>  |                    |
| Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591         | 190                |
| Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591         | 270                |
| Air throughput in Intensive level (m <sup>3</sup> /h) according to EN 61591 | 460                |
| Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591         | 330                |

PUR 98 D  
Island cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002516585794 / Material number: 12050650 / Old Material Number: 28410858GB

|  |      |
|--|------|
| Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3                           | 57,0 |
| Noise power level in Intensive level (dB(A) re 1 pW) according to EN 60704-3             | 73,0 |
| Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3                           | 62,0 |
| Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3                           | 66,0 |
| Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13                   | 40,0 |
| Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13                   | 45,0 |
| Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13                   | 49,0 |
| Noise pressure level in Intensive level (dB(A) re 20 µPa) according to EN 60704-2-13     | 56,0 |
| <b>Safety</b>  |      |
| Safety switch-off  | •    |
| <b>Technical data</b>  |      |
| Overall height for vented and external in in. (mm)                                       | 690  |
| Canopy width in mm   | 898  |
| Overall height for extraction mode and external mode cooker hoods in mm                  | 990  |
| Canopy height in mm  | 70   |
| Overall height for recirculation in in. (mm)   | 750  |
| Canopy depth in mm   | 598  |
| Overall height for recirculation mode cooker hoods in mm                                 | 1060 |
| Minimum height above electric hobs in mm   | 450  |
| Net weight in kg   | 34,0 |
| Hard-wired connection  | •    |
| Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm | 650  |
| Total rated load in kW   | 0,23 |
| Voltage in V   | 230  |
| Fuse rating in A   | 10   |
| Number of phases   | 1    |
| Frequency in Hz  | 50   |
| <b>Installation notes</b>  |      |
| Extraction ducting connection at top   | •    |
| Diameter of exhaust duct in mm   | 150  |
| Telescopic chimney   | •    |
| <b>Accessories included</b>  |      |
| Non-return flap  | •    |
| <b>Optional accessories</b>  |      |
| Active charcoal filter   | Nein |