

PFD 400 [WB SPEED]

Freestanding fresh water dishwasher
with baskets for restaurants, schools and bakeries.



- Max. cleaning performance*: 285 plates/h
- Versatile processing of two wire or plastic baskets per cycle
- Excellent user convenience with touch display – M Touch Basic
- Always the right programme – item-specific solutions
- First-class results thanks to freshwater wash system

* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002516577416 / Material number: 12066640 / Old Material Number: 61040010EXP

Construction type and design	
Construction type	Freestanding dishwasher, front loader
Model	Speed
Wash system	Fresh water front loader
Number of levels	2
Front	Stainless steel
Lid	Stainless Steel
Side panels	Stainless steel
Application	
Suitable for small restaurants/bars	•
Suitable for hospitality industry	•
Suitable for guesthouses	•
Suitable for canteens	•
Suitable for offices	•
Suitable for sports clubs	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Circulation pump Qmax in l/min.	390
Shortest programme duration in min.	8
Maximum final rinse temperature in °C	70
Cleaning performance, plates/h	285
Cleaning performance, baskets/h	15
Possible to wash plastic baskets on 2 levels	•
Service life in wash cycles	28000
Controls	
Max. delay start in h	24
Time left display	•
Programmes [number]	9
Programme sequence indicator	•
Choice of display language	•
Language-neutral operation	•
Standard electrical connection	
Electrical connection	3N AC 400V 50HZ
Heater rating in kW	8,50
Total connected load in kW	8,90
Fuse rating in A	16
Length of mains connection cable in m	1,90
Possible voltage variant 1	
Electrical connection	AC 230V 50HZ
Heater rating in kW	3,00
Total connected load in kW	3,40
Fuse rating in A	16
Water connection/drainage	
Cold or hot water [number]	1
Required flow pressure in bar	0,40-10,00
Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•

PFD 400 [WB SPEED]

Freestanding fresh water dishwasher
with baskets for restaurants, schools and bakeries.



EAN: 4002516577416 / Material number: 12066640 / Old Material Number: 61040010EXP

Maximum water hardness in mmol/l	10,70
Water protection system	Waterproof system
Water consumption per wash cycle in l	17,50
Length of water inlet hose in cm	170
Length of water drain hose in cm	150
Dimensions and weight	
External dimensions, height in mm	820
External dimensions with lid, height in mm	835
External dimensions, net width in mm	598
External dimensions, net depth in mm	598
External dimensions, gross height in mm	920
External dimensions, gross width in mm	670
External dimensions, gross depth in mm	740
Usable space in wash cabinet, height in mm	559
Usable space in wash cabinet, width in mm	536
Usable space in wash cabinet, depth of upper basket	474
Usable space in wash cabinet, depth of lower basket in mm	516
In-feed height above floor in mm	216
Required niche width in mm	600
Net weight [kg]	75
Gross weight in kg	85
Maximum floor loading in N	1200
Emissions data	
Emissions – sound pressure at workplace	47 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	59,0
Heat dissipation into the room in MJ/h	1,44
Programmes	
Universal	•
Short	•
Hygiene	•
Cold/Pre-wash	•
Glasses	•
Beer glasses	•
Plastics	•
Energy save/Eco	•
Intensive	•
Reactivation	•
Drainage	•
Basket design	
2 x E 816 inserts for plates	•
1 x APFD 215 upper basket	•
1 x APFD 220 lower basket for inserts	•
2 x APFD 420 insert for cutlery	•
Height-adjustable upper basket	•
Combinable with APFD 210 bottle basket	•
Features	
Drying	without
1 combi dispenser in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made from high-quality stainless steel	•
In-door salt container	•

PFD 400 [WB SPEED]

Freestanding fresh water dishwasher
with baskets for restaurants, schools and bakeries.



EAN: 4002516577416 / Material number: 12066640 / Old Material Number: 61040010EXP

Perfect GlassCare	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Optical interface	•
Highly effective filter system	•
A wide range of accessories (optional)	•
Connection options	
External dispensing module for cleaning agent or rinsing agent	•
Standards, certs, symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
Splash-protection IPX1	•
EMC radio suppressed	•
DIN 10512	•
DIN EN 17735	•