

Complete C2 PowerLine - SFAF3

Cylinder vacuum cleaner

With high suction power and telescopic tube for thorough, convenient vacuuming.



- High suction power – 890 W
- Versatile applications – universal floorhead
- Easy vacuuming of larger areas with 10 m operating radius
- Convenient and versatile with three integrated accessories

EAN: 4002516580201 / Material number: 12079050 / Old Material Number: 41FAF300ZA

Construction type	
Cylinder vacuum cleaner with dustbag	•
Product brand	Complete C2
Motor type	PowerLine
Product type	SFAF3
Appliance Colour	Mango red
User convenience	
Electronic suction power control	6-stage rotary selector
Ergonomic carrying handle	•
Ergonomic handle	•
Silence system	•
Suction tube	Comfort telescopic tube
Park system for pauses during vacuuming	•
Park system	on both sides
Efficiency and sustainability	
Nominal power consumption in W	890
Mobility	
Castors with steel shaft, gentle on floors	•
3-point manoeuvrability	•
Operating radius in m	10
Cable length in m	6,5
Filter system	
Vacuum cleaner bag type	HyClean GN
Dustbag volume in l	4,5
Dustbag change indicator	•
Exhaust filter	AirClean Plus filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic dustbag positioning	•
All-round furniture protection strip	•
Technical data	
Max. power	890
Volume in dB	80,0
Width in mm	487
Height in mm	227
Weight in kg	7,0
Accessories included	
Three-piece accessory set	Integrated
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush with synthetic bristles	•
Floorhead SBD 355-3	•
Filter	AirClean Plus filter
Cleaning tool	No