

Duoflex HX1 Total Care

Cordless stick vacuum cleaners

powerful | Grab & Go | light and compact | comprehensive accessory set



- Lithium-ion battery: up to 55 minutes running time with a single charge*
- Convenient Grab & Go function thanks to the SpeedLock system wall bracket
- Incl. Electro Compact brush for removing pet hair
- Intelligent electrobrush with automatic power adjustment
- Modern design combined with high-quality feel
- 99.99 %** dust retention capacity with Hygiene filter
- incl. flexible suction hose and flexible, long crevice nozzle
- Incl. flexible universal brush for cleaning sensitive surfaces
- Light and compact: 3.1 kg / 0.3 l dust container
- As powerful as a conventional Miele vacuum cleaner***

* Valid for power level 1 without connected electrobrush.

** In accordance with IEC 62885-4

*** Cleaning performance compared with a Miele Complete C3 cylinder vacuum cleaner (SGEF3) with STB 305-3 turbobrush (dust pickup from carpet and hard floor with crevices, fibre pickup from carpet). In accordance with IEC 62885-2.

EAN: 4002516715337 / Material number: 12377740 / Old Material Number: 41QLL036EU1

| | |
|---------------------------------------|--------------------------|
| Construction type | |
| Cordless stick vacuum cleaners | • |
| Product brand | Duoflex HX1 |
| Motor type | Digital Efficiency Motor |
| Product type | SQLL0 |
| Construction type and design | |
| Colour | Obsidian black |
| Cleaning | |
| Vortex Technology | • |
| User convenience | |
| Electronic suction power control | Buttons / 2 levels |
| Wall bracket | Speedlock |
| SpeedLock system | SpeedLock system |
| Accessory storage | HX-AH 20 |
| Filter system | |
| ComfortClean | • |
| Dustbag volume in l | 0,3 |
| Technical data | |
| Battery type | Li-ion |
| Nominal battery capacity in mAh | 2500 |
| Volume in dB | 79,0 |
| Width in mm | 260 |
| Height in mm | 1250 |
| Weight in kg | 3,1 |
| Running time MIN-stage PowerUnit solo | 55 |
| Cleaning area in m ² | 60 |
| Recharging time in min. | 210 |
| Nominal rating in W | 160 |
| Accessories included | |
| Cleaning tool | Integrated |
| MultiFloor electrobrush HX-EB 20 | • |
| HX-DB dusting brush | • |
| HX-UN upholstery nozzle | • |
| HX-CN crevice nozzle | • |
| Universal brush HX-UB | • |
| Flexible crevice nozzle XL HX-CNXL | • |
| Flexible suction hose HX-FSH 20 | • |
| Electro Compact HX-EC 20 | • |