

## G 7210 SC

Freestanding dishwashers  
with 3D MultiFlex tray for maximum convenience.



- Best energy efficiency class A – energy-saving and eco-friendly
- Completely dry – Miele AutoOpen drying
- Perfect results in less than one hour – QuickPowerWash
- Fresh water dishwashers – from ?? in the Automatic programme
- Convenient, great results and perfect for everyday use – ExtraComfort baskets

EAN: 4002516758662 / Material number: 12462750 / Old Material Number: 21721016ZA

<b>Model</b>	
Freestanding dishwasher	•
60 cm dishwasher	•
<b>Design</b>	
Control panel colour	Brilliant White
Control panel version	Straight fascia
Control type	Programme selector button
Display	1-line text display
Display colour	White
MultiLingua	•
<b>Convenience</b>	
Operating noise dB(A) re 1 pW	44
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	Display
Display language selection	•
<b>Efficiency and sustainability</b>	
Power rating in standby mode in W	0,30
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
<b>Quality of results</b>	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Recirculation Turbothermic drying	•
BrilliantGlassCare	•
<b>Wash programmes</b>	
ECO	•
Automatic	•
ComfortWash 45 °C	•
Intensive 75 °C	•
PowerWash	•
ComfortWash+ 55 °C	•
Gentle	•
QuickPowerWash	•
ExtraQuiet 39 dB(A)	•
Appliance care	•
Rinse out salt	•
<b>Dishwashing options</b>	
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
<b>Basket design</b>	
Cutlery loading	3D MultiFlex tray
FlexCare glass holder	2

G 7210 SC  
Freestanding dishwashers  
with 3D MultiFlex tray for maximum convenience.




EAN: 4002516758662 / Material number: 12462750 / Old Material Number: 21721016ZA

FlexCare cup rack	1
Basket design	ExtraComfort
MultiClip	•
FlexCare Glass & Bottle	•
XL Assist	•
<b>Safety</b>	
Waterproof system	•
Filter indicator light	•
Safety lock	•
<b>Technical data</b>	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	845
Niche height maximal in mm	880
Niche depth in mm	600
Appliance width in mm	598
Appliance height in mm	845
Appliance depth in mm	600
Depth with door open in cm	119,5
Net weight in kg	56,0
Total rated load in kW	2,00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1,50
Length of water drain hose in cm	1,50
Length of supply lead in m	1,70
<b>Available display languages</b>	
Available display languages via MultiLingua	deutsch, english, español, français, italiano, nederlands, português, türkçe
<b>Accessories included</b>	
1 x UltraTabs box (20 tabs)	•
Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price	•

G 7210 SC

Freestanding dishwashers  
with 3D MultiFlex tray for maximum convenience.



G7000, free standing dishwasher, 60cm (installation drawing)