

## Duoflex HX1 CarCare

### Cordless stick vacuum cleaners

powerful | Grab & Go | light and compact | attachment for easily vacuuming cars



- Lithium-ion battery: up to 55 minutes running time with a single charge\*
- As powerful as a conventional Miele vacuum cleaner\*\*
- SpeedLock: quick change between complete and hand-held unit
- Light and compact: 3.1 kg / 0.3 l dust container
- Intelligent electrobrush with automatic power adjustment
- incl. flexible suction hose and flexible, long crevice nozzle
- Modern design: Casa grey w/ applications in space grey + high-quality feel
- 99.99 %\*\*\* dust retention capacity with Hygiene filter

\* Valid for power level 1 without connected electrobrush.  
 \*\* Cleaning performance compared with a Miele Complete C3 cylinder vacuum cleaner (SGEF3) with STB 305-3 turbobrush (dust pickup from carpet and hard floor with crevices, fibre pickup from carpet). In accordance with IEC 62885-2.  
 \*\*\* In accordance with IEC 62885-4

EAN: 4002516785767 / Material number: 12532820 / Old Material Number: 41QLL039EU1

<b>Construction type</b>	
Cordless stick vacuum cleaners	•
Product brand	Duoflex HX1
Motor type	Digital Efficiency Motor
Product type	SQLL0
<b>Construction type and design</b>	
Colour	Casa grey
<b>Cleaning</b>	
Vortex Technology	•
<b>User convenience</b>	
Electronic suction power control	Buttons / 2 levels
SpeedLock system	SpeedLock system
Accessory storage	HX-AH 20
<b>Filter system</b>	
ComfortClean	•
Dustbag volume in l	0,3
<b>Technical data</b>	
Battery type	Li-ion
Nominal battery capacity in mAh	2500
Volume in dB	79,0
Width in mm	260
Height in mm	1250
Weight in kg	3,1
Running time MIN-stage PowerUnit solo	55
Cleaning area in m <sup>2</sup>	60
Recharging time in min.	210
Nominal rating in W	160
<b>Accessories included</b>	
Cleaning tool	Integrated
MultiFloor electrobrush HX-EB 20	•
HX-DB dusting brush	•
HX-UN upholstery nozzle	•
HX-CN crevice nozzle	•
Flexible crevice nozzle XL HX-CNXL	•
Flexible suction hose HX-FSH 20	•