

H 7264 BP

Pećnica

u savršeno usklađenoj izvedbi sa zaslonom s tekstom, umreženjem i pirolizom.



- Zaslon s prikaz. teksta s uprav. senzorima – DirectSensor S
- Manje čišćenja – Piroliza
- Posebno mekana tijesta i hrskava korica – Klimatsko pečenje
- Uređaj koji se može umrežiti s WLAN – Miele@home
- Sasvim jednostavno do savršenih rezultata – Automatski programi



EAN: 4002516132523 / Materijal: 11104230 / Stari broj materijala: 22726425D

Izvedba i dizajn	
Ugradbena pećnica	•
Boja	Opsidijan crna
VitroLine	•
Prednosti	
Brzo zagrijavanje	•
Načini rada	
Odmrzavanje	•
Automatski programi	•
Automatika pečenja	•
Eco vrući zrak	•
Roštijl	•
Vrući zrak plus	•
Intenzivno pečenje	•
Klimatsko pečenje	•
Klimatsko pečenje s vrućim zrakom plus	•
Gornji i donji grijač	•
Donji grijač	•
Roštijl s kruženjem zraka	•
Komfor pri korištenju	
Umrežavanje s Miele@home	•
Zaslon	DirectSensor S
SoftOpen	•
SoftClose	•
MultiLingua	•
Prikaz dnevnog vremena	•
Usklađivanje sata	•
Podsjetnik minuta	•
Programiranje vremena početka pripreme	•
Programiranje vremena završetka pripreme	•
Programiranje trajanja pripreme	•
Prikaz stvarne temperature	•
Prikaz željene temperature	•
Signalni ton pri postizanju potrebne temperature	•
Preporučena temperatura	•
Individualne postavke	•
Učinkovitost i održivost	
Razred energetske učinkovitosti (A+++ – D)	A+
Potrošnja električne energije u stanju isključenosti u W	0,5
Potrošnja električne energije u stanju pripravnosti u W	1,0
Potrošnja električne energije u umreženoj pripravnosti u W	2,0
Trajanje do automatskog prebacivanja u stanje spremno za rad u min	20
Trajanje do automatskog prebacivanja u umreženo stanje spremno za rad u min	20
Trajanje do automatskog prebacivanja u stanje isključenosti u min	20
Komfor pri održavanju	
Pirolitičko samočišćenje	•
Katalizator	•
Preklopni grijač roštilja	•

H 7264 BP

Pećnica

u savršeno usklađenoj izvedbi sa zaslonom s tekstom, umreženjem i pirolizom.



EAN: 4002516132523 / Materijal: 11104230 / Stari broj materijala: 22726425D

CleanGlass vrata

•

#### Sigurnost

Sustav hlađenja s hladnom prednjom stranom uređaja

•

Sigurnosno isključivanje

•

Blokada uključivanja

•

Zaključavanje vrata pri uporabi pirolize

•

#### Tehnički podaci

Volumen prostora za pripremu jela u l

76

Broj razina umetanja

5

Broj razina umetanja prostor za pripremu 1

5

Broj razina umetanja prostor za pripremu 2

5

Oznaka razina umetanja

•

Osvjetljenje prostora za pripremu jela

1 halogena sijalica

Temperature u °C

30–300

Min. temperature u °C

30

Maks. temperature u °C

300

Min. širina niše u mm

560

Maks. širina niše u mm

568

Min. visina niše u mm

590

Maks. visina niše u mm

595

Dubina niše u mm

550

Širina uređaja u mm

595

Visina uređaja u mm

596

Dubina uređaja u mm

568

Težina u kg

47,0

Ukupna priključna vrijednost u kW

3,60

Napon u V

220-240

Frekvencija u Hz

50

Osigurač u A

16

Broj faza

1

Priključni kabel s mrežnim utikačem

•

Duljina električnog kabela u m

1,50

Zamjena rasvjetnog tijela

Kupac

#### Isporučeni pribor

Lim za pečenje s PerfectClean slojem HBB 71

1

Univerzalni lim s PerfectClean slojem HUBB 71

1

Rešetka za pečenje i roštilj PyroFit

1

FlexiClip vodilice PyroFit (par)

1

Uklonjive bočne vodilice s PyroFit (par)

1

Tablete za uklanjanje kamenca

2

#### Raspoloživi jezici na zaslonu

Raspoloživi jezici na zaslonu s MultiLingua

bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, português, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,


H 7264 BP

Pećnica

u savršeno usklađenoj izvedbi sa zaslonom s tekстом, umreženjem i pirolizom.



installation H7000 XL, installation drawing



side view H7000 XL, installation drawings




built-in H7000 XL, installation drawing




Installation H7000 XL underframe, installation drawings


H2x6x-1B/BP/E/EP/1/P, H2850BP, H7x6xB/BP/BPX, H2x6xB, installation drawings




H7000 handle, installation drawing



H7000 handle, glass, installation drawings



Installation H7000 BM XL, installation drawings




side view Kombi BM XL, installation drawings

H 7264 BP

Pečnica

u savršeno usklađenoj izvedbi sa zaslonom s tekstom, umreženjem i pirolizom.



Installation Kombi BM XL, installation drawings