

H 7440 BM

Kompaktna pećnica s mikrovalovima

u savršeno usklađenoj izvedbi s auto. programima i kombini. načinima rada.



- Veliki zaslon s upravljanjem senzorima – DirectSensor
- Lako čišćenje – Uz PerfectClean i lan strukturu
- Ravnomjerni i brzi rezultati – Quick & Gentle
- Uređaj koji se može umrežiti s WLAN – Miele@home
- S jednim pritiskom tipke do cilja – Brzi MV i Tipka za kokice

EAN: 4002516132622 / Materijal: 11104340 / Stari broj materijala: 22744036D

Izvedba	
Boja uređaja	Grafitno siva
Izvedba i dizajn	
Ugradbena pećnica s mikrovalovima	•
VitroLine	•
Prednosti	
Quick & Gentle	•
Brzo zagrijavanje	•
Prethodno zagrijavanje	•
Održavanje topline	•
Načini rada	
Vrući zrak plus	•
Mikrovalovi	•
Mikrovalovi s vrućim zrakom plus	•
Mikrovalovi s roštiljem	•
Mikrovalovi s roštiljem s kruženjem zraka	•
Mikrovalovi s automatskim pečenjem	•
Automatika pečenja	•
Roštilj s kruženjem zraka	•
Roštilj	•
Eco vrući zrak	•
Odmrzavanje	•
Automatski programi	•
Nacionalni automatski programi	•
Posebne primjene	•
Komfor pri korištenju	
Umrežavanje s Miele@home	•
Zaslon	DirectSensor
MultiLingua	•
Prikaz dnevnog vremena	•
Prikaz datuma	•
Podsjetnik minuta	•
SoftOpen	•
SoftClose	•
Programiranje trajanja pripreme	•
Prikaz stvarne temperature	•
Preporučena temperatura	•
3 u 1	Pećnica, Mikrovalna, Pećnica + mikrovalovi
Osobni programi	•
Individualne postavke	•
Popcorn funkcija	•
Brzi mikrovalovi	•
Usklađivanje sata	•
Programiranje vremena početka pripreme	•
Programiranje vremena završetka pripreme	•
Prikaz željene temperature	•
Signalni ton pri postizanju potrebne temperature	•

H 7440 BM

Kompaktna pećnica s mikrovalovima

u savršeno usklađenoj izvedbi s auto. programima i kombini. načinima rada.



EAN: 4002516132622 / Materijal: 11104340 / Stari broj materijala: 22744036D

Preporučena snaga mikrovalova

•

Učinkovitost i održivost

Iskorištavanje preostale topline

•

Potrošnja električne energije u stanju isključenosti u W

0,5

Potrošnja električne energije u stanju pripravnosti u W

1,0

Potrošnja električne energije u umreženoj pripravnosti u W

2,0

Trajanje do automatskog prebacivanja u stanje spremno za rad u min

20

Trajanje do automatskog prebacivanja u umreženo stanje spremno za rad u min

20

Trajanje do automatskog prebacivanja u stanje isključenosti u min

20

Komfor pri održavanju

Prostor za pripremu jela od plemenitog čelika lanene strukture i s PerfectClean slojem

•

Preklopni grijač roštilja

•

CleanGlass vrata

•

Sigurnost

Sustav hlađenja s hladnom prednjom stranom uređaja

•

Sigurnosno isključivanje

•

Blokada uključivanja

•

Blokada tipki

•

Tehnički podaci

Širina uređaja u mm

595

Volumen prostora za pripremu jela u l

43

Broj razina umetanja

3

Broj razina umetanja prostor za pripremu 1

3

Broj razina umetanja prostor za pripremu 2

3

Osvjetljenje prostora za pripremu jela

1 LED sijalica

Napon u V

220-240

Osigurač u A

16

Temperature u °C

30–250

Broj faza

1

Min. temperature u °C

30

Maks. temperature u °C

250

Elektronički regulirana snaga mikrovalova

•

Razine snage mikrovalova u W

Min. širina niše u mm

560

Maks. širina niše u mm

568

Min. visina niše u mm

450

Maks. visina niše u mm

452

Dubina niše u mm

550

Visina uređaja u mm

456

Dubina uređaja u mm

562

Težina u kg

36,0

Ukupna priključna vrijednost u kW

2,70

Frekvencija u Hz

50

Priključni kabel s mrežnim utikačem

•

Duljina električnog kabela u m

2,00

H 7440 BM

Kompaktna pećnica s mikrovalovima

u savršeno usklađenoj izvedbi s auto. programima i kombini. načinima rada.



EAN: 4002516132622 / Materijal: 11104340 / Stari broj materijala: 22744036D

Zamjena rasvjetnog tijela

Servisna služba

Isporučeni pribor

Rešetka za pečenje i roštilj s PerfectClean slojem

1

Staklena posuda

1

Raspoloživi jezici na zaslonu


Raspoloživi jezici zna zaslonu s MultiLingua

bahasa malaysia, dansk,
deutsch, english, español,
français, hrvatski, italiano,
magyar, nederlands, norsk,
polski, portugês, русский,
română, slovenčina,
slovenščina, srpski, suomi,
svenska, türkçe, українська,
čeština, ελληνικά,
[?][?][?][?][?][?], [?][?], [?]
[?][?], [?][?][?][?], [?][?][?]


H 7440 BM

Kompaktna pečnica s mikrovalovima


u savršeno usklađenoj izvedbi s auto. programima i kombini. načinima rada.




side view H7000 BM, installation drawings




built-in H7000 BM, installation drawing




built-in H7000 BM build-under, installation drawings




installation H7000 BM, installation drawing




H7000 handle, installation drawing




H7000 handle, glass, installation drawings



Installation H7000 BM XL, installation drawings



side view H7000 BM build-under, installation drawings




side view Kombi BM XL, installation drawings

H 7440 BM

Kompaktna pećnica s mikrovalovima

u savršeno usklađenoj izvedbi s auto. programima i kombini. načinima rada.



Installation Kombi BM XL, installation drawings