

H 7262 B

Pećnica

sa zaslonom s tekстом, termometrom za hranu i PerfectClean



- Zaslon s prikaz. teksta s uprav. senzorima – DirectSensor S
- Lako čišćenje – PerfectClean sloj
- Sasvim jednostavno do savršenih rezultata – Automatski programi
- Puno prostora i fleksibilnosti – 76 l vol. prostora na 5 razina
- Lako korištenje na svim razinama – FlexiClip vodilica

A+

EAN: 4002516358640 / Materijal: 11580950 / Stari broj materijala: 22726244D

Izvedba i dizajn	
Ugradbena pećnica	•
PureLine	•
Boja uređaja	Plemeniti čelik/CleanSteel
Prednosti	
Brzo zagrijavanje	•
Termometar za hranu	s kabelom
Načini rada	
Odmrzavanje	•
Automatski programi	•
Automatika pečenja	•
Eco vrući zrak	•
Načini rada s roštiljem	•
Roštilj	•
Vrući zrak plus	•
Intenzivno pečenje	•
Gornji i donji grijač	•
Donji grijač	•
Roštilj s kruženjem zraka	•
Komfor pri korištenju	
Zaslon	DirectSensor S
SoftOpen	•
SoftClose	•
MultiLingua	•
Prikaz dnevnog vremena	•
Podsjetnik minuta	•
Programiranje vremena početka pripreme	•
Programiranje vremena završetka pripreme	•
Programiranje trajanja pripreme	•
Prikaz stvarne temperature	•
Prikaz željene temperature	•
Signalni ton pri postizanju potrebne temperature	•
Preporučena temperatura	•
Individualne postavke	•
Učinkovitost i održivost	
Razred energetske učinkovitosti (A+++ – D)	A+
Komfor pri održavanju	
Površina od plemenitog čelika/CleanSteel	•
Prostor za pripremu jela s PerfectClean slojem i katalitičkom stražnjom stjenkom	•
Preklopni grijač roštilja	•
CleanGlass vrata	•
Sigurnost	
Sustav hlađenja s hladnom prednjom stranom uređaja	•
Sigurnosno isključivanje	•
Blokada uključivanja	•
Tehnički podaci	
Volumen prostora za pripremu jela u l	76
Broj razina umetanja	5
Broj razina umetanja prostor za pripremu 1	5


H 7262 B

Pećnica

sa zaslonom s tekstom, termometrom za hranu i PerfectClean




H226x-1B/BP/E/EP/IP, H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX installation drawings




H226x-1B/BP/E/EP/IP, H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, installation drawings, GB, AUS




H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, DGC7351, DGC7151, installation drawings




H226x-1B/BP/E/EP/IP, H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, installation drawings




H226x-1B/BP/E/EP/IP, H2x6xB/BP, H7x6xB/BP/BPX, installation drawings




DG2840, DG7x40, DGC7x4x, DG7x6x, DGC7x6x, DGD7635, DGM7x4x, DO7, H28B/BP, H7x4xB/BM/BP, H7x6xB/BP, installation drawing



H226x-1B/BP/E/EP/IP, H2760B/BP, H28x0B/BP, H7x40BM/BMX, H7x6xB/BP/BPX, installation drawings



H2760B/BP, H28x0B/BP, H7x6xB/BP/BPX, installation drawings




H2xxx-1 B/BP/E/IP, H7xxx B/BP/BM/BMX, installation drawings

H 7262 B

Pečnica

sa zaslonom s tekstom, termometrom za hranu i PerfectClean



H2xxx-1 B/BP/E/I/IP, H7xxx B/BP/BM/BMX, installation drawings