

H 7262 B

Pećnica

sa zaslonom s tekстом, termometrom za hranu i PerfectClean




- Zaslon s prikaz. teksta s uprav. senzorima – DirectSensor S
- Lako čišćenje – PerfectClean sloj
- Sasvim jednostavno do savršenih rezultata – Automatski programi
- Puno prostora i fleksibilnosti – 76 l vol. prostora na 5 razina
- Lako korištenje na svim razinama – FlexiClip vodilica




EAN: 4002516358640 / Materijal: 11580950 / Stari broj materijala: 22726244D

Izvedba i dizajn	
Ugradbena pećnica	•
Boja	Plemeniti čelik/CleanSteel
PureLine	•
Prednosti	
Brzo zagrijavanje	•
Termometar za hranu	s kabelom
Načini rada	
Odmrzavanje	•
Automatski programi	•
Automatika pečenja	•
Eco vrući zrak	•
Roštilj	•
Vrući zrak plus	•
Intenzivno pečenje	•
Gornji i donji grijač	•
Donji grijač	•
Roštilj s kruženjem zraka	•
Komfor pri korištenju	
Zaslon	DirectSensor S
SoftOpen	•
SoftClose	•
MultiLingua	•
Prikaz dnevnog vremena	•
Podsjetnik minuta	•
Programiranje vremena početka pripreme	•
Programiranje vremena završetka pripreme	•
Programiranje trajanja pripreme	•
Prikaz stvarne temperature	•
Prikaz željene temperature	•
Signalni ton pri postizanju potrebne temperature	•
Preporučena temperatura	•
Individualne postavke	•
Učinkovitost i održivost	
Razred energetske učinkovitosti (A+++ – D)	A+
Komfor pri održavanju	
Površina od plemenitog čelika/CleanSteel	•
Prostor za pripremu jela s PerfectClean slojem i katalitičkom stražnjom stjenkom	•
Preklopni grijač roštilja	•
CleanGlass vrata	•
Sigurnost	
Sustav hlađenja s hladnom prednjom stranom uređaja	•
Sigurnosno isključivanje	•
Blokada uključivanja	•
Tehnički podaci	
Volumen prostora za pripremu jela u l	76
Broj razina umetanja	5
Broj razina umetanja prostor za pripremu 1	5
Broj razina umetanja prostor za pripremu 2	5


H 7262 B
 Pečnica
 sa zaslonom s tekstom, termometrom za hranu i PerfectClean




installation H7000 XL, installation drawing




installation H7000 XL, installation drawing, GB, AU




side view H7000 XL, installation drawings




built-in H7000 XL, installation drawing




Installation H7000 XL underframe, installation drawings




H7000 handle, installation drawing



Installation H7000 BM XL, installation drawings



side view H7000 XL build-under, installation drawing




side view Kombi BM XL, installation drawings

H 7262 B

Pečnica

sa zaslonom s tekstom, termometrom za hranu i PerfectClean



Installation Kombi BM XL, installation drawings