

H 7262 BP

Pećnica

sa zaslonom s tekстом, termometrom za hranu i pirolizom



- Zaslon s prikaz. teksta s uprav. senzorima – DirectSensor S
- Manje čišćenja – Piroliza
- Sasvim jednostavno do savršenih rezultata – Automatski programi
- Puno prostora i fleksibilnosti – 76 l vol. prostora na 5 razina
- Lako korištenje na svim razinama – FlexiClip vodilica



EAN: 4002516360971 / Materijal: 11581190 / Stari broj materijala: 22726245D

Izvedba i dizajn	
Ugradbena pećnica	•
Boja	Plemeniti čelik/CleanSteel
PureLine	•
Prednosti	
Brzo zagrijavanje	•
Termometar za hranu	s kabelom
Načini rada	
Odmrzavanje	•
Automatski programi	•
Automatika pečenja	•
Eco vrući zrak	•
Roštilj	•
Vrući zrak plus	•
Intenzivno pečenje	•
Gornji i donji grijač	•
Donji grijač	•
Roštilj s kruženjem zraka	•
Komfor pri korištenju	
Zaslon	DirectSensor S
SoftOpen	•
SoftClose	•
MultiLingua	•
Prikaz dnevnog vremena	•
Podsjetnik minuta	•
Programiranje vremena početka pripreme	•
Programiranje vremena završetka pripreme	•
Programiranje trajanja pripreme	•
Prikaz stvarne temperature	•
Prikaz željene temperature	•
Signalni ton pri postizanju potrebne temperature	•
Preporučena temperatura	•
Individualne postavke	•
Učinkovitost i održivost	
Razred energetske učinkovitosti (A+++ – D)	A+
Komfor pri održavanju	
Površina od plemenitog čelika/CleanSteel	•
Pirolitičko samočišćenje	•
Katalizator	•
Preklopni grijač roštilja	•
CleanGlass vrata	•
Sigurnost	
Sustav hlađenja s hladnom prednjom stranom uređaja	•
Sigurnosno isključivanje	•
Blokada uključivanja	•
Zaključavanje vrata pri uporabi pirolize	•
Tehnički podaci	
Volumen prostora za pripremu jela u l	76
Broj razina umetanja	5
Broj razina umetanja prostor za pripremu 1	5

H 7262 BP

Pećnica

sa zaslonom s tekстом, termometrom za hranu i pirolizom



EAN: 4002516360971 / Materijal: 11581190 / Stari broj materijala: 22726245D

Broj razina umetanja prostor za pripremu 2	5
Oznaka razina umetanja	•
Osvjetljenje prostora za pripremu jela	1 halogena sijalica
Temperature u °C	30–300
Min. temperature u °C	30
Maks. temperature u °C	300
Min. širina niše u mm	560
Maks. širina niše u mm	568
Min. visina niše u mm	590
Maks. visina niše u mm	595
Dubina niše u mm	550
Širina uređaja u mm	595
Visina uređaja u mm	596
Dubina uređaja u mm	569
Težina u kg	47,0
Ukupna priključna vrijednost u kW	3,60
Napon u V	220-240
Frekvencija u Hz	50
Osigurač u A	16
Broj faza	1
Priključni kabel s mrežnim utikačem	•
Duljina električnog kabela u m	1,50
Zamjena rasvjetnog tijela	Kupac
Isporučeni pribor	
Lim za pečenje s PerfectClean slojem HBB 71	1
Univerzalni lim s PerfectClean slojem HUBB 71	1
Rešetka za pečenje i roštilj PyroFit	1
FlexiClip vodilice PyroFit (par)	1
Termometar za hranu povezan kabelom	1
Uklonjive bočne vodilice s PyroFit (par)	1
Raspoloživi jezici na zaslonu	
Raspoloživi jezici na zaslonu s MultiLingua	bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, portugûês, русский, romãna, slovenčina, slovensčina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,


H 7262 BP

Pečnica

sa zaslonom s tekstom, termometrom za hranu i pirolizom




installation H7000 XL, installation drawing




installation H7000 XL, installation drawing, GB, AU




side view H7000 XL, installation drawings




built-in H7000 XL, installation drawing




Installation H7000 XL underframe, installation drawings




H7000 handle, installation drawing



Installation H7000 BM XL, installation drawings



side view H7000 XL build-under, installation drawing



side view Kombi BM XL, installation drawings

H 7262 BP

Pećnica

sa zaslonom s tekстом, termometrom za hranu i pirolizom



Installation Kombi BM XL, installation drawings