

## H 2467 B ACTIVE

### Pećnica

modernog dizajna s umreženjem, PerfectClean i FlexiClip vodilicom.



- Zaslon s prikazom teksta s okret. regulatorima – EasyControl Plus
- Lako čišćenje – PerfectClean sloj
- Uređaj koji se može umrežiti s WLAN – Miele@home
- Sasvim jednostavno do savršenih rezultata – Automatski programi
- Za sve što treba biti hrskavo – Način rada AirFry



EAN: 4002516622017 / Materijal: 12144230 / Stari broj materijala: 22246704D

| Izvedba i dizajn                                                                 |                   |
|----------------------------------------------------------------------------------|-------------------|
| Ugradbena pećnica                                                                | •                 |
| Boja                                                                             | Opsidijan crna EL |
| Prednosti                                                                        |                   |
| Brzo zagrijavanje                                                                | •                 |
| Načini rada                                                                      |                   |
| AirFry                                                                           | •                 |
| Automatski programi                                                              | •                 |
| Eco vrući zrak                                                                   | •                 |
| Roštilj                                                                          | •                 |
| Vrući zrak plus                                                                  | •                 |
| Intenzivno pečenje                                                               | •                 |
| Gornji i donji grijač                                                            | •                 |
| Donji grijač                                                                     | •                 |
| Roštilj s kruženjem zraka                                                        | •                 |
| Komfor pri korištenju                                                            |                   |
| Umrežavanje s Miele@home                                                         | •                 |
| Zaslon                                                                           | EasyControl Plus  |
| Multilingua                                                                      | •                 |
| Prikaz dnevnog vremena                                                           | •                 |
| Podsjetnik minuta                                                                | •                 |
| Programiranje vremena početka pripreme                                           | •                 |
| Programiranje vremena završetka pripreme                                         | •                 |
| Programiranje trajanja pripreme                                                  | •                 |
| Prikaz stvarne temperature                                                       | •                 |
| Prikaz željene temperature                                                       | •                 |
| Signalni ton pri postizanju potrebne temperature                                 | •                 |
| Preporučena temperatura                                                          | •                 |
| Individualne postavke                                                            | •                 |
| Učinkovitost i održivost                                                         |                   |
| Razred energetske učinkovitosti (A+++ – D)                                       | A+                |
| Potrošnja električne energije u stanju isključenosti u W                         | 0,5               |
| Potrošnja električne energije u stanju pripravnosti u W                          | 1,0               |
| Potrošnja električne energije u umreženoj pripravnosti u W                       | 2,0               |
| Trajanje do automatskog prebacivanja u stanje spremno za rad u min               | 20                |
| Trajanje do automatskog prebacivanja u umreženo stanje spremno za rad u min      | 20                |
| Trajanje do automatskog prebacivanja u stanje isključenosti u min                | 20                |
| Komfor pri održavanju                                                            |                   |
| Prostor za pripremu jela s PerfectClean slojem i katalitičkom stražnjom stjenkom | •                 |
| CleanGlass vrata                                                                 | •                 |
| Sigurnost                                                                        |                   |
| Sustav hlađenja s hladnom prednjom stranom uređaja                               | •                 |
| Sigurnosno isključivanje                                                         | •                 |
| Blokada uključivanja                                                             | •                 |
| Tehnički podaci                                                                  |                   |
| Volumen prostora za pripremu jela u l                                            | 76                |
| Broj razina umetanja                                                             | 5                 |

## Pećnica

modernog dizajna s umreženjem, PerfectClean i FlexiClip vodicom.




EAN: 4002516622017 / Materijal: 12144230 / Stari broj materijala: 22246704D

|                                               |                                                                                                                                                                                                                                                                    |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Broj razina umetanja prostor za pripremu 1    | 5                                                                                                                                                                                                                                                                  |
| Broj razina umetanja prostor za pripremu 2    | 5                                                                                                                                                                                                                                                                  |
| Oznaka razina umetanja                        | •                                                                                                                                                                                                                                                                  |
| Osvjetljenje prostora za pripremu jela        | 1 halogena sijalica                                                                                                                                                                                                                                                |
| Temperature u °C                              | 30–300                                                                                                                                                                                                                                                             |
| Min. temperature u °C                         | 30                                                                                                                                                                                                                                                                 |
| Maks. temperature u °C                        | 300                                                                                                                                                                                                                                                                |
| Min. širina niše u mm                         | 560                                                                                                                                                                                                                                                                |
| Maks. širina niše u mm                        | 568                                                                                                                                                                                                                                                                |
| Min. visina niše u mm                         | 590                                                                                                                                                                                                                                                                |
| Maks. visina niše u mm                        | 595                                                                                                                                                                                                                                                                |
| Dubina niše u mm                              | 550                                                                                                                                                                                                                                                                |
| Širina uređaja u mm                           | 595                                                                                                                                                                                                                                                                |
| Visina uređaja u mm                           | 596                                                                                                                                                                                                                                                                |
| Dubina uređaja u mm                           | 568                                                                                                                                                                                                                                                                |
| Težina u kg                                   | 42,0                                                                                                                                                                                                                                                               |
| Ukupna priključna vrijednost u kW             | 3,50                                                                                                                                                                                                                                                               |
| Napon u V                                     | 220-240                                                                                                                                                                                                                                                            |
| Frekvencija u Hz                              | 50                                                                                                                                                                                                                                                                 |
| Osigurač u A                                  | 16                                                                                                                                                                                                                                                                 |
| Broj faza                                     | 1                                                                                                                                                                                                                                                                  |
| Priključni kabel s mrežnim utikačem           | •                                                                                                                                                                                                                                                                  |
| Duljina električnog kabela u m                | 1,50                                                                                                                                                                                                                                                               |
| Zamjena rasvjetnog tijela                     | Kupac                                                                                                                                                                                                                                                              |
| <b>Isporučeni pribor</b>                      |                                                                                                                                                                                                                                                                    |
| Lim za pečenje s PerfectClean slojem HBB 71   | 1                                                                                                                                                                                                                                                                  |
| Univerzalni lim s PerfectClean slojem HUBB 71 | 1                                                                                                                                                                                                                                                                  |
| Rešetka za pečenje                            | 1                                                                                                                                                                                                                                                                  |
| FlexiClip vodilice HFC 70-C (par)             | 1                                                                                                                                                                                                                                                                  |
| Uklonjive bočne vodilice (par)                | 1                                                                                                                                                                                                                                                                  |
| <b>Raspoloživi jezici na zaslonu</b>          |                                                                                                                                                                                                                                                                    |
| Raspoloživi jezici na zaslonu s MultiLingua   | bahasa malaysia, dansk,<br>deutsch, english, español,<br>français, hrvatski, italiano,<br>magyar, nederlands,<br>norsk, polski, português,<br>русский, română,<br>slovenčina, slovensčina,<br>srpski, suomi, svenska,<br>türkçe, українська, čeština,<br>ελληνικά, |


## H 2467 B ACTIVE

Pećnica


modernog dizajna s umreženjem, PerfectClean i FlexiClip vodicom.




installation H7000 XL, installation drawing




side view H7000 XL, installation drawings




built-in H7000 XL, installation drawing



Installation H7000 XL underframe, installation drawings



side view H7000 XL build-under, installation drawing



H2465B, H2465BP, H2466B, H2466BP, H2467B, H2467BP, H2468B, H2468BP, H2469B, H2469BP installation drawings