

H 2861-1 BP 125 Edition

Pećnica

u kombiniranom dizajnu s AirFry funk. kao i umrežavanjem i pirolizom.



- Zaslon s prikazom teksta s okret. regulatorima – EasyControl Plus
- Manje čišćenja – Piroliza
- Uređaj koji se može umrežiti s WLAN – Miele@home
- Sasvim jednostavno do savršenih rezultata – Automatski programi
- Za sve što treba biti hrskavo – AirFry

A+

EAN: 4002516769972 / Materijal: 12432450 / Stari broj materijala: 22286195D

Jubilarna ponuda	
Jubilarni modeli 125	•
Izvedba	
Boja uređaja	Plemeniti čelik/CleanSteel
Izvedba i dizajn	
Ugradbena pećnica	•
PureLine	•
Prednosti	
Brzo zagrijavanje	•
Načini rada	
AirFry	•
Automatski programi	•
Eco vrući zrak	•
Načini rada s roštijem	•
Roštij	•
Vrući zrak plus	•
Intenzivno pečenje	•
Gornji i donji grijač	•
Roštij s kruženjem zraka	•
Komfor pri korištenju	
Umrežavanje s Miele@home	•
Zaslon	EasyControl Plus
SoftOpen	•
SoftClose	•
MultiLingua	•
Prikaz dnevnog vremena	•
Podsjetnik minuta	•
Programiranje vremena početka pripreme	•
Programiranje vremena završetka pripreme	•
Programiranje trajanja pripreme	•
Prikaz stvarne temperature	•
Prikaz željene temperature	•
Signalni ton pri postizanju potrebne temperature	•
Preporučena temperatura	•
Individualne postavke	•
Učinkovitost i održivost	
Razred energetske učinkovitosti (A+++ – D)	A+
Potrošnja električne energije u stanju isključenosti u W	0,5
Potrošnja električne energije u stanju pripravnosti u W	1,0
Potrošnja električne energije u umreženoj pripravnosti u W	2,0
Trajanje do automatskog prebacivanja u stanje spremno za rad u min	20
Trajanje do automatskog prebacivanja u umreženo stanje spremno za rad u min	20
Trajanje do automatskog prebacivanja u stanje isključenosti u min	20
Komfor pri održavanju	
Površina od plemenitog čelika/CleanSteel	•
Pirólitičko samočišćenje	•
CleanGlass vrata	•

H 2861-1 BP 125 Edition

Pećnica

u kombiniranom dizajnu s AirFry funk. kao i umrežavanjem i pirolizom.




EAN: 4002516769972 / Materijal: 12432450 / Stari broj materijala: 22286195D

Sigurnost	
Sustav hlađenja s hladnom prednjom stranom uređaja	•
Sigurnosno isključivanje	•
Blokada uključivanja	•
Zaključavanje vrata pri uporabi pirolize	•
Tehnički podaci	
Volumen prostora za pripremu jela u l	76
Broj razina umetanja	5
Broj razina umetanja prostor za pripremu 1	5
Broj razina umetanja prostor za pripremu 2	5
Oznaka razina umetanja	•
Osvjetljenje prostora za pripremu jela	1 halogena sijalica
Temperature u °C	30–300
Min. temperature u °C	30
Maks. temperature u °C	300
Min. širina niše u mm	560
Maks. širina niše u mm	568
Min. visina niše u mm	590
Maks. visina niše u mm	595
Dubina niše u mm	550
Širina uređaja u mm	595
Visina uređaja u mm	596
Dubina uređaja u mm	569
Težina u kg	47,0
Ukupna priključna vrijednost u kW	3,60
Napon u V	220-240
Frekvencija u Hz	50
Osigurač u A	16
Broj faza	1
Priključni kabel s mrežnim utikačem	•
Duljina električnog kabela u m	1,50
Zamjena rasvjetnog tijela	Kupac
Isporučeni pribor	
Lim za pečenje s PerfectClean slojem	1
Perforirani Gourmet i AirFry lim za pečenje s PerfectClean	1
Univerzalni lim s PerfectClean slojem	1
Rešetka za pečenje	1
FlexiClip vodilice (par)	1
Uklonjive bočne vodilice (par)	1
Vaučer za HG71 lim za roštilj i pečenje s PerfectClean	1


H 2861-1 BP 125 Edition

Pećnica


u kombiniranom dizajnu s AirFry funk. kao i umrežavanjem i pirolizom.




installation H7000 XL, installation drawing




side view H7000 XL, installation drawings




built-in H7000 XL, installation drawing



H226x-1B/BP/E/EP/I/IP, H2x6xB/BP, H7x6xB/BP/BPX, installation drawings



DG2840, DG7x40, DGC7x4x, DG7x6x, DGC7x6x, DGD7635, DGM7x4x, DO7, H28B/BP, H7x4xB/BM/BP, H7x6xB/BP, installation drawing



side view H7000 XL build-under, installation drawing