

KMDA 7676 FL-U BlackPerfection

Indukcijska ploča za kuhanje s integriranom napom
s dvije ekstra velike PowerFlex XL ploče za način rada na kruženje zraka



- Najtiši Miele TwoInOne uređaj – Silence motor
- fleksibilna ugradnja – Plug&Play ili vođeno kruženje zraka
- Prostranost – 4 velike zone za kuha. uklj. 2 PowerFlex XL polja
- Automatsko reguliranje stupnjeva ventilatora – Con@ctivity
- U potpunosti crni dizajn za elegantan izgled

EAN: 4002516755951 / Materijal: 12438930 / Stari broj materijala: 26767679D

Izvedba	
Indukcijska ploča za kuhanje s integriranom napom	•
Načini rada	
Vođeno kruženje zraka s dodatnim priborom	DFK-xxxx, DUU 1500, DUU 600
Vođeno kruženje zraka s dodatnim priborom	Kruženje zraka
Ne vođeno kruženje zraka (Plug&Play ugradnja)	Da
Dizajn	
Elegantna staklo-keramička površina	•
Ugradnja u ravnini s radnom površinom	•
Boja staklokeramičke površine	crna
Ugradnja polaganjem na radnu površinu	•
Napa u ravnini površine	•
Boja pokrovne rešetke	Crna
Boja filtra za masnoću	crna
Oprema zona za kuhanje	
Broj zona za kuhanje	4
Broj polja za kuhanje	2
Maksimalni broj posuda za kuhanje	4
PowerFlex zone za kuhanje	
Broj	4
Vrsta	PowerFlex XL zona za kuhanje
Promjer u mm	Ø 150 – 230
Snaga u W	2100
Booster u W	3000
TwinBooster u W	3650
1. Zona za kuhanje/područje za kuhanje	
Položaj	lijevo
Vrsta	PowerFlex XL polje za kuhanje
Dimenzija u mm	230x460
Maks. Booster snaga u W	4800
Maks. snaga u W	3400
Maks. TwinBooster snaga u W	7300
2. Zona za kuhanje/područje za kuhanje	
Položaj	desno
Vrsta	PowerFlex XL polje za kuhanje
Dimenzija u mm	230x460
Maks. Booster snaga u W	4800
Maks. snaga u W	3400
Maks. TwinBooster snaga u W	7300
Komfor pri korištenju	
Miele@home	•
Upravljanje putem senzorskih tipki	ComfortSelect White
Automatska Con@ctivity funkcija	•
Digitalni prikaz razina snage	•
Boja indikatora	Bijela
Automatika zakuhanja	•
Održavanje topline	•

KMDA 7676 FL-U BlackPerfection

Indukcijska ploča za kuhanje s integriranom napom

s dvije ekstra velike PowerFlex XL ploče za način rada na kruženje zraka



EAN: 4002516755951 / Materijal: 12438930 / Stari broj materijala: 26767679D

Stop&Go funkcija	•
Recall funkcija	•
Automatika isključivanja	•
Trajno prepoznavanje posuda	•
Mogućnosti individualne prilagodbe (primjerice zvučni signali)	•
Prikaz zasićenosti aktivnog ugljenog filtra	•
Naknadni rad 5/15 min	•
Zaštita kod brisanja	•
Prikaz zasićenosti filtra za masnoću	•
Podsjetnik minuta	•
CleanCover unutrašnjost nape za jednostavno čišćenje	•
Učinkovitost i održivost	
ECO motor	•
Komfor pri održavanju	
Staklokeramička površina jednostavna za čišćenje	•
Sustav filtracije	
Broj perivih u perilici posuđa Metalni filtri za masnoću od plemenitog čelika (10-slojni)	1
Kruženje zraka	
Protok zraka, mini. stupanj (m ³ /h) prema EN 61591	145
Protok zraka, maks. stupanj (m ³ /h) prema EN 61591	465
Protok zraka, Booster stupanj 1 (m ³ /h) prema EN 61591	510
Zvučna snaga, mini. stupanj (dB(A) re1pW) prema EN 60704-3	47,0
Zvučna snaga, maks. stupanj (dB(A) re1pW) prema EN 60704-3	68,0
Zvučni tlak, mini. stupanj (dB(A) re20μPa) prema EN 60704-2-13	34,0
Zvučna snaga, Booster stupanj 1 (dB(A) re1pW) prema EN 60704-3	70,0
Zvučni tlak, maks. stupanj (dB(A) re20μPa) prema EN 60704-2-13	55,0
Zvučni tlak, Booster stupanj 1 (dB(A) re20μPa) prema EN 60704-2-13	57,0
Sigurnost	
Sigurnosno isključivanje	•
Funkcija zaključavanja	•
Blokada uključivanja	•
Integrirani ventilator za hlađenje	•
Zaštita od pregrijavanja	•
Prikaz preostale topline	•
Priključak za prozorske kontaktne sklopke	•
Tehnički podaci	
Dimenzije u mm (širina)	800
Dimenzije u mm (visina)	238
Dimenzije u mm (dubina)	520
Dimenzije izreza u mm (širina) kod ugradnje polaganjem na radnu površinu	780
Dimenzije izreza u mm (dubina) kod ugradnje polaganjem na radnu površinu	500
Visina ugradnje s priključnom kutijom u mm	238

KMDA 7676 FL-U BlackPerfection

Indukcijska ploča za kuhanje s integriranom napom

s dvije ekstra velike PowerFlex XL ploče za način rada na kruženje zraka




EAN: 4002516755951 / Materijal: 12438930 / Stari broj materijala: 26767679D

Unutarnja dimenzija izreza u mm (širina) kod ugradnje u ravnini s radnom površinom	780
Unutarnja dimenzije izreza u mm (dubina) kod ugradnje u ravnini s radnom površinom	500
Težina u kg	20
Vanjska dimenzija izreza u mm (širina) kod ugradnje u ravnini s radnom površinom	804
Vanjska dimenzija izreza u mm (dubina) kod ugradnje u ravnini s radnom površinom	524
Ukupna priključna vrijednost u kW	7,50
Napon u V	230
Frekvencija u Hz	50-60
Duljina električnog kabela u m	1,6
Isporučeni pribor	
Priključni kabel	Da
Aktivni ugljeni filter za kruženje zraka	•
Plug&Play adapter	•


KMDA 7676 FL-U BlackPerfection

Indukcijska ploča za kuhanje s integriranom napom


s dvije ekstra velike PowerFlex XL ploče za način rada na kruženje zraka



KMDA7676FL-U BlackPerfection, KMDA7876FL-U – flush installation, drilling template, Installation depth 20 cm




KMDA7676FL-U, KMDA7876FL-U – flush installation, drilling template, Installation depth 21 cm, Installation drawing




KMDA7676FL, KMDA7876FL – Side view lying on top – Installation drawing

KMDA7676FL-U, KMDA7876FL-U – surface installation, drilling template, Installation drawing




KMDA7676FL, KMDA7876FL – Installation drawing




KMDA7676FL, KMDA7876FL – Side view lying on top+X – Installation drawing

KMDA7676FL-U, KMDA7876FL-U – surface installation, 21 cm, drilling template, Installation drawing



KMDA7676FL, KMDA7876FL – flush – Installation drawing




KMDA7676FL, KMDA7876FL – Side view flush – Installation drawing


KMDA 7676 FL-U BlackPerfection

Indukcijska ploča za kuhanje s integriranom napom


s dvije ekstra velike PowerFlex XL ploče za način rada na kruženje zraka




KMDA7676FL, KMDA7876FL – Side view flush+X – Installation drawing




KMDA7676FL, KMDA7876FL – Side view lying on top, Plug&Play – Installation drawing




KMDA7676FL, KMDA7876FL – Side view lying on top+X, Plug&Play – Installation drawing




KMDA7676FL, KMDA7876FL – Side view flush, Plug&Play – Installation drawing




KMDA7676FL, KMDA7876FL – Side view flush+X, Plug&Play – Installation drawing




KMDA7676FL, KMDA7876FL – Installation variant 1 Basis -drawing



KMDA7676FL, KMDA7876FL – Installation variant 2 Basis – drawing



KMDA7676FL, KMDA7876FL -Installation variant 3 Basis – drawing




KMDA7676FL, KMDA7876FL – Installation variant 4 Circulating air – drawing


KMDA 7676 FL-U BlackPerfection

Indukcijska ploča za kuhanje s integriranom napom


s dvije ekstra velike PowerFlex XL ploče za način rada na kruženje zraka




KMDA7676FL, KMDA7876FL – Installation variant
5 Circulating air – drawing




KMDA7676FL, KMDA7876FL – Installation variant
6 Circulating air – drawing




KMDA7676FL, KMDA7876FL – Installation variant
13 Circulating air – drawing



KMDA7676FL, KMDA7876FL – Installation variant
14 Circulating air – drawing



KMDA7676FL/FR, KMDA7876FL/FR, Air circulation
(Installation drawing)



KMDA7676FL/FR, KMDA7876FL/FR, Plug&Play
(Installation drawing)