

FNUS 7040 D

Podgradni zamrzivač

s NoFrost, SoftClose i brzim zamrzav. u kompaktnom dizajnu.



- Bez zaleđiv. smr. namirnica – više nikad odmrzav. zahva. NoFrost
- Prigušeno zatvaranje vrata sa SoftClose
- Brzo, nježno zamrzavanje namirnica – Brzo zamrzavanje
- Fleksibilno povećanje prostora za zamrzavanje – VarioRoom



EAN: 4002516779322 / Materijal: 12519380 / Stari broj materijala: 37704010EU1

Kategorija uređaja	
Zamrzivač	•
Izvedba	
Integrirani ugradbeni uređaj	•
Ugradbeni uređaj s mogućnosti podgradnje	•
Smjer otvaranja vrata	desno
Promjenjiv smjer otvaranja vrata	•
Mogućnost postavljanja side-by-side	•
Dizajn	
Osvjetljenje zone za zamrzavanje	LED
Komfor pri korištenju	
Umrežavanje s Miele@home	•
NoFrost	•
VarioRoom	•
SoftClose	•
Upravljanje	
Koncept upravljanja	FreshTouch
Nezavisna regulacija temperature zone za hlađenje i zone za zamrzavanje	Ne
Brzo zamrzavanje	•
Broj temperaturnih zona	1
Šabat način rada	•
Holiday način rada	•
Uređaj/zona za zamrzavanje	
Broj ladica za zamrzavanje	3
Učinkovitost i održivost	
Razred energetske učinkovitosti (A-G)	D
Godišnja potrošnja energije u kWh	149,70
Potrošnja energije u 24 h u kWh	0,41
Sigurnost	
Funkcija zaključavanja	•
Akustični alarm vrata	•
Akustični alarm temperature za zamrzivač	•
Optički alarm vrata	•
Optički alarm temperature	•
Prikaz nestanka mrežnog napona u zamrzivaču	•
Tehnički podaci	
Min. širina niše u mm	600
Maks. širina niše u mm	600
Min. visina niše u mm	820
Maks. visina niše u mm	880
Dubina niše u mm	560
Širina uređaja u mm	597
Visina uređaja u mm	818
Dubina uređaja u mm	550
Težina u kg	36,0
Način pričvršćenja	Fiksna vrata

FNUS 7040 D

Podgradni zamrzivač

s NoFrost, SoftClose i brzim zamrzav. u kompaktnom dizajnu.



EAN: 4002516779322 / Materijal: 12519380 / Stari broj materijala: 37704010EU1

Maks. težina prednje strane vrata dijela za hlađenje izražena u kg 10

Klimatski razred	SN-T
Zona za zamrzavanje sa 4 zvjezdice u l	74
Ukupna iskoristiva zapremnina u l	74
Vrijeme pohrane kod kvara u h	12
Snaga zamrzavanja u kg/24h	8,20
Razred emisije buke koja se prenosi zrakom (A-D)	B
Emisija buke koja se prenosi zrakom u dB(A) re1pW	32
Potrošnja električne energije u miliamperima (mA)	2000
Napon u V	220-240
Osigurač u A	10
Broj faza	1
Frekvencija u Hz	50-60
Duljina električnog kabela u m	2,2

Isporučeni pribor


Posuda za kockice leda

•


FNUS 7040 D

Podgradni zamrzivač


s NoFrost, SoftClose i brzim zamrzav. u kompaktnom dizajnu.




KU7016D, KU7015D, KU7035D, FNUS7040D, Built-under, Einbauskizze, Nischenmaß (installation drawings)



KU7016D, KU7015D, KU7035D, KU7135C, FNUS7040D, FNUS7140C, Built-under, top view (installation drawings)



KU7016D, KU7015D, KU7035D, FNUS7040D, Built-under, side view (installation drawings)



KU7016D, KU7015D, KU7035D, KU7135C, FNUS7140C, Built-under, installation drawing (*footnote) (installation drawings)