

DG 7440

Ugradbena parna pećnica

za zdravu pripremu hrane s automatskim programima, umrežavanjem i Sous-vide.



- Veliki zaslon s upravljanjem senzorima – DirectSensor
- Savršen rezultat – DualSteam tehnologija pare
- Jamstvo uspješne pripreme svakog jela – Automatski programi
- Osvjetljavanje prostora za pripremu jela – 2 LED sijalice
- Uređaj koji se može umrežiti putem WLAN – Miele@home

EAN: 4002516923930 / Materijal: 12867620 / Stari broj materijala: 23744000D

| Izvedba i dizajn                                                       |              |
|------------------------------------------------------------------------|--------------|
| Ugradbena parna pećnica                                                | •            |
| VitroLine                                                              | •            |
| Boja uređaja                                                           | Perla krem   |
| Prednosti                                                              |              |
| Vanjsko stvaranje pare                                                 | •            |
| Priprema jelovnika bez prijenosa okusa                                 | •            |
| Automatski programi s individualnim prilagođavanjem rezultata pripreme | •            |
| Održavanje topline                                                     | •            |
| Načini rada                                                            |              |
| Priprema na pari                                                       | •            |
| Sous-vide                                                              | •            |
| Eco kuhanje na pari                                                    | •            |
| Odmrzavanje                                                            | •            |
| Zagrijavanje                                                           | •            |
| Automatski programi                                                    | •            |
| Nacionalni automatski programi                                         | •            |
| Posebne primjene                                                       | •            |
| Komfor pri korištenju                                                  |              |
| Umrežavanje s Miele@home                                               | •            |
| Zaslon                                                                 | DirectSensor |
| SoftOpen                                                               | •            |
| SoftClose                                                              | •            |
| MultiLingua                                                            | •            |
| Priprema jela neovisna o količini                                      | •            |
| Priprema na pari na 3 razine istovremeno                               | •            |
| Automatska priprema jelovnika                                          | •            |
| Redukcija pare po isteku vremena pripreme                              | •            |
| Prikaz dnevnog vremena                                                 | •            |
| Prikaz datuma                                                          | •            |
| Podsjetnik minuta                                                      | •            |
| Programiranje vremena početka pripreme                                 | •            |
| Programiranje vremena završetka pripreme                               | •            |
| Programiranje trajanja pripreme                                        | •            |
| Prikaz stvarne temperature                                             | •            |
| Prikaz željene temperature                                             | •            |
| Signalni ton pri postizanju potrebne temperature                       | •            |
| Preporučena temperatura                                                | •            |
| Osobni programi                                                        | •            |
| Individualne postavke                                                  | •            |
| Učinkovitost i održivost                                               |              |
| Potrošnja električne energije u stanju isključenosti u W               | 0,3          |
| Potrošnja električne energije u stanju pripravnosti u W                | 0,8          |
| Potrošnja električne energije u umreženom stanju pripravnosti u W      | 2,0          |
| Vrijeme do automatskog prebacivanja u stanje pripravnosti u min        | 20           |

DG 7440

Ugradbena parna pećnica

za zdravu pripremu hrane s automatskim programima, umrežavanjem i Sous-vide.



EAN: 4002516923930 / Materijal: 12867620 / Stari broj materijala: 23744000D

|                                                                          |                 |
|--------------------------------------------------------------------------|-----------------|
| Vrijeme do automatskog prebacivanja u stanje isključenosti u min         | 20              |
| Vrijeme do automatskog prebacivanja u umreženo stanje pripravnosti u min | 20              |
| <b>Komfor pri održavanju</b>                                             |                 |
| Prostor za pripremu jela od plemenitog čelika lanene strukture           | •               |
| Vanjski generator pare                                                   | •               |
| Grijač u podnožju za redukciju kondenzata                                | •               |
| Brzi utični zapor za bočne vodilice                                      | •               |
| Uklonjive bočne vodilice                                                 | •               |
| Uklanjanje kamenca                                                       | •               |
| CleanGlass vrata                                                         | •               |
| <b>Tehn. pare/Opskrba vodom</b>                                          |                 |
| DualSteam                                                                | •               |
| Volumen spremnika za svjež u vodu l                                      | 1,5             |
| Uklanjanje spremnika za svjež u vodu s Push2Release mehanizmom           | •               |
| <b>Sigurnost</b>                                                         |                 |
| Sustav hlađenja s hladnom prednjom stranom uređaja                       | •               |
| Sigurnosno isključivanje                                                 | •               |
| Blokada uključivanja                                                     | •               |
| Sustav hlađenja pare                                                     | •               |
| Blokada tipki                                                            | •               |
| <b>Tehnički podaci</b>                                                   |                 |
| L prostor za pripremu jela                                               | •               |
| Volumen prostora za pripremu jela u l                                    | 40              |
| Broj razina umetanja                                                     | 4               |
| Dimenzije uređaja (Š x V x D) u mm                                       | 595 x 455 x 569 |
| Smjer otvaranja vrata                                                    | dolje           |
| Osvjetljenje prostora za pripremu jela                                   | 2 LED sijalice  |
| Min. temperatura kod rada na pari u °C                                   | 40              |
| Maks. temperatura kod rada na pari u °C                                  | 100             |
| Min. širina niše u mm                                                    | 560             |
| Maks. širina niše u mm                                                   | 568             |
| Min. visina niše u mm                                                    | 450             |
| Maks. visina niše u mm                                                   | 452             |
| Dubina niše u mm                                                         | 550             |
| Dimenzije uređaja (Š x V x D) u mm                                       | 595 x 455 x 569 |
| Širina uređaja u mm                                                      | 595             |
| Visina uređaja u mm                                                      | 455             |
| Dubina uređaja u mm                                                      | 569             |
| Težina u kg                                                              | 26,3            |
| Ukupna priključna vrijednost u kW                                        | 3,60            |
| Napon u V                                                                | 230             |
| Frekvencija u Hz                                                         | 50-60           |
| Osigurač u A                                                             | 16              |
| Broj faza                                                                | 1               |
| Priključni kabel s mrežnim utikačem                                      | •               |

## Ugradbena parna pećnica




EAN: 4002516923930 / Materijal: 12867620 / Stari broj materijala: 23744000D

|                                                                   |                                                                                                                                                                                                                                                                                                                                     |
|-------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Duljina električnog kabela u m                                    | 2                                                                                                                                                                                                                                                                                                                                   |
| Zamjena rasvjetnog tijela                                         | Servisna služba                                                                                                                                                                                                                                                                                                                     |
| <b>Isporučeni pribor</b>                                          |                                                                                                                                                                                                                                                                                                                                     |
| Uklonjive bočne vodilice (par)                                    | 1                                                                                                                                                                                                                                                                                                                                   |
| Perforirana posuda za kuhanje od plemenitog čelika                | 2                                                                                                                                                                                                                                                                                                                                   |
| Neperforirana posuda za kuhanje od plemenitog čelika<br>DGG 50 40 | 1                                                                                                                                                                                                                                                                                                                                   |
| Rešetka                                                           | 1                                                                                                                                                                                                                                                                                                                                   |
| Posuda za prikupljanje tekućine DGG 100 40                        | 1                                                                                                                                                                                                                                                                                                                                   |
| Tablete za uklanjanje kamenca                                     | 2                                                                                                                                                                                                                                                                                                                                   |
| <b>Raspoloživi jezici na zaslonu</b>                              |                                                                                                                                                                                                                                                                                                                                     |
| Raspoloživi jezici na zaslonu s MultiLingua                       | bahasa malaysia, dansk,<br>deutsch, english, español,<br>français, hrvatski, italiano,<br>magyar, nederlands, norsk,<br>polski, portuguese, русский,<br>română, slovenčina,<br>slovensčina, srpski, suomi,<br>svenska, türkçe, українська,<br>čeština, ελληνικά,<br>[?][?][?][?][?][?], [?][?], [?]<br>[?][?], [?][?][?], [?][?][?] |


DG 7440

Ugradbena parna pečnica


za zdravu pripremu hrane s automatskim programima, umrežavanjem i Sous-vide.




H7000 handle, glass, installation drawings




Installation DG, DGM, DGC XL, ESW7x20 installation drawings




side view, DG, DGM, ESW7x20 installation drawings




Installation\_DG\_DGM\_DGC\_XL\_ESW7x10\_EVS7010, installation drawings




Side view\_DG\_DGM\_ESW7x10\_EVS7010 installation drawings




built-in DG DGM DGC XL build-under, installation drawing



Screw joint DG DGM, installation drawing



DG DGM, installation drawing




side view DG DGM, installation drawings

DG 7440

Ugradbena parna pečnica

za zdravu pripremu hrane s automatskim programima, umrežavanjem i Sous-vide.



Installation DG, installation drawing