

H 2880 BP

Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.



- Display de 7 segmentos con mandos ocultos: EasyControl
- Mínimo esfuerzo de limpieza: dotación con función pirólisis
- Posibilidades ilimitadas: volumen de 4,59 ft³ en 6 niveles
- Movimiento suave de la puerta: SoftOpen & SoftClose
- Protección frente a quemaduras: frontal frío

Código EAN: 4002516487159 / Número de material: 11805330 /
Número de material antiguo: 22288045USA

General information	
Model identifier	H 2880 BP
Número de material del fabricante	11805330
EAN number	4002516487159
Gama	Silver
Construcción y diseño	
PureLine	•
Tipo y diseño del aparato	
Horno	•
Color del aparato	Acero inoxidable/acero limpio
Ventajas Miele	
Regulación precisa de la temperatura hornos en °F (°C)	85-575 (30-300)
Calentamiento rápido	•
Funciones	
Calor de bóveda y solera	•
Calor de solera	•
Grill con recirculación de aire	•
Grill	•
Funciones con grill	•
Confort de manejo	
Display	EasyControl
SoftOpen	•
SoftClose	•
Indicación de la hora	•
Minutero avisador	•
Programación de fin de cocción	•
Programación de tiempos de cocción	•
Ajustes individuales	•
Confort de mantenimiento	
Frontal en acero inoxidable con acabado CleanSteel	•
Autolimpieza pirolítica	•
Catalizador sin calentamiento	•
Puerta CleanGlass	•
Seguridad	
Sistema de enfriamiento del aparato con frente frío	•
Bloqueo de puesta en funcionamiento	•
Bloqueo de puerta durante pirólisis	•
Datos técnicos	
Volumen interior en l	130
Número de niveles de bandeja	6
Identificación de los niveles de bandeja	•
Iluminación interior	2 halógenos
Ventilador de aire caliente TwinPower	•
Ancho del hueco mín. en mm	724
Alto del hueco mín. en mm	718
Fondo del hueco en mm	610
Peso neto en kg	83,7

H 2880 BP

Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




Código EAN: 4002516487159 / Número de material: 11805330 /
Número de material antiguo: 22288045USA


Potencia nominal total en kW	6,50
Tensión en V	120
Tensión conmutable en V	240/208
Frecuencia en Hz	60
Fusibles en A	30
Número de fases	1
Longitud del cable de conexión eléctrica en m	1,80
Accesorios suministrados	
Parrilla	1
Bandeja universal con PerfectClean HUBB 91	1
Listones portabandejas extraíbles (par)	1

H 2880 BP


Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




side view 30 inch Flush inset, installation drawing, NA




installation 30 inch Flush inset, installation drawing, NA




installation 30 inch Flush inset built-under, installation drawing, NA




installation 30 inch Proud, installation drawing, NA




H 6x80 BP, ESW 6x80, H 6x80-2BP, H2x80, H7x80m ESW7x80 Combi, Installation drawing, Flush inset, NA




H 6x80 BP, ESW 6x80, H 6x80-2BP, H2x80BP, H7x80BP(X), ESW7x80, Combi, Installation drawing, Proud, NA



DGC6x6+EBA680B, H6x80BP, H6x80-2BP, DGC786x+EBA786B, H2880BP, H7x80BPX, Fitting Combi, Installation drawing, Proud, NA




H6x80BP, (H6x00BM, DGC6x00-1)+EBA680B, H6x80-2BP, DGC7x4x+EBA784B, H2880BP, H7x80BPX, Fitting Combi, Installation drawing, Proud, NA




H6x80BP, H6x70BM, H6x80-2BP, DGC7x7x, H7x70BM, H2x80BP, H7x80BP(X), Fitting Combi, Installation drawing, Proud, NA

H 2880 BP


Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




H6x80BP, ESW6x80, H6x80-2BP, H2x80BP,
H7x80BPX, ESW7x80, Fitting Combi, Installation
drawing, Proud, NA




DGC6x6(AM)+EBA6808,H6x80(-2)BP,ESW6x80,
DGC786x+EBA7868, H2880BP, H7x80BP, ESW7x80,
Fitting Combi, Installation, Proud,




H6x80BP, H6x00BM+EBA6808, ESW6x85,
DGC6x00-1 + EBA6808, H6x80-2BP, NA7000 Fitting
Combi, Installation drawing, Proud, NA




H6x80BP, H6x00BM+EBA6808, ESW6x80, DGC6x00-
1+EBA6808, H6x80-2BP, NA7000 Fitting Combi,
Installation drawing, Proud, NA




H 6x80 BP, H 6x70 BM, ESW 6x80, H 6x80-2BP,
NA7000 Fitting Combi, Installation drawing, Proud, NA




H 6x80 BP, H 6x80-2BP, NA7000, Fitting Combi side by
side, Installation drawing, Proud, NA



H 6x80 BP, H 6x70 BM, ESW 6x85, H 6x80-2BP,
NA7000, Fitting Combi side by side, Installation
drawing, Proud, NA




H 6x80 BP, H 6x80-2BP, NA7000 Fitting Combi side by
side without wall, Installation drawing, Proud, NA




H6x80BP, H6x70BM, ESW6x85, H6x80-2BP, NA7000,
Fitting Combi side by side without wall, Installation
drawing, Proud, NA

H 2880 BP


Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




DGC 6x6x (AM) + EBA 6808, H 6x80 BP, H 6x80-2BP, NA7000, Fitting Combi wide front, Installation drawing, Proud, NA




H6x80BP, (H6x00BM, DGC6x00-1) + EBA6808, H6x80-2BP, NA7000, Fitting Combi wide front, Installation drawing, Proud




DGC 6x6x (AM) + EBA 6808, H 6x80 BP, ESW 6x80, H 6x80-2BP, NA7000 Fitting Combi wide front, Installation drawing, Proud




H 6x80 BP, H 6x00 BM + EBA 6808, ESW 6x85, DGC6x00 + EBA6808, H6x80-2BP, NA7000, Fitting Combi w. front, drawing, Proud




H6x80BP, H6x00BM + EBA6808, ESW6x80, DGC6x00 + EBA 6808, H 6x80-2BP, NA7000 Fitting Combi w. front, drawing, Proud, NA




H 6x80 BP, H 6x80-2BP, H2x80BP, H7x80BP(X), Fitting Combi wide front side by side, Installation drawing, Proud, NA



H 6x80 BP, H 6x80-2BP, NA7000 Fitting Combi wide front side by side without wall, Installation drawing, Proud, NA




H6x80(-)2BP, H6x00BM + EBA6808, H7x40BM, H2880BP, H7x80BP(X), Installation Combi, Installation drawing, Proud, NA




H 6x80 BP, H 6x70 BM, H 6x80-2BP, Hx70BM, H2x80BP(X), H7x80BP(X), Installation Combi, Installation drawing, Proud, NA

H 2880 BP


Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




H 6x80 BP, ESW 6x80, H 6x80-2BP, H2x80BP, H7x80BP, ESW7x80, Installation Combi, Installation drawing, Proud, NA




H 6x80 BP, H 6x00 BM + EBA 6808, ESW 6x85, H 6x80-2BP, NA7000 Installation Combi, Installation drawing, Proud, NA




H 6x80 BP, H 6x00 BM + EBA 6808, ESW 6x80, H 6x80-2BP, NA7000 Installation Combi, Installation drawing, Proud, NA




H 6x80 BP, H 6x70 BM, ESW 6x85, H 6x80-2BP, NA7000 Installation Combi, Installation drawing, Proud, NA




H 6x80 BP, H 6x70 BM, ESW 6x80, H 6x80-2BP, NA7000, Installation Combi, Installation drawing, Proud, NA




H 6x80 BP, H 6x80-2BP, H2x80BP, H7x80BP, Installation Combi, side by side, Installation drawing, Proud, NA



H6x80(-)BP, H6x70BM, ESW6x85, H2x80BP, H7x80BP, ESW7x70, EVS7670, Installation Combi side by side, Installation drawing




H 6x80 BP, H 6x80-2BP, H2x80BP, H7x80BP(X), Installation Combi side by side without wall, Installation drawing, Proud, NA




H 6x80 BP, H 6x70 BM, ESW 6x85, H 6x80-2BP, NA7000, Installation Combi side by side without wall, drawing, Proud, NA

H 2880 BP


Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




DGC 6x6x (AM) + EBA 6808, H 6x80 BP, H 6x80-2BP, Installation Combi wide front, Installation drawing, Proud, NA




H 6x80 BP, H 6x00 BM + EBA 6808, H 6x80-2BP, NA7000, Installation Combi wide front, Installation drawing, Proud, NA




H 6x80 BP, H 6x70 BM, H 6x80-2BP, NA7000, Installation Combi wide front, Installation drawing, Proud, NA




H 6x80 BP, ESW 6x80, H 6x80-2BP, NA7000, Installation Combi wide front, Installation drawing, Proud, NA




H 6x80 BP, H 6x00 BM + EBA 6808, ESW 6x85, H 6x80-2BP, NA7000, Installation Combi wide front, Installation drawing, Proud, NA




H 6x80 BP, H 6x00 BM + EBA 6808, ESW 6x80, H 6x80-2BP, NA7000, Installation Combi wide front, Installation drawing, Proud, NA



H 6x80 BP, H 6x70 BM, ESW 6x85, H 6x80-2BP, NA7000, Installation Combi wide front, Installation drawing, Proud, NA




H 6x80 BP, H 6x70 BM, ESW 6x80, H 6x80-2BP, NA7000, Installation Combi wide front, Installation drawing, Proud, NA




H 6x80 BP, H 6x80-2BP, H 2x80 BP, H 7x80 BP, Installation Combi wide front side by side, Installation drawing, Proud, NA

H 2880 BP


Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




H6x80(2)BP, H6x70BM, ESW6x85, H2x80BP, H7x80BP, Installation Combi wide front side by side, Installation drawing, Proud




H6x80BP, H6x80-2BP, H2x80BP, H7x80BP, Installation Combi wide front side by side without wall, Installation drawing




H6x80 BP, H6x70BM, ESW6x85, H6x80-2BP, NA7000, Installation Combi w. front side by side without wall, drawing, Proud, NA




H2x80BP, side view, 30 Zoll, Proud, Discovery




installation 30 inch Proud Discovery, installation drawing, NA




installation 30 inch Proud build-under Discovery, installation drawing, NA



installation 30 inch Proud wide front Discovery, installation drawing, NA




installation 30 inch Flush inset discovery, installation drawing, NA




installation 30 inch Flush inset built-under Discovery, installation drawing, NA

H 2880 BP


Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




installation 30 inch Flush inset built-under wide front discovery, installation drawing, NA




DGC7x7x(X), H7x8x(X)BP, side view, 30 Zoll, Flush inset, combi, XL, 650




DGC7x8x, H2x80BP, H7x8xBP(X), side view, 30 Zoll, Flush inset, combi, XXL 650




DGC7x8x(X), H2x80BP, H7x8xBP, ESW7x80, side view, 30 Zoll, Flush inset, combi, XXL, 650, ESW30




DGC7xxx, H2x80BP, H7x8xBP(X), side view, 30 Zoll, Proud, combi, XL, 650




DGC7x8x, H2x80BP, H7x8xBP(X), side view, 30 Zoll, Proud, combi, XXL 650



DGC7x8x(X), H2x80BP, H7x8xBP(X), ESW7x80, side view, 30 Zoll, Proud, combi, XXL, 650




DGC7x4x+EBA7848, H2880BP, H7x8xBP(X), Installation, 30 Zoll, Proud, combi, 650




DGC786x+EBA7868, H2880BP, H7x8xBP(X), Installation, 30 Zoll Proud, combi, XXL, 650

H 2880 BP


Horno de 30 pulgadas de ancho
diseño fácilmente combinable, con pirólisis.




DGC7x4x+EBA7848, H2880BP, H7x6xBP(X), ESW7x80, Installation, 30 Zoll, Proud, combi, XL, 650




DGC786x+EBA7868, H7x8xBP, ESW7x80, Installation, 30 Zoll, Proud, combi, XXL, 650




DGC7x4x+EBA7848, H2880BP, H7280BPX, Installation, 30 Zoll, Proud, combi, wide front, XL, 650



DGC7x4x+EBA7848, H2880BP, H7x8xBP, ESW7x80, Installation, 30 Zoll, Proud, combi, wide front, XL, 650



Handle H72xx, H76xx, H78xx, PureLine – NA7000 - Installation drawing



installation 30 inch Flush inset wide front Discovery, installation drawing, NA