

## PRODOTTI CON ESTENSIONE DI GARANZIA (SE RICHIESTA)

Nr. Articolo	EAN	Descrizione
<b>LAVASTOVIGLIE</b>		
12445390	4002516748427	G 7260 SCVi
12445320	4002516748250	G 7180 SCVi
12445400	4002516748434	G 7265 SCVi XXL
12445330	4002516748267	G 7185 SCVi XXL
12445460	4002516748489	G 7650 SCVi
12445470	4002516748496	G 7655 SCVi XXL
12445480	4002516748502	G 7980 SCVi K2O
12445490	4002516748519	G 7985 SCVi K2O XXL
12289200	4002516678786	G 5790 SCVI
12445380	4002516748410	G 7210 SCi CLST
12445450	4002516748472	G 7600 SCi CLST
12849480	4002516906063	G 7080 SCVI AUTODOS
12470510	4002516763437	G 7793 SCVi K2O 125 Gala Edition
12470500	4002516763420	G 7771 SCVi AUTODOS 125 Gala Edition
<b>FORNI</b>		
11599820	4002516375784	H 7262 B EDST/CLST
11120220	4002516182238	H 7264 B EDST/CLST
11120520	4002516120728	H 7264 B OBSW
11120530	4002516182511	H 7264 B GRGR
11599870	4002516391197	H 7262 BP EDST/CLST
11614710	4002516375753	H 7262 BP OBSW
11120230	4002516182313	H 7264 BP EDST/CLST
11120550	4002516120445	H 7264 BP OBSW
11120560	4002516182542	H 7264 BP GRGR
11120760	4002516182191	H 7460 B EDST/CLST
11120650	4002516172949	H 7460 B OBSW
11120660	4002516172864	H 7460 B GRGR
11120910	4002516182535	H 7464 BP EDST/CLST
11120890	4002516172871	H 7464 BP OBSW
11120900	4002516172673	H 7464 BP GRGR
11120930	4002516172697	H 7464 BPX OBSW
11120940	4002516172772	H 7464 BPX GRGR
11120980	4002516120711	H 7660 BP EDST/CLST
11120960	4002516172970	H 7660 BP OBSW
11120970	4002516172789	H 7660 BP GRGR
11121100	4002516182351	H 7860 BP EDST/CLST
11121080	4002516172895	H 7860 BP OBSW
11121090	4002516173038	H 7860 BP GRGR
11121120	4002516173007	H 7860 BPX OBSW
11121130	4002516172901	H 7860 BPX GRGR
11120200	4002516182221	H 7244 B EDST/CLST
11120260	4002516182177	H 7244 B OBSW
11120600	4002516182528	H 7440 B EDST/CLST
11120580	4002516172765	H 7440 B OBSW
11120590	4002516172840	H 7440 B GRGR
11120620	4002516120469	H 7440 BPX OBSW
11120630	4002516120476	H 7440 BPX GRGR
11121020	4002516182627	H 7840 BP EDST/CLST
11121000	4002516172796	H 7840 BP OBSW
11121010	4002516172802	H 7840 BP GRGR
11121050	4002516172987	H 7840 BPX OBSW
11121060	4002516172888	H 7840 BPX GRGR
11119240	4002516229063	H 7890 BP EDST/CLST
11119360	4002516172727	H 7240 BM OBSW
11119380	4002516172604	H 7240 BM GRGR
11119390	4002516182733	H 7240 BM EDST/CLST
11119430	4002516172635	H 7440 BM OBSW
11119460	4002516172642	H 7440 BM GRGR

11119480	4002516207511	H 7440 BM EDST/CLST
11119510	4002516172741	H 7440 BMX OBSW
11119520	4002516172918	H 7440 BMX GRGR
11119550	4002516172758	H 7840 BM OBSW
11119560	4002516172826	H 7840 BM GRGR
11119570	4002516182634	H 7840 BM EDST/CLST
11119590	4002516172925	H 7840 BMX OBSW
11119600	4002516172666	H 7840 BMX GRGR
12624340	4002516835851	H 7464 BPX PEBE
12624370	4002516835875	H 7860 BPX PEBE
12624320	4002516836025	H 7440 BPX PEBE
12624350	4002516835868	H 7840 BPX PEBE
12624330	4002516835950	H 7440 BMX PEBE
12624360	4002516835967	H 7840 BMX PEBE
12347850	4002516751731	H 7464 BPX OBSW/MATT
12347880	4002516751670	H 7860 BPX OBSW/MATT
12347830	4002516751724	H 7440 BPX OBSW/MATT
12347860	4002516751663	H 7840 BPX OBSW/MATT
12347840	4002516751656	H 7440 BMX OBSW/MATT
12347870	4002516751243	H 7840 BMX OBSW/MATT
<b>FORNI A VAPORE</b>		
11134240	4002516160403	DG 7240 EDST/CLST
11134220	4002516160380	DG 7240 OBSW
11134280	4002516160267	DG 7440 EDST/CLST
11134260	4002516160427	DG 7440 OBSW
11134270	4002516160434	DG 7440 GRGR
12113840	4002516595298	DGC 7250 EDST
11821040	4002516596011	DGC 7450 EDST
11821050	4002516610885	DGC 7450 OBSW
11821060	4002516595380	DGC 7450 GRGR
12116100	4002516632863	DGC 7440 HC Pro EDST/CLST
12116020	4002516632924	DGC 7440 HC Pro OBSW
12116050	4002516632764	DGC 7440 HC Pro GRGR
12116360	4002516632771	DGC 7440 HCX Pro OBSW
12116400	4002516633051	DGC 7440 HCX Pro GRGR
Material su richiesta	Momentaneamente non disponibile	DGC 7445 HC Pro EDST/CLST
Material su richiesta	Momentaneamente non disponibile	DGC 7445 HC Pro VitroLine OBSW
12116540	4002516633068	DGC 7460 HC Pro EDST/CLST
12116450	4002516632870	DGC 7460 HC Pro OBSW
12116480	4002516632887	DGC 7460 HC Pro GRGR
12116590	4002516632894	DGC 7460 HCX Pro OBSW
12116630	4002516632900	DGC 7460 HCX Pro GRGR
Material su richiesta	Momentaneamente non disponibile	DGC 7465 HC Pro EDST/CLST
Material su richiesta	Momentaneamente non disponibile	DGC 7465 HC Pro VitroLine OBSW
12118490	4002516637424	DGC 7840 HC Pro EDST/CLST
12116920	4002516632948	DGC 7840 HC Pro OBSW
12116980	4002516633112	DGC 7840 HC Pro GRGR
12117110	4002516633099	DGC 7840 HCX Pro OBSW
12117190	4002516633129	DGC 7840 HCX Pro GRGR
Material su richiesta	Momentaneamente non disponibile	DGC 7845 HC Pro EDST/CLST
Material su richiesta	Momentaneamente non disponibile	DGC 7845 HC Pro Vitroline OBSW
12118470	4002516596417	DGC 7660 HC Pro EDST/CLST
12116770	4002516632795	DGC 7660 HC Pro OBSW
12117600	4002516632962	DGC 7860 HC Pro EDST/CLST
12117550	4002516633143	DGC 7860 HC Pro OBSW
12117580	4002516632955	DGC 7860 HC Pro GRGR
12117630	4002516633211	DGC 7860 HCX Pro OBSW
12117640	4002516633150	DGC 7860 HCX Pro GRGR
Material su richiesta	Momentaneamente non disponibile	DGC 7865 HC Pro EDST/CLST
Material su richiesta	Momentaneamente non disponibile	DGC 7865 HC Pro Vitroline OBSW
12624500	4002516829003	DGC 7440 HCX Pro PEBE
12624530	4002516829089	DGC 7460 HCX Pro PEBE
12624650	4002516823667	DGC 7840 HCX Pro PEBE

12624670	4002516822400	DGC 7860 HCX Pro PEBE
12347600	4002516720010	DGC 7440 HCX Pro OBSW/MATT
12347660	4002516719779	DGC 7460 HCX Pro OBSW/MATT
12347670	4002516720027	DGC 7840 HCX Pro OBSW/MATT
12347680	4002516719908	DGC 7860 HCX Pro OBSW/MATT

<b>FORNO A VAPORE CON MICROONDE</b>		
11134520	4002516160281	DGM 7440 OBSW
11134530	4002516160298	DGM 7440 GRGR
11134540	4002516160304	DGM 7440 EDST/CLST
11134620	4002516160502	DGM 7840 EDST/CLST
11134600	4002516160472	DGM 7840 OBSW
11134610	4002516160489	DGM 7840 GRGR
<b>FORNI A MICROONDE</b>		
11133740	4002516124542	M 7240
11133880	4002516124597	M 7244 EDST/CLST
11133850	4002516124573	M 7244 OBSW
11133860	4002516124580	M 7244 GRGR
<b>CASSETTI SCALDASTOVIGLIE E SCALDAVIVANDE</b>		
11133980	4002516191339	ESW 7010 OBSW
11133990	4002516191421	ESW 7010 GRGR
11134010	4002516191438	ESW 7020 OBSW
11134020	4002516191445	ESW 7020 GRGR
11153820	4002516164524	ESW 7020 EDST/CLST
11323530	4002516241690	ESW 7030 OBSW
11323540	4002516242413	ESW 7030 GRGR
12625490	4002516822301	ESW 7010 PEBE
12347690	4002516719632	ESW 7010 OBSW/MATT
12347700	4002516719649	ESW 7020 OBSW/MATT
<b>CASSETTI PER SOTTOVUOTO</b>		
11134090	4002516160243	EVS 7010 OBSW
11134100	4002516160250	EVS 7010 GRGR
12625520	4002516823643	EVS 7010 PEBE
12347710	4002516719571	EVS 7010 OBSW/MATT

## PIANI COTTURA

10882050	4002515996805	KM 6564 FR
11153910	4002516147282	KM 7464 FL (50 x 60)
11154100	4002516147411	KM 7564 FL
11154180	4002516147244	KM 7667 FL
11154120	4002516147435	KM 7575 FL
12276880	4002516675686	KM 7878-1 FL
11154130	4002516147442	KM 7594 FL*
12276890	4002516675181	KM 7897-1 FL
11153890	4002516147268	KM 7404 FX - (47x57)
11153920	4002516147299	KM 7465 FL (50 x 60)
11153930	4002516147305	KM 7474 FL
11154110	4002516147428	KM 7574 FL
11249900	4002516193227	KM 7677 FL
11507220	4002516347651	KM 7678 FL
11512270	4002516338390	KM 7679 FL
11512290	4002516339427	KM 7699 FR
11512300	4002516339526	KM 7899 FL
11154150	4002516147459	KM 7684 FL
11155770	4002516230632	KM 7999 FL
11155740	4002516230984	KM 7999 FR
12409290	4002516739890	KMDA 7473 FR-U
12507670	4002516777953	KMDA 7676 FL-U BlackPerfection
12270270	4002516668459	KMDA 7473 FL-A
12270280	4002516668596	KMDA 7473 FL-U
12904860	4002516944607	KMDA 7473-1 FR
12904880	4002516944591	KMDA 7676-1 FL BlackPerfection
12904890	4002516944713	KMDA 7876-1 FL MattFinish
12904870	4002516944331	KMDA 7473-1 FL
9606920	4002515341391	KM 2312 G
9606940	4002515341407	KM 2334 G
9228920	4002515094013	KM 3010 G
9606950	4002515334959	KM 2335 G
9305210	4002515181072	KM 2354 G
9348570	4002515188965	KM 2355 G
10939730	4002516127567	KM 3034-1 G
10939040	4002516127611	KM 3054-1 G
11402830	4002516306399	CS 7101-1 FL
11402840	4002516306184	CS 7102-1 FL
11402380	4002516305842	CSDA 7001
10686470	4002515893142	CS 7612 FL
10686510	4002515875155	CS 7632 FL
11323200	4002516276128	CS 7641 FL
12514840	4002516818687	KMDA 7876 FL-U 125 Gala Edition
12527240	4002516785668	KM 7576 FL 125 Gala Edition

<b>CAPPE ASPIRANTI</b>		
12010830	4002516570059	DAS 4920 EDST
12010840	4002516544364	DAS 4930 OBSW
12010820	4002516544302	DAS 4640 GLASS
12010860	4002516544517	DAS 4940 GLASS
12010850	4002516570325	DAS 8930 EDST
Momentaneamente non disponibile	Momentaneamente non disponibile	DAS 4620 EDST
10751620	4002515935446	DA 2558
10847500	4002515977316	DA 2578
10847520	4002515977330	DA 2668
10847530	4002515977347	DA 2698 EDST
10751480	4002515935576	DA 2698 BRWS
10847510	4002515977323	DA 2628 EDST
10751350	4002515935514	DA 2628 BRWS
12506080	4002516788676	DA 9299 W blbo
10847580	4002516019718	DA 4298 W
10749620	4002515935590	DA 5798 W Next Step EDST
12533960	4002516802327	DAH 2960 OBSW Escala
12533970	4002516802334	DAH 2960 GRGR Escala
10847570	4002516019565	DA 4228 W Puristic Plus EDST
12560010	4002516802693	DAC 4940 EDST Stella Ambient
10749650	4002515935996	DA 6698 W Puristic Edition 6000 Cls
10750330	4002515935965	DA 6698 W Puristic Edition 6000 OBSW
12555990	4002516802709	DAC 4940 WSMA Stella Ambient
12440800	4002516762324	DAD 4841 Black Levantar
12440810	4002516762331	DAD 4941 Black Levantar
10750490	4002515937006	DA 6698 D Puristic Edition 6000 CLS
10750470	4002515936979	DA 6698 D Puristic Edition 6000 OBSW
10755650	4002515937099	DA 6708 D EDST
10755630	4002515937075	DA 6708 D OBSW
11159560	4002516169642	DA 7078 D AURA 3.0
12555980	4002516802723	DAC 4240 EDST Stella Ambient
12534070	4002516802402	DAH 4970 OBSW Sienna
12459990	4002516771531	DAS 4931 125 Edition
11476590	4002516311102	DA 7378 D AURA 4.0
12534150	4002516802457	DAH 4980 obsw/matt 125 Gala Edition
<b>CONGELATORI</b>		
12379970	4002516716204	F 31202 Ui-1
12443420	4002516746669	FNS 7040 B
12449050	4002516751359	FNS 7140 C
12443480	4002516746683	FNS 7710 E
12443620	4002516746706	FNS 7774 D
12443650	4002516747031	FNS 7794 D L
12519380	4002516779322	FNUS 7040 D
12361980	4002516711827	FNS 7740 D 125 Gala Edition
<b>FRIGO CONGELATORI</b>		
12445080	4002516748151	KFN 7733 E
12665220	4002516840602	KFN 7833 D
12336150	4002516701323	KFN 7734 C
12445160	4002516748175	KFN 7764 C
12445190	4002516748205	KFN 7774 C
12445210	4002516748229	KFN 7795 C
12445040	4002516748113	KF 7742 B
12361990	4002516711704	KFN 7744 C 125 Gala Edition

<b>FRIGORIFERI</b>		
12364350	4002516712374	K 31222 Ui-1
12364370	4002516712398	K 31242 Ui F-1
12364410	4002516712411	K 31252 Ui-1
12444100	4002516746577	K 7438 D
12444380	4002516747543	K 7715 E
12444390	4002516747567	K 7716 E
12444430	4002516747598	K 7737 D
12444450	4002516747710	K 7738 D
12444700	4002516747802	K 7748 D
12444890	4002516747871	K 7777 C
12444940	4002516748014	K 7778 C
12444970	4002516748045	K 7797 C R
12519110	4002516779216	KU 7015 D
12519090	4002516779100	KU 7016 D
12519150	4002516779230	KU 7030 D
12361920	4002516711674	K 7747 C 125 Gala Edition
<b>FRIGORIFERI PER VINI</b>		
9764980	4002515397282	KWT 6321
11186560	4002516150701	KWT 7112 iG ed
11186580	4002516150923	KWT 7112 iG OBSW
12364290	4002516712329	KWT 6422 i-1
12364280	4002516712312	KWT 6422 iG-1 obsw
12497000	4002516770367	KWT 6322UG-1
12364320	4002516712367	KWT 6722 iS-1
12364310	4002516712350	KWT 6722 iG S-1
12615940	4002516813392	KWT 7112 iG PEBE
12615910	4002516813385	KWT 6422 iG-1 PEBE
12519510	4002516779360	KWTUS 7074 F
12519560	4002516779438	KWTUS 7096 E
12519660	4002516779421	KWTUS 7196 E
12204800	4002516643135	KWT 7112 iG OBSW/MATT 125 Gala Edition
<b>MACCHINE PER IL CAFFÈ</b>		
11166410	4002516141440	CVA 7440 EDST/CLST
11166390	4002516141426	CVA 7440 OBSW
11166400	4002516141433	CVA 7440 GRGR
11166430	4002516141464	CVA 7840 EDST/CLST
11166470	4002516141501	CVA 7845 EDST/CLST
11166450	4002516141488	CVA 7845 OBSW
11166460	4002516141495	CVA 7845 GRGR
12642380	4002516825432	CVA 7440 PEBE
12642420	4002516826323	CVA 7845 PEBE
12388840	4002516722113	CVA 7440 OBSW/MATT
12388850	4002516722120	CVA 7845 OBSW/MATT