






		<i>SlimLine</i>	<i>G 5000 and 7000</i>
	<i>Semi Integrated</i>		<div>Material number: 10986720 (Full Size) Description: GFV 60/60 -7 6" toekick</div> <div>Material number: 10986730 (Full Size) Description: GFV 60/65 -7 4" toekick</div>
	<i>Fully Integrated (4")</i>	<div>Material number: 11573740 (Slimline) Description: GFVi 453/77 - 7 4" toekick / no handle</div>	<div>Material number: 10986750 (Full Size) Description: GFVi 701/77 4" toekick / no handle</div> <div>Material number: 11558080 (Full Size) Description: GFVi 706/77 4" toekick / PureLine handle</div> <div>Material number: 11558100 (Full Size) Description: GFVi 707/77 4" toekick / ContourLine handle</div> <div>Material number: 11558110 (Full Size) Description: GFVi 708/77 4" toekick / Range panel</div> <div>Material number: 11750840 (Full Size) Description: GFVi 709/77 4" toekick / Pocket handle</div>
	<i>Fully Integrated (6")</i>	<div>Material number: 11526970 (Slimline) Description: GFVi 453/72 - 7 6" toekick / no handle</div>	<div>Material number: 10986740 (Full Size) Description: GFVi 701/72 6" toekick / no handle</div> <div>Material number: 11558090 (Full Size) Description: GFVi 707/72 6" toekick / ContourLine handle</div>



AutoDos
AutoDos with integrated PowerDisk®, automatically dispenses the correct amount of detergent in accordance with the selected program and degree of soiling.



AutoStart
No matter where you are, use the Miele@mobile app to automatically start your dishwasher at pre-determined times.



WifiConn@ct
For your convenience, use your WiFi to remotely operate and monitor your dishwasher at any time.



Knock2Open
Our dishwashers can be perfectly integrated into handleless kitchens – the door opens automatically by tapping twice.



M Touch S/Vi
M Touch controls are both easy-to-operate and navigate. An intuitive swipe of the screen will quickly lead you to your desired selection.




QuickIntenseWash
Excellent cleaning and drying results for normally soiled dishware in 58 minutes.



Clean Touch Steel™
This innovative finish resists fingerprints, scratches and smudges. A special treatment stands up to aggressive handling – keeping the exterior cleaner and easier to maintain.



FlexLine Baskets
These baskets offer incredible flexibility for loading and cleaning all kinds of dishware and utensils.



MultiFlex Cutlery Tray
With movable sections, the 3D MultiFlex Tray makes space where there wasn't any before.



ExtraQuiet
This program reduces the sound emissions of the dishwasher cycle to whisper quiet levels.



BrilliantLight
4 powerful LED lights illuminate the dishwasher from the inside out – creating a crystal clear appearance.



SaniWash
When hygiene is especially important, this program offers temperatures high enough to remove germs from baby bottles, chopping boards, utensils, etc.

Miele Dishwashers

Model Comparison Overview 2021



Choose the right model for you and your home. Miele offers the ultimate in convenience and seamless design integration.

Pre-Finished (“U”) Models

Pre-finished models are complete with control and door panel. Generally, these models are available in Clean Touch Steel™.



Semi Integrated (“I”) Models

Integrated dishwashers have a visible control panel and are designed to fit with a custom door panel that reflects the cabinetry decor of your kitchen. Alternatively, Miele offers Clean Touch Steel™ panels for a more professional look.



Fully Integrated (“Vi”) Models

These units can either disappear into your cabinetry by adding a custom front panel or stand out as a robust appliance with a full Clean Touch Steel™ panel. The elegant stainless steel or black glass control panel is integrated on top of the door and is only visible when the door is ajar.



Fully Integrated (“SF”) Models

For convenience, Miele offers fully integrated, pre-finished models that are already equipped with a Clean Touch Steel™ door panel, a 4-inch and 6-inch toe-kick and either a straight door handle or a pocket handle.



*Highlights depend on model.

