

**Miele**

**Miele G 5000 Dishwashers**  
Delivering Superior Results,  
Without Compromise.



# FEATURE HIGHLIGHTS

## PERFORMANCE

### EcoPower Technology

Delivering significantly reduced water and energy consumption, EcoPower features 3-way spray arm alternation, a highly-efficient filtration system and enhanced internal feed pipes.



### QuickIntenseWash

Excellent cleaning and drying results for normally soiled dishware in 58 minutes.

### Water Softner

Optimize performance with sparkling results by eliminating cloudiness and hard water spots.

## CONVENIENCE

### 3D MultiFlex Cutlery Tray

With movable sections, the 3D MultiFlex Tray makes space where there wasn't any before.



### Low Sound Levels

Our dishwashers provide excellent cleaning results with whisper-quiet sound levels.

### AutoSensor

Situated in the pump, the AutoSensor precisely measures dirt particles inside the water 3 times, providing better cleaning results.



## EFFICIENCY

### SensorDry

Consistent and excellent drying results with the lowest energy and time consumption – active in all programs except QuickIntenseWash and Economy.



### AutoOpen Drying

Exclusive to Miele – perfect drying of challenging items such as plastics. The dishwasher door opens automatically at the end of a program cycle, warm moist air exits the dishwasher with special air flow, protecting the countertop.

## DESIGN

### ComfortClose

Designed for effortless opening and closing. And with optimal suspension to ensure your door will remain in its desired position at all times.

### BrilliantLight\* and WifiConn@ct\*

4 powerful LED lights illuminate the dishwasher from the inside out – creating a crystal clear appearance. And equipped with WiFi to remotely operate and monitor your dishwasher at any time.

\*Available on select models



### Pocket Handle

Designed with a new sleek look in mind, our G 5000 dishwashers feature the pocket handle.

