

2024 Kitchen Package Promotion

List of qualifying appliances

| Dishwashers | | |
|--|-----------------|----------|
| G 5000 SlimLine + 24" Dishwashers | | |
| 18" Dishwasher - Slimline | G 5482 SCVi | 11636760 |
| 18" Dishwasher - Slimline | G 5892 SCVi | 11636790 |
| 24" Dishwasher | G 5006 SCU | 11636690 |
| 24" Dishwasher | G 5008 SCU | 11966810 |
| 24" Dishwasher - ADA | G 5051 SCVi | 11636710 |
| 24" Dishwasher | G 5056 SCVi | 11636720 |
| 24" Dishwasher | G 5056 SCVi SF | 11695330 |
| 24" Dishwasher | G 5056 SCVi SFP | 11636730 |
| 24" Dishwasher | G 5058 SCVi SFP | 11966820 |
| 24" Dishwasher | G 5266 SCVi | 11636740 |
| 24" Dishwasher | G 5266 SCVi SF | 11636750 |
| 24" Dishwasher | G 5268 SCVi SF | 11955820 |
| 24" Dishwasher | G 5266 SCVi SFP | 11695340 |
| G 7000 24" Dishwashers | | |
| 24" Dishwasher | G 7106 SCU | 11387580 |
| 24" Dishwasher | G 7156 SCVi | 11387590 |
| 24" Dishwasher w/ GEN7 handle | G7156 SCVi SF | 12055090 |
| 24" Dishwasher | G7158 SCVi SFP | 11667320 |
| 24" Dishwasher | G7166 SCVi | 11947220 |
| 24" Dishwasher | G7166 SCVi SFP | 11947240 |
| 24" Dishwasher | G7176 SCVi SF | 12021290 |
| 24" Dishwasher (Independents) | G7176 SCVi SF | 12021290 |
| 24" Dishwasher (Lowe's) | G7176 SCVi SF | 12021290 |
| 24" Dishwasher | G 7316 SCU | 11388020 |
| 24" Dishwasher | G 7366 SCVi | 11388030 |
| 24" Dishwasher | G 7366 SCVi SF | 11388110 |
| 24" Dishwasher w/ GEN7 handle | G7366 SCVi SF | 12055100 |
| 24" Dishwasher | G 7516 SCi | 11388120 |
| 24" Dishwasher | G 7566 SCVi | 11388140 |
| 24" Dishwasher | G 7566 SCVi SF | 11388250 |
| 24" Dishwasher w/ GEN7 handle | G7566 SCVi SF | 12055110 |
| 24" Dishwasher | G 7591 SCVi | 11388260 |
| 24" Dishwasher | G 7596 SCVi | 11388280 |
| 24" Dishwasher | G 7916 SCi | 11388290 |
| 24" Dishwasher | G 7966 SCVi | 11388300 |
| G 7000 Redesign | | |
| G7186 SCVi XXL USA ED120/60 1,3 SFP ADos | | 12496690 |
| G7193 SCVi USA ED120/60 1,3 AutoDos | | 12496700 |
| G7196 SCVi XXL USA ED120/60 1,3 SF ADos | | 12496710 |
| G7656 SCVi XXL USA OS120/60 1,3 SF ADos | | 12496880 |
| G7766 SCVi XXL USA OS120/60 1,3 AutoDos | | 12496900 |
| G7766 SCVi XXL USA OS120/60 1,3 SF ADos | | 12496910 |
| G7791 SCVi USA OS120/60 1,3 K2O AutoDos | | 12496920 |
| G7796 SCVi XXL USA OS120/60 1,3 K2O ADos | | 12496930 |

| | | |
|--|--|----------|
| G7936 SCi XXL USA OS120/60 1,3 AutoDos | | 12496970 |
| G7986 SCVi XXL USA OS/CS120/60 1,3K2O AD | | 12496980 |
| G7186 SCVi XXL USA ED120/60 1,3 AutoDos | | 12496990 |
| G7216 SCU XXL USA ED120/60 1,3CLST Front | | 12497130 |
| G7266 SCVi XXL USA ED120/60 1,3 | | 12497140 |
| G7266 SCVi XXL USA ED120/60 1,3 SF | | 12497150 |
| G7606 SCU XXL USA ED120/60 1,3 ADos CLST | | 12497170 |
| G7656 SCVi XXL USA OS120/60 1,3 AutoDos | | 12497190 |

| Ranges | | |
|---|--------------|----------|
| Range | | |
| 48" Dual Fuel (6 Burner/Griddle) LP | HR 1956-3 LP | 11791750 |
| 48" Dual Fuel (6 Burner/Griddle) G | HR 1956-3 G | 11791700 |
| 48" Dual Fuel (6 Burner/Grill) G | HR 1955-3 G | 11791690 |
| 48" Dual Fuel (8 Burner) LP | HR 1954-3 LP | 11791680 |
| 48" Dual Fuel (8 Burner) G | HR 1954-3 G | 11791670 |
| 36" Dual Fuel (4 Burner/Griddle) LP | HR 1936-3 LP | 11791630 |
| 36" Dual Fuel (4 Burner/Griddle) G | HR 1936-3 G | 11791610 |
| 36" Dual Fuel (4 Burner/Grill) G | HR 1935-3 G | 11791600 |
| 36" Dual Fuel (6 Burner) LP | HR 1934-3 LP | 11791590 |
| 36" Dual Fuel (6 Burner) G | HR 1934-3 G | 11791570 |
| 30" Dual Fuel (4 Burner) LP | HR 1924-3 LP | 11791560 |
| 30" Dual Fuel (4 Burner) G | HR 1924-3 G | 11791550 |
| 30" Dual Fuel (4 Burner) G | HR1724 G | 10773300 |
| 30" Induction | HR 1622I-3 | 11791520 |
| 30" Induction | HR 1422I-3 | 12298850 |
| 36" All Gas (4 Burner/Griddle) LP | HR 1136-3 LP | 11791510 |
| 36" All Gas (4 Burner/Griddle) G | HR 1136-3 G | 11791500 |
| 36" All Gas (4 Burner/Grill) G | HR 1135-3 G | 11791450 |
| 36" All Gas (6 Burner) LP | HR 1134-3 LP | 11791430 |
| 36" All Gas (6 Burner) G | HR 1134-3 G | 11791410 |
| 30" Dual Fuel (4 Burner) Direct Select LP | HR 1724-3 LP | 11791540 |
| 30" Dual Fuel (4 Burner) Direct Select G | HR 1724-3 G | 11791530 |
| 30" All Gas (4 Burner) LP | HR 1124-3 LP | 11791390 |
| 30" All Gas (4 Burner) G | HR 1124-3 G | 11791360 |

| Ovens | | |
|---|----------------|----------|
| 24" Convection Oven | | |
| 24" Convection Oven - PureLine MTs EDST | H 7660 BP EDST | 11804810 |
| 24" Convection Oven - VitroLine MTs OBSW | H 7660 BP OBSW | 11804860 |
| 24" Convection Oven - VitroLine MTs BRWS | H 7660 BP BRWS | 11804800 |
| 24" Convection Oven - VitroLine MTs GRGR | H 7660 BP GRGR | 11804840 |
| 24" Convection Oven - PureLine DS I EDST | H 7263 BP EDST | 11804760 |
| 24" Convection Oven - VitroLine DS I BRWS | H 7263 BP BRWS | 11804750 |
| 24" Convection Oven - VitroLine DS I GRGR | H 7263 BP GRGR | 11804780 |
| 30" Convection Oven | | |
| 30" Convection Oven - VitroLine MT GRGR | H 7880 BP GRGR | 11805600 |
| 30" Convection Oven - ContourLine 0 EDST | H 2780 BP EDST | 11805330 |
| 30" Convection Oven - PureLine MT EDST | H 7880 BP EDST | 11805590 |
| 30" Convection Oven - VitroLine MT OBSW | H 7880 BP OBSW | 11805610 |

| | | |
|--|------------------------|----------|
| 30" Convection Oven - VitroLine MT BRWS | H 7880 BP BRWS | 11805580 |
| 30" Double oven - ContourLine MT EDST | H 7780 BP2 EDST | 11805570 |
| 30" Convection Oven - ContourLine MT EDST | H 7780 BP EDST | 11805560 |
| 30" Convection Oven - VitroLine DS I BRWS | H 7280 BP BRWS | 11805350 |
| 30" Convection Oven - PureLine MTs EDST | H 7680 BP EDST | 11805550 |
| 30" Convection Oven - ContourLine MTs EDST | H 7580 BP EDST | 11805540 |
| 30" Convection Oven - PureLine DS I EDST | H 7280 BP EDST | 11805500 |
| 30" Convection Oven - ContourLine DS I EDST | H 7180 BP EDST | 11805340 |
| 30" Convection Oven - VitroLine DS I GRGR | H 7280 BP GRGR | 11805520 |
| 30" Convection Oven - PureLine 0 EDST | H 2880 BP EDST | 11805320 |
| 30" Convection Oven - ArtLine MT GRGR | H 7880 BPX GRGR | 11805630 |
| 30" Convection Oven - ArtLine Matte Black | H 7880 BPX Matte Black | 12397540 |
| 30" Convection Oven - ArtLine Matte Black | H 7870 BMX Matte Black | 12397570 |
| 30" Convection Oven | H 6281 BP EDST/CLST | 10773320 |
| 24" Speed Oven | | |
| 24" Speed oven - VitroLine MT GRGR | H 7840 BM GRGR | 11804650 |
| 24" Speed oven - VitroLine MT OBSW | H 7840 BM OBSW | 11804660 |
| 24" Speed oven - VitroLine DS I BRWS | H 7240 BM BRWS | 11804480 |
| 24" Speed oven - PureLine MTs EDST | H 7640 BM EDST | 11804600 |
| 24" Speed oven - PureLine MT EDST | H 7840 BM EDST | 11804640 |
| 24" Speed oven - PureLine DS I EDST | H 7240 BM EDST | 11804510 |
| 24" Speed oven - VitroLine MT BRWS | H 7840 BM BRWS | 11804630 |
| 24" Speed oven - VitroLine DS I GRGR | H 7240 BM GRGR | 11804520 |
| 24" Speed oven | H 6200 BM EDST/CLST | 9769630 |
| 30" Speed Oven | | |
| 30" Speed oven - VitroLine MT GRGR | H 7870 BM GRGR | 11804690 |
| 30" Speed oven - VitroLine MT OBSW | H 7870 BM OBSW | 11804700 |
| 30" Speed oven - VitroLine MT BRWS | H 7870 BM BRWS | 11804670 |
| 30" Speed oven - PureLine MT EDST | H 7870 BM EDST | 11804680 |
| 30" Speed oven - PureLine MTs EDST | H 7670 BM EDST | 11804610 |
| 30" Speed oven - ContourLine MT EDST | H 7770 BM EDST | 11804620 |
| 30" Speed oven - ContourLine MTs EDST | H 7570 BM EDST | 11804590 |
| 30" Speed oven - PureLine DS I EDST | H 7270 BM EDST | 11804570 |
| 30" Speed oven - ArtLine MT GRGR | H 7870 BMX GRGR | 11804710 |
| 30" Speed oven - ContourLine DS I EDST | H 7170 BM EDST | 11804470 |
| 30" Speed oven - VitroLine DS I BRWS | H 7270 BM BRWS | 11804530 |
| 30" Speed oven - VitroLine DS I GRGR | H 7270 BM GRGR | 11804580 |
| 24" Combi-Steam Oven XL | | |
| 24" Steam oven combination XL - VitroLine MT GRGR | DGC 7840 GRGR | 11876600 |
| 24" Steam oven combination XL - PureLine MT EDST | DGC 7845 EDST | 11876580 |
| 24" Steam oven combination XL - VitroLine MT OBSW | DGC 7840 OBSW | 11876610 |
| 24" Steam oven combination XL - PureLine MT EDST | DGC 7840 EDST | 11876590 |
| 24" Steam oven combination XL - VitroLine MT BRWS | DGC 7840 BRWS | 11876630 |
| 24" Steam oven combination XL - PureLine MTs EDST | DGC 7640 EDST | 11876660 |
| 24" Steam oven combination XL - VitroLine DS II GRGR | DGC 7440 GRGR | 11876960 |
| 24" Steam oven combination XL - PureLine DS II EDST | DGC 7440 EDST | 11876950 |
| 24" Steam oven combination XL - VitroLine DS II BRWS | DGC 7440 BRWS | 11876970 |
| 24" Combi-Steam Oven XXL | | |
| 24" Steam oven combination XXL - PureLine MT EDST | DGC 7865 EDST | 11877020 |
| 24" Steam oven combination XXL - VitroLine MT OBSW | DGC 7860 OBSW | 11877000 |
| 24" Steam oven combination XXL - VitroLine MT BRWS | DGC 7860 BRWS | 11877010 |
| 24" Steam oven combination XXL - PureLine MT EDST | DGC 7860 EDST | 11876980 |

| | | |
|--|------------------------|----------|
| 24" Steam oven combination XXL - VitroLine MT GRGR | DGC 7860 GRGR | 11876990 |
| 30" Combi-Steam Oven XL | | |
| 30" Steam oven combination XL - PureLine MT EDST | DGC 7875 EDST | 11876050 |
| 30" Steam oven combination XL - PureLine MT EDST | DGC 7870 EDST | 11876080 |
| 30" Steam oven combination XL - PureLine MTs EDST | DGC 7670 EDST | 11876210 |
| 30" Steam oven combination XL - ContourLine MT EDST | DGC 7775 EDST | 11875760 |
| 30" Steam oven combination XL - ContourLine MT EDST | DGC 7770 EDST | 11875780 |
| 30" Steam oven combination XL - VitroLine MT OBSW | DGC 7870 OBSW | 11876190 |
| 30" Steam oven combination XL - VitroLine MT BRWS | DGC 7870 BRWS | 11876200 |
| 30" Steam oven combination XL - VitroLine MT GRGR | DGC 7870 GRGR | 11876180 |
| 30" Steam oven combination XL - ArtLine MT GRGR | DGC 7870 X GRGR | 11877030 |
| 30" Steam oven combination XL - ContourLine MTs EDST | DGC 7570 EDST | 11875790 |
| 30" Steam oven combination XL - ContourLine DS II EDST | DGC 7370 EDST | 11875800 |
| 30" Steam oven combination XL - VitroLine DS II BRWS | DGC 7470 BRWS | 11876270 |
| 30" Steam oven combination XL - PureLine DS II EDST | DGC 7470 EDST | 11876230 |
| 30" Steam oven combination XL - VitroLine DS II GRGR | DGC 7470 GRGR | 11876250 |
| 30" Steam oven combination XL - ArtLine Matt Black | DGC 7870 X Matte Black | 12423580 |
| 30" Steam oven combination XL - ArtLine Matt Black | DGC 7880 X Matte Black | 12423590 |
| 30" Combi-Steam Oven XXL | | |
| 30" Steam oven combination XXL - PureLine MTs EDST | DGC 7680 EDST | 11876470 |
| 30" Steam oven combination XXL - PureLine MTs EDST | DGC 7685 EDST | 11876450 |
| 30" Steam oven combination XXL - ArtLine MT GRGR | DGC 7880 X GRGR | 11877040 |
| 30" Steam oven combination XXL - ContourLine MTs EDST | DGC 7580 EDST | 11876020 |
| 30" Steam oven combination XXL - PureLine MT EDST | DGC 7880 EDST | 11876350 |
| 30" Steam oven combination XXL - ContourLine MTs EDST | DGC 7585 EDST | 11875850 |
| 30" Steam oven combination XXL - PureLine MT EDST | DGC 7885 EDST | 11876310 |
| 30" Steam oven combination XXL - ContourLine MT EDST | DGC 7780 EDST | 11875830 |
| 30" Steam oven combination XXL - VitroLine MT OBSW | DGC 7880 OBSW | 11876420 |
| 30" Steam oven combination XXL - VitroLine MT BRWS | DGC 7880 BRWS | 11876440 |
| 30" Steam oven combination XXL - VitroLine MT GRGR | DGC 7880 GRGR | 11876370 |
| 30" Steam oven combination XXL - ContourLine MT EDST | DGC 7785 EDST | 11875810 |

| Refrigeration | | |
|----------------------------------|------------------|----------|
| PerfectCool | | |
| 24" Integrated Fridge | KS 37472 iD | 10093870 |
| 24" Integrated Fridge | KS7793 D | 11749850 |
| 24" Integrated Freezer | FNS7794 E | 11911910 |
| 24" Integrated Bottom Mount | KFNS 37692 iDE-1 | 10595620 |
| 24" Integrated Bottom Mount | KFN7795 D | 11749900 |
| 30" Integrated Bottom Mount L | KFN 9855 iDE | 9623660 |
| 30" Integrated Bottom Mount R | KFN 9859iDE | 12153750 |
| 30" Integrated Bottom Mount R | KFN 9855 iDE | 9472260 |
| 30" Integrated Bottom Mount L | KFN 9859iDE | 12153760 |
| 36" French Door | KFNF 9955 iDE | 10277970 |
| 36" French Door | KFNF 9959iDE | 12153770 |
| 24" Freestanding | KFN 13923 DE | 10870510 |
| 24" Freestanding | KFN4799 DDE | 11951210 |
| 30" Freestanding (less features) | KFN4776 | 11954030 |
| 30" Freestanding | KFN 15943 DE | 10721530 |
| 24" Under-Counter | K 31222 Ui | 10799700 |

| Wine | | |
|--|--------------|----------|
| Under-Counter Wine w/sommelier | KWT 6312 UGS | 10028650 |
| Under-Counter Wine | KWT 6322 UG | 10028620 |
| Under-Counter Wine (CleanTouch St) | KWT 6322 UG | 11545800 |
| 24" PerfectCool Wine (Vi) | KWT 6722 iS | 11329860 |
| Refrigerator Columns | | |
| 24" Refrigerator Column Integrated - Right Hinge | K 2602 Vi | 11501360 |
| 24" Refrigerator Column Integrated - Left Hinge | K 2611 Vi | 10744860 |
| 24" Refrigerator Column Integrated - Left Hinge | K 2612 Vi | 11502560 |
| 24" Refrigerator Column SS Panel - Left Hinge | K 2601 SF | 10745060 |
| 24" Refrigerator Column SS Panel - Left Hinge | K 2602 SF | 11502570 |
| 30" Refrigerator Column Integrated - Right Hinge | K 2801 Vi | 10744220 |
| 30" Refrigerator Column Integrated - Right Hinge | K 2802 Vi | 11502590 |
| 30" Refrigerator Column Integrated - Left Hinge | K 2811 Vi | 10744230 |
| 30" Refrigerator Column Integrated - Left Hinge | K 2812 Vi | 11502640 |
| 30" Refrigerator Column SS Panel - Right Hinge | K 2801 SF | 10744290 |
| 30" Refrigerator Column SS Panel - Right Hinge | K 2802 SF | 11502700 |
| 30" Refrigerator Column SS Panel - Left Hinge | K 2811 SF | 10744270 |
| 36" Refrigerator Column Integrated - Right Hinge | K 2901 Vi | 10744550 |
| 36" Refrigerator Column Integrated - Right Hinge | K 2902 Vi | 11502710 |
| 36" Refrigerator Column Integrated - Left Hinge | K 2911 Vi | 10744600 |
| 36" Refrigerator Column Integrated - Left Hinge | K 2912 Vi | 11502720 |
| 36" Refrigerator Column SS Panel - Right Hinge | K 2901 SF | 10744840 |
| 36" Refrigerator Column SS Panel - Right Hinge | K 2902 SF | 11502840 |
| Freezers | | |
| 18" Freezer Column Integrated - Left Hinge | F 2412 Vi | 11503300 |
| 18" Freezer Column SS Panel - Left Hinge | F 2411 SF | 10745360 |
| 18" Freezer Column SS Panel - Left Hinge | F 2412 SF | 11503310 |
| 30" Freezer Column Integrated - Right Hinge | F 2801 Vi | 10744890 |
| 30" Freezer Column Integrated - Right Hinge | F 2802 Vi | 11503330 |
| 30" Freezer Column Integrated - Left Hinge | F 2811 Vi | 10744900 |
| 30" Freezer Column Integrated - Left Hinge | F 2812 Vi | 11503340 |
| 30" Freezer Column SS Panel - Left Hinge | F 2811 SF | 10744910 |
| 30" Freezer Column SS Panel - Left Hinge | F 2812 SF | 11503350 |
| 36" Freezer Column Integrated - Right Hinge | F 2901 Vi | 10744940 |
| 36" Freezer Column Integrated - Right Hinge | F 2902 Vi | 11503360 |
| 36" Freezer Column Integrated - Left Hinge | F 2911 Vi | 10745030 |
| 36" Freezer Column Integrated - Left Hinge | F 2912 Vi | 11503390 |
| 36" Freezer Column SS Panel - Left Hinge | F 2911 SF | 10745040 |
| 36" Freezer Column SS Panel - Left Hinge | F 2912 SF | 11503410 |
| 18" Freezer Column IWD Integrated - Right Hinge | F 2461 Vi | 10745050 |
| 18" Freezer Column IWD Integrated - Right Hinge | F 2462 Vi | 11503420 |
| 18" Freezer Column IWD Integrated - Left Hinge | F 2471 Vi | 10745080 |
| 18" Freezer Column IWD Integrated - Left Hinge | F 2472 Vi | 11503430 |
| 18" Freezer Column IWD SS Panel - Left Hinge | F 2471 SF | 10745470 |
| 18" Freezer Column IWD SS Panel - Left Hinge | F 2472 SF | 11503530 |
| 24" Freezer Column IWD Integrated - Right Hinge | F 2661 Vi | 10745610 |
| 24" Freezer Column IWD Integrated - Right Hinge | F 2662 Vi | 11503540 |
| 24" Freezer Column IWD Integrated - Left Hinge | F 2671 Vi | 10745680 |
| 24" Freezer Column IWD Integrated - Left Hinge | F 2672 Vi | 11503550 |
| 24" Freezer Column IWD SS Panel - Left Hinge | F 2671 SF | 10745720 |
| 24" Freezer Column IWD SS Panel - Left Hinge | F 2672 SF | 11503570 |

| Bottom Mounts | | |
|--|--------------|----------|
| 30" Bottom Mount Integrated - Right Hinge | KF 2802 Vi | 11502850 |
| 30" Bottom Mount Integrated - Left Hinge | KF 2811 Vi | 10745780 |
| 30" Bottom Mount Integrated - Left Hinge | KF 2812 Vi | 11502870 |
| 30" Bottom Mount SS Panel - Right Hinge | KF 2801 SF | 10745790 |
| 30" Bottom Mount SS Panel - Right Hinge | KF 2802 SF | 11502900 |
| 30" Bottom Mount SS Panel - Left Hinge | KF 2811 SF | 10745800 |
| 30" Bottom Mount SS Panel - Left Hinge | KF 2812 SF | 11502910 |
| 36" Bottom Mount Integrated - Right Hinge | KF 2901 Vi | 10745810 |
| 36" Bottom Mount Integrated - Right Hinge | KF 2902 Vi | 11502930 |
| 36" Bottom Mount Integrated - Left Hinge | KF 2911 Vi | 10745830 |
| 36" Bottom Mount Integrated - Left Hinge | KF 2912 Vi | 11502940 |
| 36" Bottom Mount SS Panel - Right Hinge | KF 2901 SF | 10745880 |
| 36" Bottom Mount SS Panel - Right Hinge | KF 2902 SF | 11502960 |
| 36" Bottom Mount SS Panel - Left Hinge | KF 2911 SF | 10745920 |
| 36" Bottom Mount SS Panel - Left Hinge | KF 2912 SF | 11502970 |
| 36" French Door Integrated | KF 2981 Vi | 10745930 |
| 36" French Door Integrated | KF 2982 Vi | 11503020 |
| 36" French Door SS Panel | KF 2981 SF | 10745950 |
| 36" French Door SS Panel | KF 2982 SF | 11503040 |
| Wine | | |
| 24" Wine Unit Integrated - Right Hinge | KWT 2602 Vi | 11503590 |
| 24" Wine Unit Integrated - Left Hinge | KWT 2611 Vi | 10746000 |
| 24" Wine Unit Integrated - Left Hinge | KWT 2612 Vi | 11503610 |
| 24" Wine Unit SS Panel - Right Hinge | KWT 2601 SF | 10746020 |
| 24" Wine Unit SS Panel - Right Hinge | KWT 2602 SF | 11503620 |
| 24" Wine Unit SS Panel - Left Hinge | KWT 2611 SF | 10746050 |
| 24" Wine Unit SS Panel - Left Hinge | KWT 2612 SF | 11503640 |
| 24" Wine Unit Integrated Sommelier - Right Hinge | KWT 2661 ViS | 10746060 |
| 24" Wine Unit Integrated Sommelier - Right Hinge | KWT 2662 ViS | 11503650 |
| 24" Wine Unit Integrated Sommelier - Left Hinge | KWT 2671 ViS | 10746080 |
| 24" Wine Unit Integrated Sommelier - Left Hinge | KWT 2672 ViS | 11503660 |
| 24" Wine Unit SS Panel Sommelier - Right Hinge | KWT 2661 SFS | 10746120 |
| 24" Wine Unit SS Panel Sommelier - Right Hinge | KWT 2662 SFS | 11503670 |

| Hoods | | |
|---|-----------|----------|
| Range Hood | | |
| 30" Wall Range Hood | DAR1220-3 | 11898130 |
| 36" Wall Range Hood | DAR1230-3 | 11898170 |
| 48" Wall Range Hood | DAR1250-3 | 11898190 |
| 36" Insert Hood | DAR 1130 | 9753480 |
| 48" Insert Hood | DAR 1150 | 9753510 |
| Wall Hood | | |
| 30" Wall Hood | DA398-7 | 10558810 |
| 36" Wall Hood | DA399-7 | 10558800 |
| 48" Wall Hood w/Wifi | DA5428W | 10934860 |
| 36" Incognito Wall Hood | DA6596 W | 9762220 |
| 36" Puristic Edition 6000 Wall Hood w/Wifi | DA6698 W | 10877010 |
| 36" Puristic Edition 6000 Wall Hood BRWS w/Wifi | DA6698 W | 10877030 |
| 36" Puristic Edition 6000 Wall Hood OBSW w/Wifi | DA6698 W | 10877060 |
| 36" Shape Wall Hood w/Wifi | DA6798 | 10876860 |

| | | |
|---|----------------|----------|
| 30" PUR Wall Hood | PUR88 W | 10743170 |
| 36" PUR Wall Hood | PUR98 W | 10743150 |
| 36" Pure Wall Hood GRGR | DA 6498 | 10811940 |
| Island Hood | | |
| 48" Puristic Varia Island Hood w/Wifi | DA4248 V D | 10877250 |
| 36" Incogntio Island Hood | DA6596 D | 9762240 |
| 36" Puristic Edition 6000 Island Hood BRWS w/Wifi | DA6698 D | 10877230 |
| 36" Puristic Edition 6000 Island Hood OBSW w/Wifi | DA6698 D | 10877240 |
| 36" PUR Island Hood | PUR98 D | 10743130 |
| Built Under Hood | | |
| 24" Built-Under Hood | DA1260 | 10662780 |
| 30" Built-Under Hood | DA1280 | 10451490 |
| Built In Hood | | |
| 44" Built In Hood w/Wifi | DA2518 | 10876740 |
| 32" Built In Hood w/Wifi | DA2588 | 10876770 |
| 35" Extra Slim Insert ss w/Wifi | DA 2698 ss | 10876810 |
| 35" Extra Slim Insert BRWS w/Wifi | DA 2698 brws | 10876830 |
| 44" Extra Slim Insert ss w/Wifi | DA 2628 | 10876800 |
| 24" Extra Slim Insert | DA 2360 | 10765130 |
| 36" Extra Slim Insert Insert | DA 2390 | 10743660 |
| 6" Adapter | DAA6 | 10811120 |
| 24" Built In Hood | DAS2620 | 11878490 |
| 36" Built in Hood | DAS2920 | 11878500 |
| 30" Built in hood w/ WiFi | DAS4720 | 11878520 |
| 36" Built in Hood w/ WiFi | DAS4930 | 11878550 |
| 36" Built in Hood Glass Canopy w/ WiFi | DAS4940 | 11878570 |
| 36" Built In Slimline Hood w/Wifi | DAS8930 | 11878590 |
| Downdraft | | |
| 30" Downdraft w/DAG1000 | DA6881+DAG1000 | 94001370 |
| 36" Downdraft w/DAG1000 | DA6891+DAG1000 | 94001390 |
| 30" Downdraft chassie | DA6881 | 10595900 |
| 36" Downdraft chassie | DA6891 | 10595910 |
| Ceiling Extractor | | |
| DA 2818 stainless steel | DA2818 | 9762150 |

| Cooktops | | |
|-----------------------------------|-----------------------|----------|
| Rangetop | | |
| 30" RangeTop 4 Burners G | KMR 1124-3 G | 11852270 |
| 30" RangeTop 4 Burners LP | KMR 1124-3 LP | 11852330 |
| 36" RangeTop 6 Burners G | KMR 1134-3 G | 11852340 |
| 36" RangeTop 6 Burners LP | KMR 1134-3 LP | 11852370 |
| 36" RangeTop 4 Burners+Grill G | KMR 1135-3 G grill | 11852380 |
| 36" RangeTop 4 Burners+Griddle G | KMR 1136-3 G griddle | 11852460 |
| 36" RangeTop 4 Burners+Griddle LP | KMR 1136-3 LP griddle | 11852550 |
| 48" RangeTop 8 Burners G | KMR 1354-3 G | 11852560 |
| 48" RangeTop 8 Burners LP | KMR 1354-3 LP | 11852570 |
| 48" RangeTop 6 Burners+Grill G | KMR 1355-3 G grill | 11852600 |
| 48" RangeTop 6 Burners+Griddle LP | KMR 1356-3 LP griddle | 11852660 |
| 48" RangeTop 6 Burners+Griddle G | KMR1356-3 G GD | 11852640 |
| Induction Cooktop | | |
| 24" Induction Cooktop | KM 7720 | 12074190 |

| | | |
|--|--------------|----------|
| 30" Induction Cooktop | KM 7730 | 12074200 |
| 36" Induction Cooktop | KM 7740 | 12074220 |
| 30" Induction PowerFlex Cooktop | KM 7735 FL | 12074210 |
| 36" Induction PowerFlex Cooktop | KM 7745 FL | 12074230 |
| 42" Induction PowerFlex Cooktop | KM 7755 FL | 12074240 |
| 24" Induction Cooktop | KM 6320 | 9775880 |
| 30" Induction Cooktop (possible extension) | KM 6360 | 9775890 |
| 30" Frameless Induction Cooktop | KM 6365 | 9775900 |
| 36" Induction Cooktop | KM 6370 | 9775910 |
| 36" Frameless Induction Cooktop | KM 6375 | 9775920 |
| 42" Induction Cooktop | KM 6377 | 9775930 |
| Gas Cooktop | | |
| 24" Gas Cooktop G | KM2021 G | 11471350 |
| 30" Gas Cooktop G | KM2032 G | 10735660 |
| 30" Gas Cooktop Hexa G | KM3464 G | 6792680 |
| 30" Gas Cooktop Linear G | KM3465 G | 6792700 |
| 30" Gas Cooktop Linear LP | KM3465 LP | 6792730 |
| 36" Gas Cooktop Hexa G | KM3474 G | 6792760 |
| 36" Gas Cooktop Hexa LP | KM3474 LP | 6792800 |
| 36" Gas Cooktop Linear G | KM3475 G | 6792770 |
| 36" Gas Cooktop Linear LP | KM3475 LP | 6792810 |
| 42" Gas Cooktop Hexa G | KM3484 G | 6792840 |
| 42" Gas Cooktop Linear G | KM3485 G | 6792850 |
| 42" Gas Cooktop Linear LP | KM3485 LP | 6792870 |
| 24" Gas on Glass Cooktop G | KM3010 G | 9272050 |
| 36" Gas on Glass Cooktop G | KM3054-1 G | 11766750 |
| 36" Flush Gas Cooktop G | KM2355 G | 9450190 |
| 36" Flush Gas Cooktop LP | KM2355 LP | 9456920 |
| Electric Cooktop | | |
| 24" Electric Cooktop w/Knobs 240V | KM5621 | 7821660 |
| 24" Electric Cooktop w/Knobs 208V | KM5621 | 7821670 |
| 30" Electric Cooktop w/Knobs 240V | KM5624 | 7821680 |
| 36" Electric Cooktop w/Knobs 240V | KM5627 | 7821700 |
| 36" Electric Cooktop w/Knobs 208V | KM5627 | 7821710 |
| 24" Electric Cooktop w/Direct Selection 240V | KM5820 | 7821720 |
| 30" Electric Cooktop w/Direct Selection 240V | KM5840 | 7821740 |
| 36" Electric Cooktop w/Direct Selection 240V | KM5860 | 7821760 |
| 42" Electric Cooktop w/Direct Selection 240V | KM5880 | 7821780 |
| Combi-Sets | | |
| 12" Wok Gas Burner G | CS1011-1 G | 11763790 |
| 12" Double Gas Burner G | CS1012-2 G | 11763800 |
| 12" Double Gas Burner LP | CS 1012-2 LP | 11763810 |
| 12" Electric Double Burner 240V | CS1112 E | 7141710 |
| 15" Tepan Yaki | CS1327 Y | 7890140 |
| Electric Boiler/Fryer | CS1411 F | 7141820 |

| Coffee Machines | | |
|---|---------------|----------|
| Coffee Built-in | | |
| 24" Coffee maker - VitroLine MT GRGR | CVA 7845 GRGR | 11733850 |
| 24" Coffee maker - VitroLine MT OBSW | CVA 7845 OBSW | 11754250 |
| 24" Coffee maker - VitroLine DS II BRWS | CVA 7440 BRWS | 11754290 |

| | | |
|---|-------------------|----------|
| 24" Coffee maker - VitroLine MT BRWS | CVA 7845 BRWS | 11754260 |
| 24" Coffee maker - PureLine MT EDST | CVA 7845 EDST | 11733840 |
| 24" Coffee maker - PureLine MT EDST | CVA 7840 EDST | 11754270 |
| 24" Coffee maker - PureLine DS II EDST | CVA 7445 EDST | 11754300 |
| 24" Coffee maker - PureLine DS II EDST | CVA 7440 EDST | 11733860 |
| 30" Coffee maker - ContourLine DS II EDST | CVA 7370 EDST | 11733830 |
| 30" Coffee maker - ContourLine MT EDST | CVA 7775 EDST | 11733820 |
| 24" Coffee maker - VitroLine DS II GRGR | CVA 7440 GRGR | 11754280 |
| 30" Coffee maker - Artline Matte Black | CVA7875 OBSW/MATT | 12579040 |

| Microwaves | | |
|-------------------|-----------|----------|
| Microwave | | |
| PureLine | M 7240 TC | 11845600 |
| PureLine | M 2241 SC | 11845640 |

| Drawers | | |
|---|----------------------|----------|
| Warming Drawer | | |
| 24" Warming drawer - VitroLine OBSW | ESW 7010 OBSW | 11794720 |
| 24" Warming drawer - VitroLine BRWS | ESW 7010 BRWS | 11794730 |
| 24" Warming drawer - VitroLine GRGR | ESW 7010 GRGR | 11794740 |
| 30" Warming drawer - Panel Ready | ESW 6380 FB | 9685060 |
| 30" Warming drawer - PureLine EDST | ESW 7670 EDST | 11794810 |
| 30" Warming drawer - PureLine EDST | ESW 7680 EDST | 11794860 |
| 30" Warming drawer - ContourLine EDST | ESW 7570 EDST | 11794790 |
| 30" Warming drawer - ContourLine EDST | ESW 7580 EDST | 11794800 |
| 30" Warming drawer - VitroLine OBSW | ESW 7670 OBSW | 11794840 |
| 30" Warming drawer - VitroLine BRWS | ESW 7670 BRWS | 11794850 |
| 30" Warming drawer - VitroLine GRGR | ESW 7670 GRGR | 11794820 |
| 30" Warming drawer - VitroLine OBSW | ESW 7680 OBSW | 11794880 |
| 30" Warming drawer - VitroLine BRWS | ESW 7680 BRWS | 11794890 |
| 30" Warming drawer - VitroLine GRGR | ESW 7680 GRGR | 11794870 |
| 30" Warming drawer - Artline Matte Black | ESW 7670 Matte Black | 12423660 |
| 30" Warming drawer - Artline Matte Black | ESW 7870 Matte Black | 12424280 |
| Vacuum Sealing Drawer | | |
| 24" Vacuum sealing drawer - VitroLine OBSW | EVS 7010 0 | 11845430 |
| 30" Vacuum sealing drawer - VitroLine OBSW | EVS 7670 0 | 11845480 |
| 30" Vacuum sealing drawer - Artline Matte Black | EVS 7670 Matte Black | 12423610 |