

**Miele**



The perfect couple  
at the touch of a button.

**Miele. Immer Besser.**





## Everybody loves something more than anything else in the world.

Little things, big things, beautiful moments and great memories that they only entrust to one. We want precious possessions to be well-protected, faithful friends to be handled with the utmost care, recipes to be perfect, and food to be always fresh. That's Miele. That's Immer Besser.







# Have a good start to the day - with an extra cup of coffee!

Treat yourself to a well-loved morning ritual. Miele's full range of milky coffee specialties now comes in pairs - with the OneTouch for Two function.



## **OneTouch for Two - Brew two coffee specialties at the same time**

All Countertop Coffee Machines feature the OneTouch for Two function. This allows you to make two delicious coffee specialties at the same time with only the touch of a button. Preparation takes less time, giving you more time for enjoying a delicious coffee drink with company.



# Suitable models for every kitchen.

## An overview of our countertop coffee machines.

At Miele, you have the choice between different colors and designs. You are certain to find the perfect coffee machine – all manufactured to Miele's legendary quality standards.



### **CM 6150 Countertop Coffee Machine**

Offers a sleek design with remarkable functionality. Features include the ability to brew several beverage specialties, 4 programmable user profiles, OneTouch for Two function and convenient cleaning programs along with dishwasher safe components. Available in Obsidian Black or Lotus White.



### **CM 6350 Countertop Coffee Machine**

Offering even more convenience and luxury. The CM 6350 carries out the same functionalities as the CM 6150, along with an array of additional amenities. This includes a hot water function, integrated cup warmer, LED lights and standard Stainless Steel Milk Flask. Available in Obsidian Black, Lotus White or Graphite Grey.

Exclusive design for exclusive tastes.  
The CM6 with new design.







# The highlights of the CM6 countertop coffee machine.



## **AromaticSystem**

Intelligent technology: the brew chamber mixes coffee and water perfectly, creating the perfect aroma.



## **Cappuccinatore**

Minimum effort required: hot milk or creamy milk froth is delivered straight to the cup, glass or small coffee pot.



## **Automatic rinsing of the milk pipework**

Excellent user convenience: after making special coffee beverages with milk, the machine is cleaned automatically.

### **Easily removable brew unit**

Easy to remove and clean: the guarantee for impeccable hygiene, long service life and perfect coffee enjoyment.



### **ComfortClean**

Thorough cleaning and value retention: many components are dishwasher-proof.



The perfect option for every kitchen.  
Explore our built-in coffee machines.











Obsidian Black





# The highlights of the built-in coffee machine.



## **EasyClick milk system**

Innovative and only available from Miele: the milk system simply clicks into place at the front and can be easily removed.



## **CupSensor**

Ideal distance: the CupSensor recognizes the rim of the cup and alters the position of the central spout accordingly.



## **ComfortDoor**

Easy access: convenient access to bean container, water container, grounds container and drip tray.

### Automatic rinsing of the milk pipework

Excellent user convenience: after making coffee beverages with milk, the machine is cleaned automatically.



### AromaticSystem

Intelligent technology: the brew chamber mixes coffee and water perfectly, creating the perfect aroma.



# CVA 6000



Model/Sales designation	CVA 6401	CVA 6405
<b>Construction type</b>		
Countertop bean-to-cup coffee machine	—	—
Built-in bean-to-cup coffee machine	●	●
<b>Design</b>		
PureLine/ContourLine	●/●	●/●
Control panel	DirectSensor	DirectSensor
<b>Beverage specialties</b>		
Espresso/Coffee/Long coffee	●/●/●	●/●/●
Cappuccino/Caffè Latte/Cappuccino Italiano/Café au lait	●/●/—/—	●/●/—/—
Latte Macchiato/Espresso Macchiato/Flat white/Caffè Americano	●/—/—/—	●/—/—/—
Hot water/Hot milk/Milk froth	●/●/●	●/●/●
Green tea/Black tea/Herbal tea/Fruit tea	—/—/—/—	—/—/—/—
<b>Consumer benefits</b>		
OneTouch/OneTouch for Two preparation	●/●	●/●
Flavor preserving conical grinding unit	●	●
Second type of coffee possible using ground coffee	●	●
Programmable user profile	10	10
Grinding grade adjustable/Grinding grade programmable	●/●	●/●
Water quantity/Water temperature programmable	●/●	●/●
Pre-brewing/Milk quantity/Milk froth quantity programmable	●/●/●	●/●/●
Coffee/tea pot function	●/—	●/—
<b>Control panel</b>		
Choice of language/clock display/date display	●/●/●	●/●/●
CupSensor	—	—
Height adjustment of infinitely adjustable central spout in inches (mm)	3 <sup>3</sup> / <sub>8</sub> " (83) – 6 <sup>1</sup> / <sub>2</sub> " (165)	3 <sup>3</sup> / <sub>8</sub> " (83) – 6 <sup>1</sup> / <sub>2</sub> " (165)
ComfortDoor/BrilliantLight/Concealed door handle	●/●/●	●/●/●
Removable bean container/Nespresso capsule magazine	●/—	●/—
Capacity of coffee bean container in oz (g)	17.64 oz (500)	17.64 oz (500)
Capacity of waste container in portions	15	15
Capacity of water container in fl oz (l)	77.77 oz (2.3)	77.77 oz (2.3)
Switch-on time programmable/Switch-off time programmable	●/●	●/●
Standby time programmable/Time buffer in h	●/200	●/200
Fresh water connection	—	●
<b>Cleaning convenience</b>		
Convenient cleaning program/ComfortClean	●/●	●/●
AutoDescale function	—	—
Automatic rinsing of the milk pipework from the water container	●	●
Removable milk pipework/brew unit	●/●	●/●
<b>Efficiency and sustainability</b>		
Energy-saving Eco mode option	●	●
<b>Networking of domestic appliances</b>		
Miele@home	—	—
<b>Safety</b>		
System lock	●	●
<b>Technical data</b>		
Appliance dimensions in inches (W x H x D)	23 <sup>7</sup> / <sub>16</sub> " x 17 <sup>15</sup> / <sub>16</sub> " x 19"	23 <sup>7</sup> / <sub>16</sub> " x 17 <sup>15</sup> / <sub>16</sub> " x 19"
Door depth when open in inches (mm)	23 <sup>7</sup> / <sub>16</sub> " (594)	23 <sup>7</sup> / <sub>16</sub> " (594)
Total connected load in kW	1.5	1.5
Voltage in V/Fuse rating in A	120/15	120/15
Length of water intake hose/connection wire in ft	—/5	—/5
<b>Standard accessories</b>		
Glass/stainless steel milk flask	●/—	●/—
Descaler/cleaning tablets	●/●	●/●



# CVA 6000



Model/Sales designation	CVA 6800	CVA 6805
<b>Construction type</b>		
Countertop bean-to-cup coffee machine	–	–
Built-in bean-to-cup coffee machine	●	●
<b>Design</b>		
PureLine/ContourLine	●/●	●/●
Control panel	M Touch	M Touch
<b>Beverage specialties</b>		
Espresso/Coffee/Long coffee	●/●/●	●/●/●
Cappuccino/Caffè Latte/Cappuccino Italiano/Café au lait	●/●/–/–	●/●/–/–
Latte Macchiato/Espresso Macchiato/Flat white/Caffè Americano	●/–/–/–	●/–/–/–
Hot water/Hot milk/Milk froth	●/●/●	●/●/●
Green tea/Black tea/Herbal tea/Fruit tea	–/–/–/–	–/–/–/–
<b>Consumer benefits</b>		
OneTouch/OneTouch for Two preparation	●/●	●/●
Flavor preserving conical grinding unit	●	●
Second type of coffee possible using ground coffee	●	●
Programmable user profile	10	10
Grinding grade adjustable/Grinding grade programmable	●/●	●/●
Water quantity/Water temperature programmable	●/●	●/●
Pre-brewing/Milk quantity/Milk froth quantity programmable	●/●/●	●/●/●
Coffee/tea pot function	●/–	●/–
<b>Control panel</b>		
Choice of language/clock display/date display	●/●/●	●/●/●
CupSensor	●	●
Height adjustment of infinitely adjustable central spout in inches (mm)	3 <sup>3</sup> / <sub>8</sub> " (83) – 6 <sup>1</sup> / <sub>2</sub> " (165)	3 <sup>3</sup> / <sub>8</sub> " (83) – 6 <sup>1</sup> / <sub>2</sub> " (165)
ComfortDoor/BrilliantLight/Concealed door handle	●/●/●	●/●/●
Removable bean container/Nespresso capsule magazine	●/–	●/–
Capacity of coffee bean container in oz (g)	17.64 oz (500)	17.64 oz (500)
Capacity of waste container in portions	15	15
Capacity of water container in fl oz (l)	77.77 oz (2.3)	77.77 oz (2.3)
Switch-on time programmable/Switch-off time programmable	●/●	●/●
Standby time programmable/Time buffer in h	●/200	●/200
Fresh water connection	–	●
<b>Cleaning convenience</b>		
Convenient cleaning program/ComfortClean	●/●	●/●
AutoDescale function	–	–
Automatic rinsing of the milk pipework from the water container	●	●
Removable milk pipework/brew unit	●/●	●/●
<b>Efficiency and sustainability</b>		
Energy-saving Eco mode option	●	●
<b>Networking of domestic appliances</b>		
Miele@home	–	–
<b>Safety</b>		
System lock	●	●
<b>Technical data</b>		
Appliance dimensions in inches (W x H x D)	23 <sup>7</sup> / <sub>16</sub> " x 17 <sup>15</sup> / <sub>16</sub> " x 19"	23 <sup>7</sup> / <sub>16</sub> " x 17 <sup>15</sup> / <sub>16</sub> " x 19"
Door depth when open in inches (mm)	23 <sup>7</sup> / <sub>16</sub> " (594)	23 <sup>7</sup> / <sub>16</sub> " (594)
Total connected load in kW	1.5	1.5
Voltage in V/Fuse rating in A	120/15	120/15
Length of water intake hose/connection wire in ft	–/5	–/5
<b>Standard accessories</b>		
Glass/stainless steel milk flask	●/–	●/–
Descaler/cleaning tablets	●/●	●/●

# CM6



Model/Sales designation	CM 6150	CM 6350
<b>Construction type</b>		
Countertop bean-to-cup coffee machine	●	●
Built-in bean-to-cup coffee machine	–	–
<b>Design</b>		
PureLine/ContourLine	–/–	–/–
Control panel	DirectSensor	DirectSensor
<b>Beverage specialties</b>		
Espresso/Coffee/Long coffee	●/●/●	●/●/●
Cappuccino/Caffè Latte/Cappuccino Italiano/Café au lait	●/●/–/–	●/●/–/–
Latte Macchiato/Espresso Macchiato/Flat white/Caffè Americano	●/–/–/–	●/–/–/–
Hot water/Hot milk/Milk froth	–/●/●	●/●/●
Green tea/Black tea/Herbal tea/Fruit tea	–/–/–/–	–/–/–/–
<b>Consumer benefits</b>		
OneTouch/OneTouch for Two preparation	●/●	●/●
Flavor preserving conical grinding unit	●	●
Second type of coffee possible using ground coffee	●	●
Programmable user profile	4	4
Grinding grade adjustable/Grinding grade programmable	●/●	●/●
Water quantity/Water temperature programmable	●/●	●/●
Pre-brewing/Milk quantity/Milk froth quantity programmable	●/●/●	●/●/●
Coffee/tea pot function	●/–	●/–
<b>Control panel</b>		
Choice of language/clock display/date display	●/–/–	●/–/–
CupSensor	–	–
Height adjustment of infinitely adjustable central spout in inches (mm)	3.15" (80) – 5.51" (140)	3.15" (80) – 5.51" (140)
ComfortDoor/BrilliantLight/Concealed door handle	–/–/–	–/●/–
Removable bean container/Nespresso capsule magazine	–/–	–/–
Capacity of coffee bean container in oz (g)	10.58 (300)	10.58 (300)
Capacity of waste container in portions	10	10
Capacity of water container in fl oz (l)	61 oz (1.8)	61 oz (1.8)
Switch-on time programmable/Switch-off time programmable	●/●	●/●
Standby time programmable/Time buffer in h	●/–	●/–
Fresh water connection	–	–
<b>Cleaning convenience</b>		
Convenient cleaning program/ComfortClean	●/●	●/●
AutoDescale function	–	–
Automatic rinsing of the milk pipework from the water container	●	●
Removable milk pipework/brew unit	●/●	●/●
<b>Efficiency and sustainability</b>		
Energy-saving Eco mode option	●	●
<b>Networking of domestic appliances</b>		
Miele@home	–	–
<b>Safety</b>		
System lock	●	●
<b>Technical data</b>		
Appliance dimensions in inches (W x H x D)	10" x 14 1/8" x 16 3/4"	10" x 14 1/8" x 16 3/4"
Door depth when open in inches (mm)	–	–
Total connected load in kW	1.5	1.5
Voltage in V/Fuse rating in A	120/15	120/15
Length of water intake hose/connection wire in ft	–/4' 7"	–/4' 7"
<b>Standard accessories</b>		
Glass/stainless steel milk flask	–/–	–/●
Descaler/cleaning tablets	●/●	●/●



Miele, Inc.  
9 Independence Way  
Princeton, NJ 08540

[mieleusa.com](http://mieleusa.com)  
[moreinfo@mieleusa.com](mailto:moreinfo@mieleusa.com)

800.843.7231

Visit one of Miele's Experience Centers:

Beverly Hills  
Boca Raton  
Chicago  
Coral Gables  
Dallas  
Manhattan  
Princeton  
San Francisco  
Scottsdale  
Seattle  
Tysons Corner  
Wellesley