



Miele. For everything you really love.  
**The perfect finish – whatever your style.**











The perfect finish – whatever your style.

Whether it's a summer dress or your favorite jeans, you can trust the exclusive new Miele FashionMaster – it will change the way you iron forever. Look forward to countless chic features such as the gentle-glide soleplate with honeycomb structure. The finishing touch for every look, every time.

**Miele. For everything you really love.**







The FashionMaster also stands out with its functional and attractive design. Even when folded it is almost too good-looking to be hidden away.



# A new era in laundry care

## Miele FashionMaster steam ironing system

With the compact combination of iron, steam generator and ironing table, the often unloved task of ironing turns into an uplifting and fun activity.





# Product Highlights

**Exclusive  
to Miele**

## Honeycomb soleplate

It already ensures outstanding gentle treatment of laundry in washing machines and tumble dryers: the patented honeycomb drum. The same principle is also applied to the FashionMaster. The unique honeycomb soleplate<sup>1)</sup> achieves best ironing results combined with perfect laundry care. Unlike conventional irons, steam is distributed quickly and evenly along the channels between the hexagons. This creates a film of steam which allows the iron to glide effortlessly, but at the same time effectively, over textiles.





**Exclusive  
to Miele**

### 1-2-Lift-System

Two easy steps to set up, requiring little or no effort at all! Ready for use in next to no time thanks to the patented<sup>2)</sup> 1-2-Lift-System.



### Variable height adjustment

Simply ergonomic: The built-in gas-pressure lift brings the ironing table to the perfect working height. (33"-40").



### Active ironing table

Best ironing results: Suction and inflation functions ensure excellent steam application and hold the textiles in place.



**Exclusive  
to Miele**

### Steamer/Steam Jet

Easy to handle: Hanging garments such as dresses, jackets and curtains are gently smoothed and brought back into shape.

\* depends on model

<sup>1)</sup> European patent EP 2 233 632 B1

<sup>2)</sup> European patent EP 2 169 108 B1





#### **Steam**

More than merely blowing hot air: 4 bar steam pressure and a consistent steam output ensures professional ironing results.



#### **Non-stick soleplate**

Perfect care: Sequins, prints, delicate fabrics and dark items are all ironed without creating shiny patches.



#### **Suction function**

Intensive and smooth: The suction function enables more steam to penetrate the fabric, holding them in place so they are perfectly smoothed.



#### **Inflation function**

Virtually weightless: The air cushion allows the textile to be smoothed but not pressed.



### Ironing multi-layered items

Saves physical strength and time: Multi-layered items can be ironed in a single process. Ironing both sides of a garment is no longer necessary!



### ComfortZone

Ironing in a single process: The entire front half of a shirt or blouse can be ironed without having to re-position.



### Water tank

Long-lasting: The water tank holds up to 0.33 gal – sufficient for one full hour of ironing.



### Display

Always in your sight: The display informs you of the state of the appliance and prompts you, for example, when the water tank needs replenishing.









# Product overview



Design	B 3312	B 3847
Appliance color	Lotus white	Lotus white
Iron color	Anthracite/Grey	Anthracite/Lotos white
Ironing board color	Grey	Anthracite
Display	Single line	Single line
Perfect ironing results		
Chrome-plated aluminium honeycomb soleplate	●	●
Steam pressure in bar	3.5	4.0
Vertical steam	●	●
Steam pulse/Continuous steam	●/●	●/●
Steamer	–	●
Active ironing table (inflation and suction function)	●	●
2-stage fan/Non-stick soleplate	–/●	●/●
Time-saving ironing		
Water container volume in gallons	0.33	0.33
Removable water container	●	●
Ironing multi-layered items	●	●
User convenience		
All-in-one/1-2 Lift system	●/●	●/●
Infinitely variable height adjustment with gas pressure stay, in inches	33 – 40	33 – 40
Selection of water hardness/Automatic fan switch-on/switch-off	●/●	●/●
Fan memory function/Prompted descaling/Automatic rinsing	●/●/●	●/●/●
Storage compartment for iron/Storage compartment for power cord	●/●	●/●
Safety		
CoolDown function/AutoOff function	●/●	●/●
Technical data		
Entire machine		
Weight in lbs/Gross weight (incl. packaging) in lbs	64/73	66/75
Dimensions (folded) in inches (W x H x D)	19 x 50 x 15	19 x 50 x 15
Dimensions (set up) in inches (W x H x D)	19 x 38 x 58	19 x 38 x 58
Dimensions (packaging) in inches (W x H x D)	54 x 18 x 20	54 x 18 x 20
Connection cable (length in inches)	98	98
Hand iron	●	●
Steamer		
Brush attachment	–	●
Rated loads		
Rated voltage (V)	120	120
Fuse rating (A)/Rated load (kW)/Nominal rating (W)	15/1,7/1700	15/1,7/1700
Accessories supplied		
Non-stick soleplate/Steamer/Basic ironing table cover	●/–/●	●/●/–
Premium ironing table cover (particularly heat resistant)	–	●
Steam hose holder/Mains connection cable holder	●/●	●/●
Test strips to test water hardness/Descaling tablets	●/●	●/●
Optional accessories		
Steamer/Premium ironing table cover/Basic ironing table cover	●/●/●	●/●/●
UMRP & MAP/Retail Pricing	\$1,999/\$2,199	\$2,499/\$2,699
Item number	13331221USA	13384721USA



Miele, Inc.  
9 Independence Way  
Princeton, New Jersey 08540  
Phone: 800.843.7231  
[mieleusa.com](http://mieleusa.com)