

Miele
IMMER BESSER



Introducing Miele's PerfectCool French Door
KFNF 9955 iDE

Fresher food by design.

Introducing the 36" French Door refrigerator to the PerfectCool series.

The new Miele PerfectCool series offers ideal storage conditions for food without the loss of vitamins and flavor. With respect to design and user convenience, Miele PerfectCool appliances are first choice.

Now with the 36" French Door unit, the compact design blends in harmoniously with kitchen cabinetry. Clear, concise and convenient controls keep the user well informed. The ideal conditions for simplifying your life!



PerfectFresh Drawers
For perfect storage conditions: Innovative Miele technology keeps fruits and vegetables fresh even longer.



LED Lighting
Maintenance-free and energy saving: Efficient and durable LEDs ensure perfect illumination of the interior.



Double-Freezer Drawers
Ideal storage solutions: Two SoftClose drawers with interior lights provide the best storage solution.



Comfort Clean Door Bins
Fast cleaning: The high-quality shelves on the inside of the door can be easily cleaned in a Miele dishwasher.




Gallon Door Bins
Convenience: The gallon door bins allow for larger items to be stored for easy access.




Sabbath Mode
Worry-Free technology: Sabbath mode capabilities allow for religious observance.

KFNF 9955 iDE

Specifications



- A = 3" (76 mm)
- B = 79^{13/16}" (2027 mm)
- C = 35^{13/16}" (910 mm)
- D = 3" (76 mm)
- E = 24" (610 mm)
- G = 42^{7/16}" (1078 mm)
- H = 37^{1/8}" (943 mm)



Unit	
Overall Unit Width	35 ^{13/16} " (910 mm)
Overall Unit Height	79 ^{13/16} " (2027 mm)
Overall Unit Depth	24" (610 mm)
Niche	
Minimum Cabinet Opening Width	36" (915 mm)
Minimum Cabinet Opening Height	80" (2032 mm)
Minimum Cabinet Opening Depth	≥ 24" (610 mm)
Plumbing	
Water Supply Requirements	Connect to a cold water supply only. Must be connected to a shut-off valve. The water shut-off valve must be accessible after installation. The water pressure must be between 22 psi (1.5 bar) and may not exceed 87 psi (6 bar). If the pressure is higher than 87 psi (6 bar), a pressure reducing valve must be installed.
Water Connection Line	Use 1/4" OD copper line. This is not supplied with the appliance.
Electrical	
Electrical Requirements - Volts/Amps	110V / 120V, 60Hz, 15 Amps (single) 110V / 120V, 60Hz, 20 Amps (side-by-side)
Power Cord - Plug and Length	NEMA 5-15 plug, 7' 10 ^{1/2} " (2.4 m)
Custom Panel	
Maximum Panel Weight	Top Panels - 26 ^{1/2} lbs (12 kg) Middle Panel - 26 ^{1/2} lbs (12 kg) Bottom Panel - 26 ^{1/2} lbs (12 kg)
Maximum Panel Thickness	3/4" (19 mm)
Minimum Panel Thickness	5/8" (16 mm)

Experience Miele First-hand.

Discover what Miele has to offer at your local Miele Experience Center or browse our full-line of appliances, vacuums, and accessories at mieleusa.com

Beverly Hills
189 North Robertson Blvd.
Beverly Hills, CA 90211
beverlyhillscenter@mieleusa.com

Princeton
9 Independence Way
Princeton, NJ 08540
princetoncenter@mieleusa.com

Boca Raton
7680 North Federal Highway
Boca Raton, FL 33487
bocaratoncenter@mieleusa.com

San Francisco
Sobel Building, 680 8th St.
Suite 155
San Francisco, CA 94103
sanfranciscocenter@mieleusa.com

Chicago
222 Merchandise Mart Plaza
Suite 33
Chicago, IL 60654
chicagocenter@mieleusa.com

Scottsdale
7550 E. Greenway Rd.
Suite 100
Scottsdale, AZ 85260
scottsdalecenter@mieleusa.com

Coral Gables
4218 Ponce de Leon Blvd.
Coral Gables, FL 33146
coralgablescenter@mieleusa.com

Seattle
13500 Bel-Red Rd.
Suite 1
Bellevue, WA 98005
seattlecenter@mieleusa.com

Dallas
1700 Oak Lawn Ave.
Suite 200
Dallas, TX 75207
dallascenter@mieleusa.com

Tysons Corner
Fairfax Square 1
8065 Leesburg Pike
Suite 110
Vienna, VA 22182
tysonscornercenter@mieleusa.com

Manhattan
A&D Building, 150 East 58th St.
9th Floor
New York, NY 10155
newyorkcenter@mieleusa.com

Wellesley
555 Washington St.
Wellesley, MA 02482
wellesleycenter@mieleusa.com