


Miele



Miele's EcoFlex
Dishwasher Series

Immer Besser
(forever better)





Our Pledge —

When our two great-grandfathers were in the process of founding the Miele company, they had to make sure they stood apart from the competition in order to be successful. There are effectively only two ways of doing this: either by being cheaper than the rest or by being better than the rest. It is not really possible to be both at the same time.

They decided to be “better” than the rest.

Numerous best in class awards and certificates attest to the fact that Miele has continued to renew its commitment to being “Immer Besser” throughout the past 120 years. However, the millions of satisfied customers around the world are perhaps the most important endorsement.

At the heart of this success lies a continuity of values and goals which are typically only found in companies which have been family-run for generations, rather than in businesses which are guided by the often short-term interests of the stock market.

It is in this sense that Miele has embodied first-class product quality and German engineering since 1899. Miele also stands in equal measure for respect, fairness and mutual esteem towards sales partners, customers, suppliers, employees and neighbors. Buying a Miele is an environmentally friendly decision. We ensure this by using methods of production that save resources as well by producing products which set new standards in terms of their consumption of electricity, water and detergent — and save you money at the same time.

As directors and co-proprietors of the fourth generation of our business we promise you that this will not change.

Markus Miele Reinhard Zinkann

Dr. Markus Miele

Dr. Reinhard Zinkann





Celebrating Over 30 Years of Miele's Cutlery Tray

Miele originated the cutlery tray in 1987 and was awarded patents for this development lasting 20 years. Now, with the patented 3D+ cutlery tray, Miele continues to set the standard for innovation, design, and performance.

Miele's cutlery tray offers numerous benefits:

- a dedicated, full spray arm for superb cleaning results
- increased lower basket capacity
- easy and hygienic loading and unloading

The 3D+ cutlery tray has increased flexibility which allows for tall stemware in the upper basket. No other brand but Miele can offer the innovation of the unique 3D+ cutlery tray. It offers more loading capacity, better cleaning results, and enhanced flexibility.

Fully Integrated (Vi) Models*



	<i>Classic Plus</i>	<i>Crystal</i>	<i>Dimension</i>	<i>Lumen</i>	<i>Diamond</i>
	<i>Basket/Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>
Custom Panel Ready	Basket G4998 Vi 21499861USA Tray G4998 SCVi 21499862USA	G6665 SCVi 21666562USA	G6785 SCVi 21678562USA	G6875 SCVi 21687562USA	
Custom Panel Ready (Knock2Open)				G6885 SCVi K2O 21688562USA	G6987 SCVi K2O 21698762USA

<i>Features</i>					
Water Softener		•	•	•	•
Miele@Mobile				•	•
AutoOpen Drying		•	•	•	•

<i>Programs</i>					
Normal	•	•	•	•	•
Express/QuickIntenseWash	•/-	-/•	-/•	-/•	-/•
Pots & Pans	•	•	•	•	•
SaniWash	•	•	•	•	•
Rinse & Hold	•	•	•	•	•
China & Crystal		•	•	•	•
Extra Quiet			•	•	•
Grates & Filters			•	•	•
Clean Machine			•	•	•
Economy			•	•	•
Energy Saver				•	•
Tall Items					•
Glass - No Rinse Aid					•
Sensor Wash				•	•

<i>Options</i>					
Delay Start	•	•			
Short	•	•	•	•	•
FlexiTimer			•	•	•
Extra Economical			•	•	•
Intensive Lower Rack				•	•
Extra Dry				•	•
Soak					•
Pre-Rinse					•

*Diamond model shown

Fully Integrated (SF) Models*



	<i>Classic Plus</i>		<i>Crystal</i>	<i>Dimension</i>	<i>Lumen</i>
	<i>Basket</i>	<i>Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>
Clean Touch Steel™	G4998 Vi SF 21499863USA	G4998 SCVi SF 21499864USA	G6665 SCVi SF 21666563USA	G6785 SCVi SF 21678563USA	G6875 SCVi SF 21687563USA

<i>Features</i>					
Water Softener			•	•	•
Miele@Mobile					•
AutoOpen Drying			•	•	•

<i>Programs</i>					
Normal	•	•	•	•	•
Express/QuickIntenseWash	•/-	•/-	-/•	-/•	-/•
Pots & Pans	•	•	•	•	•
SaniWash	•	•	•	•	•
Rinse & Hold	•	•	•	•	•
China & Crystal			•	•	•
Extra Quiet				•	•
Grates & Filters				•	•
Clean Machine				•	•
Economy				•	•
Energy Saver					•
Tall Items					
Glass - No Rinse Aid					
Sensor Wash					•

<i>Options</i>					
Delay Start	•	•	•		
Short	•	•	•	•	•
FlexiTimer				•	•
Extra Economical				•	•
Intensive Lower Rack					•
Extra Dry					•
Soak					
Pre-Rinse					

*Lumen model shown

Slimline & ADA Compliant Models*



	<i>High Toe-Kick</i>		<i>Slimline</i>
	<i>Classic Plus</i>	<i>Lumen</i>	<i>Dimension Slimline</i>
	<i>Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>	
Custom Panel Ready	G4993 SCVi 21499362 USA		G4720 SCi 21472057USA
			G4780 SCVi 21478062USA
Custom Panel Ready (Knock 2 Open)		G6880 SCVi K2o 21688062USA	

<i>Features</i>			
Water Softener		•	•
Miele@Mobile		•	
AutoOpen Drying		•	•

<i>Programs</i>			
Normal	•	•	•
Express/ QuickIntenseWash	•/-	-/•	-/•
Pots & Pans	•	•	•
SaniWash	•	•	•
Rinse & Hold	•	•	•
China & Crystal		•	•
Extra Quiet		•	
Grates & Filters		•	
Clean Machine		•	
Economy		•	
Energy Saver		•	
Tall Items			
Glass - No Rinse Aid			
Sensor Wash		•	

<i>Options</i>			
Delay Start	•		•
Short	•	•	•
FlexiTimer		•	
Extra Economical		•	
Intensive Lower Rack		•	
Extra Dry		•	
Soak			
Pre-Rinse			

*Dimension model shown

Pre-Finished Models*



	Classic Plus		Crystal		Dimension
	Basket	Cutlery Tray	Basket	3D+ Cutlery Tray	3D+ Cutlery Tray
Black	G4948 U 21494824USA	G4948 SCU 21494834USA			G6745 SCU 21674534USA
White	G4948 U 21494826USA	G4948 SCU 21494836USA			G6745 SCU 21674536USA
Clean Touch Steel™	G4948 U 21494827USA	G4948 SCU 21494837USA	G6625 U 21662527USA	G6625 SCU 21662537USA	G6745 SCU 21674537USA

Features

Water Softener			•	•	•
Miele@Mobile					
AutoOpen Drying			•	•	•

Programs

Normal	•	•	•	•	•
Express/ QuickIntenseWash	•/-	•/-	-/•	-/•	-/•
Pots & Pans	•	•	•	•	•
SaniWash	•	•	•	•	•
Rinse & Hold	•	•	•	•	•
China & Crystal			•	•	•
Extra Quiet					•
Grates & Filters					•
Clean Machine					•
Economy					
Energy Saver					
Tall Items					
Glass - No Rinse Aid					
Sensor Wash					

Options

Delay Start	•	•	•	•	
Short	•	•	•	•	•
FlexiTimer					•
Extra Economical					•
Intensive Lower Rack					
Extra Dry					
Soak					
Pre-Rinse					

*Dimension model shown

Integrated (i) Models*



	<i>Lumen</i>	<i>Diamond</i>
	<i>3D+ Cutlery Tray</i>	<i>3D+ Cutlery Tray</i>
Custom Panel Ready	G6835 SCi 21683557USA	G6935 SCi 2169357USA

<i>Features</i>		
Water Softener	•	•
Miele@Mobile	•	•
AutoOpen Drying	•	•

<i>Programs</i>		
Normal	•	•
Express/ QuickIntenseWash	-/•	-/•
Pots & Pans	•	•
SaniWash	•	•
Rinse & Hold	•	•
China & Crystal	•	•
Extra Quiet	•	•
Grates & Filters	•	•
Clean Machine	•	•
Economy	•	•
Energy Saver	•	•
Tall Items		•
Glass - No Rinse Aid		•
Sensor Wash	•	•

<i>Options</i>		
Delay Start		
Short	•	•
FlexiTimer	•	•
Extra Economical	•	•
Intensive Lower Rack	•	•
Extra Dry	•	•
Soak		•
Pre-Rinse		•

*Diamond model shown

Integration Options

Choose the right model for you and your home. Miele offers the ultimate in convenience and seamless design integration.

Pre-Finished Models

Pre-finished models are complete with control and door panel. Generally, these models are available in black, white, or Clean Touch Steel™.



Integrated (“i”) Models

Integrated dishwashers have a visible control panel and are designed to fit with a custom door panel that reflects the cabinetry decor of your kitchen.



Fully Integrated (“Vi”) Models

These units can either disappear into your cabinetry by adding a custom front panel or stand out as a robust appliance with a full Clean Touch Steel™ panel. The elegant stainless steel control panel is integrated on top of the door and is only visible when the door is ajar.



Fully Integrated (“SF”) Models

For convenience, Miele offers fully integrated, pre-finished models that are already equipped with a Clean Touch Steel™ door panel, a 4-inch toe-kick and straight door handle.



Clean Touch Steel™ Door Panels



Front Panel with Handle

Integrated	Fully Integrated		Slimline
	4" Toekick	6" Toekick	4" Toekick
GFV 60/65-1 4" Toekick 21995335D UMRP/MAP: \$169	GFVi 614/77-1 PureLine 21996078D UMRP/MAP: \$275	GFVi 605/72-1 Profi 21995374D UMRP/MAP: \$295	GFV 45/65-1 Integrated 21995368D UMRP/MAP: \$169
GFV 60/60-1 6" Toekick 21995332D UMRP/MAP: \$169	GFVi 615/77-1 ContourLine 21996079D UMRP/MAP: \$275	GFVi 609/72-1 Square 21995340D UMRP/MAP: \$295	GFVi 459/77-1 Straight 21995370D UMRP/MAP: \$295
	GFVi 616/77-1 Range Panel 21996290D UMRP/MAP: \$299	GFVi 6010/72-1 Straight 21995456D UMRP/MAP: \$295	GFVi 4510/77 Square 21995459D UMRP/MAP: \$295
	GFVi 605/77-1 Profi 21995375D UMRP/MAP: \$295	GFVi 6011/72-1 Signature 21995458D UMRP/MAP: \$295	GFVi 4511/77-1 Signature 21995460D UMRP/MAP: \$295
	GFVi 608/77-2 Classic 21995376D UMRP/MAP: \$295	GFVi 615/72-1 ContourLine 21996080D UMRP/MAP: \$275	
	GFVi 608/77-2 Classic 21995377D UMRP/MAP: \$295		
	GFVi 609/77-1 Square 21995341D UMRP/MAP: \$295		
	GFVi 6010/77-1 Straight 21995457D UMRP/MAP: \$295		

Front Panel without Handle

Integrated	Fully Integrated		Slimline
	4" Toekick	6" Toekick	
	GFVi 603/77-1 4" Toekick 21995337D UMRP/MAP: \$295		GFVi 453/77-1 4" Toekick 21995371D UMRP/MAP: \$295
			GFVi 453/72-1 6" Toekick 21995345D UMRP/MAP: \$295

Highlights




QuickIntenseWash*

So easy, so fast.

The new QuickIntenseWash program solves the problem of quick cleaning that actually performs. Top cleaning performance: best cleaning and drying results on normally soiled dishes in 58 minutes.**

**Program duration with hot water connection.



Miele@Mobile*

Keep everything under control.

With the Miele@Mobile app on your phone or tablet, you can monitor your dishwasher's progress from anywhere.

*Available on select models



Perfect GlassCare*

Miele's intelligent Perfect GlassCare system constantly monitors the rinse water's mineral content, while other sensors check temperature, cycle intensity and even air flow — ensuring optimal performance and consistent results with each use.

Miele is the only dishwasher recommended by legendary stemware company Riedel. Handled properly, Riedel glasses can last up to 1,500 washing cycles or an average of 20 years.



*Available on Crystal, Dimension, Lumen, and Diamond models

Miele



Miele, Inc.
9 Independence Way
Princeton, NJ 08540
☎800.843.7231
🌐mieleusa.com

B999932_12-18