

Spring 2018 edition

**Miele**

# The Everything Washer Meets the Anywhere Dryer

## W 1 T1

Miele. Immer Besser.











# Welcome to Miele

## IMMER BESSER (forever better) - our pledge

When our two great grandfathers founded the Miele company, they had to make sure they stood apart from the competition in order to be successful. There are effectively only two ways of doing this: either by being cheaper than the rest or by being better than the rest. It is not really possible to be both at the same time.

They decided to be "better" than the rest.

Numerous best in class awards and certificates attest to the fact that Miele has continued to renew its commitment to being "immer besser" (forever better) throughout the past 119 years. However, the millions of satisfied customers around the world are perhaps the most important endorsement.

At the heart of this success lies a continuity of values and goals which are typically only found in companies which have been family-run for generations, rather than in businesses which are guided by the often short-term interests of the stock market.

It is in this sense that Miele has embodied first-class product quality and German engineering since 1899. Miele also stands in equal measure for respect, fairness and mutual esteem towards sales partners, customers, suppliers, employees and neighbours. Buying a Miele is an environmentally friendly decision. We ensure this by using methods of production that save resources as well by producing products which set new standards in terms of their consumption of electricity, water and detergent – and save you money at the same time.\*

As directors and co-proprietors of the fourth generation of our business we promise you that this will not change.



Dr. Markus Miele



Dr. Reinhard Zinkann

\* Please visit [www.miele-sustainability.com](http://www.miele-sustainability.com) for more information on our efforts and guiding principles.



# "IMMER BESSER" (FOREVER BETTER)

Our brand promise



## **There are many good reasons for choosing Miele.**

Here are just six of them.

Since the company was founded in 1899, Miele has remained true to its "immer besser" (forever better) brand promise. This means that we will do all that we can to be "immer besser" (forever better) than our competitors and "immer besser" (forever better) than we already are.



## **Miele quality**

For more than 100 years it has been a proven adage that you can trust Miele and rely on our appliances. We are the only manufacturer in our branch of industry to test products such as our washing machines, tumble dryers, dishwashers and ovens to the equivalent of 20 years' use. Once a Miele, always a Miele: Miele customers around the world remain loyal to Miele and recommend Miele to others. Looking to the future, we promise not to entertain any compromises when it comes to the dependability and durability of our appliances.





### Miele technology

Miele stands for top-class results combined with minimum energy consumption. This goes for the hygienic and gentle care of your laundry, your flooring and your fine china as well as when conjuring up exquisite culinary delights. The key to this is a wealth of innovative features available only from Miele. This is born out by numerous first places in leading product tests conducted around the world.



### Miele convenience

Whether using a conventional rotary switch, discreet sensor controls or a high-resolution touch display like the one on your smartphone: operating a Miele appliance is both easy and fun. Add to this a multitude of convenient and reliable automatic programs and a great love of detail - success is guaranteed - on board both laundry and kitchen appliances. Make life easier for yourself with Miele!



### Miele design

Miele believes in clean lines and timeless elegance. Nowhere else will you find such a comparable range of built-in kitchen appliances, with consistency in design lines and color options, to suit the most diverse of interior designs and kitchen furniture fronts. Great care is taken to coordinate appliance design across the range. Whatever the style of your kitchen: Miele is the perfect match.



### Miele service

Miele customers enjoy preferential treatment: Thanks to our fast and efficient after-sales service operation which has been voted best in its branch of industry many times over. Even if you need personalized instructions on appliance use or professional cleaning of your appliances, Miele will gladly make a home visit. We will always be there for you. That's a promise!



### Miele brand

In many countries Miele is the most coveted brand in its branch of industry. On its own home market in Germany, Miele was even voted 'best brand ever', across all product branches. And the ownership of products from such a brand reveals much about its users: Miele customers have high expectations for the performance and the environmental friendliness of their domestic appliances. People who buy Miele are quality conscious and have style.





Highest levels of product quality, perfect and outstanding results – and extremely efficient at the same time. The highest demands on production and the materials used underline Miele's brand promise: "immer besser" (forever better).



#### **Tested for the equivalent of 20 years' use**

Miele carries out intensive endurance tests during the development phase in order to meet the highest quality standards. In these tests the appliances (e.g. washing machines) are expected to wash for 10,000 hours. This involves running a mix of approximately 5,000 wash programs. This corresponds to approx. 5 programs per week with an average cycle time of two hours – over 20 years.



# Quality – made by Miele



## Enamelled front

Miele enamels the front panels of all washing machines and tumble dryers. The high-quality enamel is scratch-proof, corrosion-proof, alkaline-resistant, impervious to acids, easy to clean and color-fast.



## Stainless-steel suds container

The suds container is particularly robust and hygienic. It is supported by shock absorbers and four suspension springs, and is weighed down with cast-iron counterweights. This is Miele perfection for minimum wear and tear, excellent sound-proofing qualities and durability.



## Bearing cross and counterweights made of cast iron

High-quality materials and manufacturing ensure less wear and tear and excellent stability in all Miele washing machines and tumble dryers.



## Maintenance-free heat exchanger

In Miele heat-pump dryers, the heat exchanger is protected by an effective filtration system and does not require cleaning. This ensures constant low energy consumption – a whole appliance life long.

# Domestic appliance networking with Miele@home\*

Freedom at home



## WiFiConn@ct

The networking of individual Miele domestic appliances is directly via the home's wireless router.



## Remote Vision

Revolutionizing the concept of wireless appliance support, Miele's RemoteVision technology monitors appliances 24 hours a day, 7 days a week - reporting any user faults or potential service problems.

Whether you are at home or out and about – you want to be able to rely on your domestic appliances. Networking of your appliances opens up more options that give your dynamic life more convenience, quality and safety. When approaching the subject of networking domestic appliances, we place the usefulness for the user at the center of attention. With in-house developed functionalities, mobile controls and new network technologies we offer a system that gives you more freedom and supports you in living every day as you want to – effectively and sustainably: Miele@home.




# Miele@mobile app\*\*

Everything under control – when out and about or at home



The Miele@mobile app offers a wide range of functions that enable you to monitor and operate your appliances to achieve the best possible results.



## MobileControl

With MobileControl you can for example select a program on your washing machine, tumble dryer and dishwasher even when you are not at home.



## ShopConn@ct

With ShopConn@ct you can conveniently buy the essential supplies such as dishwasher tablets and detergent cartridges for your domestic appliances via the Internet.



## Assistants

The interactive Assistants recommend the most suitable wash, drying and rinse program. This will ensure perfect results every time.

To enable wireless capabilities\*, simply download the **Miele@mobile App** (via Google Play or the App Store). And be on the look-out for a **Summer 2018** enhanced update – including additional features and functions.

\* Depends on model

\*\* Available for a mobile device (min. requirement Android 4.4+ and iOS 9+)





Discover the new dimension for perfect cleanliness!













# Miele TwinDos

## The best liquid detergent system

### Automatic dispensing

#### **TwinDos<sup>1)</sup>**

Fabric type, quantity of laundry and degree of soiling – all this must be taken into consideration when dispensing the correct amount of detergent. This sounds pretty complicated. That is why Miele is taking this off your hands.

With the TwinDos function two detergent containers can be integrated into the washing machine, and the appliance dispenses the optimum quantity of detergent for the laundry to be washed at the touch of a button.

For best results use UltraPhase 1 and 2, Miele's unique 2-Phase detergent system. TwinDos dispenses both components at the correct point in time during the wash cycle. This ensures the thorough cleaning of your laundry, and radiant colored and white textiles.

And should you wish to use a different detergent such as powder? No problem! Simply dispense the powder via the detergent dispenser drawer.

#### **30% detergent savings<sup>2)</sup>**

By the way, such accurate dispensing is difficult to accomplish manually. This is also certified by the ecological institute Öko-Institute e.V. in Freiburg, Germany, which confirms a 30% detergent saving potential thanks to the automatic dispensing feature from Miele.

<sup>1)</sup> Patent: EP 2 784 205

<sup>2)</sup> According to Öko-Institut e. V. report dd. 06.09.2013: 'Potential savings with automatic TwinDos dispensing on washing machines'



# Miele UltraPhase 1 and 2

The best liquid dispensing system

<b>HOHENSTEIN</b> INSTITUTE	Competence in Textiles · Worldwide
	The endorsed properties for the automatic 2-phase dosing system using Miele UltraPhase 1 and UltraPhase 2 detergents were compared with branded liquid detergents at different temperatures.
<b>Tested QUALITY</b>	At 40°C the stain removal was tested against a colour care detergent, and at 60°C the stain removal, degree of whiteness and anti-greying properties were tested against a heavy-duty detergent.
	The dosing accuracy was confirmed regardless of the washing temperature.
<a href="http://www.hohenstein.com">www.hohenstein.com</a>	

TEST NO: HL 13.2.10991

**AUTOMATIC 2-PHASE DOSING SYSTEM**

- › Stain removal
- › Degree of whiteness
- › Anti-greying
- › Dosing accuracy

## Best liquid detergent system on the market!


The German Hohenstein test institute tested the automatic 2-Phase dispensing system in connection with Miele's UltraPhase 1 and UltraPhase 2 detergents. They confirmed excellent wash results in terms of stain removal, the degree of whiteness, the anti-greying effect and accuracy of dispensing.







No other liquid detergent washes whites as well as colors as thoroughly as the 2-Phase-System from Miele. That is because conventional liquid detergents do not contain any bleach as it would damage the other ingredients. But bleach is necessary to remove stubborn stains (coffee, tea, fruit juice, red wine).



UltraPhase 1 and 2 are stored and dispensed separately which makes it possible to add bleach to the TwinDos system. Active ingredients in UltraPhase 1 break up the soil and remove stains such as oil, grease, protein and starch stains.



With UltraPhase 2, bleach is added at the appropriate time during the wash process and removes even stubborn stains such as coffee, tea, fruit juice or red wine.



# Which convenience features would you like?

Overview of the product highlights\* of Miele washing machines





### **TwinDos<sup>1)</sup>**

Automatic dispensing system

For best results use UltraPhase 1 and 2, Miele's unique 2-Phase detergent system. TwinDos dispenses both components at the correct point in time during the wash cycle.

This ensures the thorough cleaning of your laundry, and radiant colors and white textiles. With this, Miele offers the best liquid detergent system on the market.



### **IntenseWash**

IntenseWash offers the highest level of cleaning performance. Small loads, too, are washed economically. This is possible thanks to the Spin&Spray technology which works with a very low water level and saves heating energy.



### **QuickIntenseWash**

Excellent cleanliness in less than 1 hour – barely believable. With QuickIntenseWash, Miele realizes a high-level cleaning performance in a surprisingly short time.



\*depending on model

<sup>1)</sup> Patent: EP 2 784 205





### SingleWash

You want to wash your favorite blouse quickly for tonight? Washing individual pieces is not ecologically acceptable - who does not know about this dilemma? The Miele solution is SingleWash. You can select this option for a lot of programs. The device optimally adjusts program runtime, water and electricity consumption to loads of up to 2.2 lbs. Washing single pieces has never been faster and more economical.



### CapDosing<sup>1)</sup>

Miele's portioned capsules are a convenient solution for processing laundry requiring special applications. They are simply placed into the fabric conditioner compartment. The appliance dispenses the contents automatically at the perfect point in time during the wash process. Your choice: 6 special detergents (Sport, Down, Outerwear, WoolCare, SilkCare, UltraDark), 3 fabric conditioners (Aqua, Nature, Cocoon), as well as Impraprotect and the Booster which deals with persistent soiling.



### Honeycomb drum

The web-like surface structure of the Miele honeycomb drum creates a thin film of water between the drum and the laundry. This results in laundry gliding gently and protects the fibers perfectly. The smaller, smoothly polished holes in the walls of the drum are also gentle on your textiles and prevent pilling. Foreign objects such as paper clips no longer end up in the drain pump.



### WiFiConn@ct<sup>2)</sup>

With WiFiConn@ct you can conveniently connect your Miele appliance to the internet via a wireless router. Use your smartphone or tablet to take advantage of many benefits: call up an appliance status whilst at home or when out and about, read notifications such as the requirement to replenish the detergent. To do this you need the Miele@mobile app which you can download for free via Google Play or the App Store.



### Energy Star Rated

Miele washing machines are ecological and consume only the amount of water and electricity needed. ENERGY STAR® is the government-backed symbol for energy efficiency, providing simple, credible and unbiased information that consumers and businesses rely on to make well-informed decisions. Miele prides itself on being an ENERGY STAR partner.



### AutoClean<sup>3)</sup>

The AutoClean detergent dispenser is rinsed with a series of powerful jets of water after every wash program. This removes any detergent residue thoroughly. The particularly smooth surface assists the rinsing process.



\* depends on model

<sup>1)</sup> Patent: EP 2 365 120

<sup>2)</sup> App available for a mobile device (min. requirement Android 4.2+ and iOS 9+)

<sup>3)</sup> Patent: EP 2 840 679 4



# Washing machines



Model/Sales designation	WWF060 WCS WiFiConn@ct	WWH660 WCS TDos&WiFiConn@ct	WWH860 WCS TDos&IntenseWash WiFi
Load in lbs/capacity in cu ft	17.6 lb/2.26 cu ft	17.6 lb/2.26 cu ft	17.6 lb/2.26 cu ft
Max. spin speed	1.600	1.600	1.600
<b>Construction type</b>			
Can be slotted-under/stacked	●/●	●/●	●/●
Door hinge	left	left	left
<b>Design</b>			
Rotary selector color	Lotus white cap/chrome ring	Lotus white cap/chrome ring	Lotus white cap/chrome ring
Fascia panel angle	5°incline	5°incline	5°incline
Door design	Silver with white ring	Chrome with white ring	Chrome with white ring
Control panel	ComfortSensor white, 1 line	ComfortSensor white, 1 line	ComfortSensor white, 1 line
<b>Cleaning performance</b>			
TwinDos	–	●	●
IntenseWash	–	–	●
CapDosing	●	●	●
<b>Gentle laundry care</b>			
Honeycomb drum	●	●	●
<b>User convenience</b>			
SoftSteam	●	●	●
Delay start up to 24 h/Countdown indicator	●/●	●/●	●/●
Drum lighting	LED	LED	LED
AutoClean detergent drawer	●	●	●
<b>Efficiency and sustainability</b>			
Energy Star	●	●	●
Annual water consumption in l/Annual energy consumption in kWh*	2294/84	2294/84	2294/84
Hot water connection	●	●	●
EcoFeedback function/ProfiEco Motor	●/●	●/●	●/●
Automatic load recognition/Flow meter/Foam control	●/●/●	●/●/●	●/●/●
<b>Main wash programs</b>			
Normal/Wrinkle-free/Delicates	●/●/●	●/●/●	●/●/●
QuickIntenseWash/Express	–/●	–/●	●/●
Dress Shirts/Silks/Handwash	●/●/●	●/●/●	●/●/●
Darks and Demins/Extra White/Sanitize	●/●/●	●/●/●	●/●/●
Outdoor/Proofing	●/●	●/●	●/●
Baby clothes/Downs/Towels/Pillows	–/–/–/–	●/●/●/●	●/●/●/●
<b>Main wash options</b>			
SingleWash	–	–	●
Soak/Pre-Wash	●/●	●/●	●/●
<b>Appliance networking</b>			
Miele@home/WiFiConn@ct	●/●	●/●	●/●
MobileControl/RemoteVision	●/●	●/●	●/●
<b>Quality</b>			
Suds container	stainless steel	stainless steel	stainless steel
Enamelled front/Counterweights made of cast iron	●/●	●/●	●/●
<b>Safety</b>			
Watercontrol-System	●	●	●
Safety lock/PIN code	●/●	●/●	●/●
<b>Technical data</b>			
Appliance dimensions in mm (W x H x D)	596 x 850 x 643	596 x 850 x 643	596 x 850 x 643
Appliance dimensions in inch (W x H x D)	23 1/2" x 33 1/2" x 23 5/8"	23 1/2" x 33 1/2" x 23 5/8"	23 1/2" x 33 1/2" x 23 5/8"
<b>Included accessories</b>			
3 Caps/UltraPhase 1+2	●/–	●/●	●/●
<b>Optional accessories</b>			
Stacking kit	WTV502/512, WTS510	WTV502/512, WTS510	WTV502/512, WTS510
<b>Item Number</b>			
White	11WF0605USA	11WH6605USA	11WH8605USA
<b>UMRP&amp;MAP/Retail pricing</b>	<b>\$1,499/\$1,699</b>	<b>\$1,799/\$1,999</b>	<b>\$1,999/\$2,199</b>









Bouncy, fragrant and virtually free of creases — that is how we dry nowadays!











# Heat-pump technology

## Economical and gentle

Contrary to conventional condenser dryers, the heat, once generated, is used again. Miele Tumble dryers\* with heat pumps are known predominantly for their energy efficiency and highest demands on quality and durability. They dry your laundry especially economically. But the lower temperatures of the heat-pump technology also protect the high-quality fibers of your laundry. This allows you to dry delicate textiles with convenience.



### **Maintenance-free heat exchanger**

In Miele heat-pump dryers, the heat exchanger is protected by an effective filtration system and does not require cleaning. This ensures a high energy efficiency for the complete service life of the appliance.







# FragranceDos\*

Scented laundry just the way you like it

## Discover a new kind of freshness

With your Miele tumble dryer you can now enjoy the superb convenience of a long-lasting and well-balanced fragrance. The new Miele fragrances add your personal favorite scent to your laundry during the drying process. This results in particularly fluffy and beautifully fragrant laundry. The fragrance flaçon is simply fitted into a holder on the easily accessible fluff filter and distributes an unobtrusive fragrance evenly onto your laundry. The intensity of the fragrance can be adjusted by turning the flaçon. For the ultimate freshness experience in every drying cycle!

Choose your very own personal favorite from 3 fragrances: Aqua, Cocoon and Nature





# Which convenience features would you like?

Overview of the product highlights\* of Miele tumble dryers







### Heat-pump technology

Above all, heat-pump tumble dryers are known for high energy efficiency. Laundry dries particularly economically. The lower temperatures of the heat-pump technology are very gentle on valuable fibers of your textiles. This allows you to conveniently dry even delicate items.

### FragranceDos<sup>1)</sup>

With Miele fragrance pods – in 3 scent variants – your laundry is enwrapped with your own personal favorite scent. A family-run company in the south of France, which has been creating perfumes since 1871, produces fragrances for Miele. Using a patented process their perfume specialists ensure that the essential oils in the perfume are preserved. The result: pleasantly fresh and naturally fragranced laundry for up to four weeks.



### Energy Star Most Efficient

T1 tumble dryers have been designated as the Most Efficient ENERGY STAR certified products in 2018. Products that are recognized as the Most Efficient of ENERGY STAR in 2018 prevent greenhouse gas emissions by meeting rigorous energy efficiency performance levels set by the U.S. Environmental Protection Agency.



\* depends on model

<sup>1)</sup> ) Patent pending: EP 2 431 516






### SteamFinish

If ironing is not your favorite task, then you will appreciate Miele's SteamFinish with the Steam Smoothing program. At the beginning of the drying process, water is sprayed into the honeycomb drum creating a fine mist which is heated by the drying air. The developing steam penetrates the textiles and visibly smoothes the laundry. This ensures that ironing is much easier and faster.



### PerfectDry

Thanks to this system, your laundry dries perfectly – even if the water contains significant amounts of calcium. This is by no means the norm on machines without Perfect Dry as the calcium content in the water influences residual moisture sensing – and in turn has an impact on drying results. Perfect Dry takes the current calcium content of water into account and precisely adjusts the drying process accordingly. This ensures that the selected drying stage is always achieved.



### Honeycomb drum<sup>1)</sup>

The unique honeycomb structure lifts the laundry higher in the rotating drum. Items are exposed to the warm air stream for longer, which achieves more uniform drying results. Air pockets form in the depressions of the individual hexagons and cushion the fall of laundry. This ensures that your textiles are treated much more gently and have less creases after drying. This simplifies ironing considerably.



### Door hinged on the right or left

On all Miele washing machines and tumble dryers, the door hinges can be relocated to suit your individual requirements perfectly. If you have a washer-dryer stack, for example, both doors open in the same direction.



### WiFiConn@ct<sup>2)</sup>

With WiFiConn@ct you can conveniently connect your Miele appliance to the internet via a wireless router. Use your smartphone or tablet to take advantage of many benefits: call up an appliance status whilst at home or when out and about and read notifications. To do this you need the Miele@mobile app which you can download for free via Google Play or the App Store.



### Intelligent drum reversal

A Miele tumble dryer changes the rotation of the drum in irregular intervals. This prevents laundry from rolling into a tangled knot, ensures uniform drying results and reduces creasing.



<sup>1)</sup> Patent: EP 1 293 594

<sup>2)</sup> App available for a mobile device (min. requirement Android 4.2+ and iOS 9+)



# Heat-pump dryer

## Product Overview



Model/Sales designation	TWF160 WP Eco&WiFiConn@ct	TWI180 WP Eco&Steam WiFiConn@ct
Load in lbs/capacity in cu ft	17.6 lbs/4.026 cu ft	17.6 lbs/4.026 cu ft
<b>Construction type</b>		
Heat-pump dryer	●	●
Can be slotted-under/stacked	●/●	●/●
Door hinge/convertible	right/●	right/●
<b>Design</b>		
Rotary selector color	Lotus white cap/chrome ring	Lotus white cap/chrome ring
Fascia panel angle	5°incline	5°incline
Door design	White	Chrome with white ring
Control panel	ComfortSensor white, 1 line	ComfortSensor white, 1 line
<b>Drying results</b>		
PerfectDry/FragranceDos	●/●	●/●
SteamFinish	—	●
Intelligent drum reversal	●	●
<b>Gentle laundry care</b>		
Honeycomb drum	●	●
<b>User convenience</b>		
Integrated condensed water drainage	●	●
Delay start up to 24 h/Countdown indicator	●/●	●/●
Drum lighting	LED	LED
<b>Efficiency and sustainability</b>		
Energy Star	●	●
Annual energy consumption in kWh	130 kWh	130 kWh
EcoFeedback function/ProfiEco Motor	●/●	●/●
Maintenance-free heat exchanger	●	●
<b>Main drying programs</b>		
Normal/Wrinkle-free/Delicates	●/●/●	●/●/●
Dress Shirts/Woolens/Silks	●/●/●	●/●/●
SoftSteam	—	●
Express	●	●
Outdoor/Proofing/Pillows	●/●/—	●/●/●
<b>Main drying options</b>		
Freshen-up	●	●
Anti-Crease/Gentle/Buzzer	●/●/●	●/●/●
<b>Appliance networking</b>		
Miele@home/WiFiConn@ct	●/●	●/●
MobileControl/RemoteVision	●/●	●/●
<b>Quality</b>		
Soft ribs/Enamelled front	●/●	●/●
<b>Safety</b>		
PIN code	●	●
"Empty out container" indicator/"Clean filter" indicator	●/●	●/●
<b>Technical data</b>		
Appliance dimensions in mm (W x H x D)	596 x 850 x 643	596 x 850 x 643
Appliance dimensions in inch (W x H x D)	23 1/2" x 33 1/2" x 25 5/16"	23 1/2" x 33 1/2" x 25 5/16"
<b>Included accessories</b>		
Fragrance capsules	●	●
<b>Optional accessories</b>		
Stacking kit	WTV502/512, WTS510	WTV502/512, WTS510
<b>Item Number</b>		
White	12WF1602USA	12WI1802USA
<b>UMRP&amp;MAP/Retail pricing</b>	<b>\$1,499/\$1,699</b>	<b>\$1,799/\$1,999</b>





**Miele** T0

Eco & Steam  
WiFiControl

Normal 1:21  
Gentle Freshen-up  
Anti-crease Buzzer Start/Stop

Normal  
Wrinkle-free  
Delicates  
Smoothing  
Woolens/Silk  
Dress Shirts  
MobileControl  
Soft Steam  
Express  
Denims  
Outdoor  
More Programs







# This is only available from Miele

## Perfect systematic laundry care



Our laundry-care system covers the entire process, from washing and drying to ironing. Even the special cleaning products from Miele were developed in our own laboratories and have been perfectly formulated to match Miele appliances.

### The ideal combination

Miele washing machines and tumble dryers match each other perfectly. As a result, you can find a matching tumble dryer for every washing machine with respect to design and features. This enables us to offer you best cleaning and care performance combined with gentle laundry care.



### Perfect laundry finish

Many textiles only get a perfect finish when they are ironed and given additional protection through mechanical and thermal treatment. You can iron particularly easily, conveniently, quickly and effectively using the Miele FashionMaster steam ironing system and Miele rotary ironers.



### Results are simply perfect

Not all off-the-shelf products deliver the same results on all washing machines. For this reason, we have developed Miele detergents in our own laboratories in collaboration with selected suppliers. The formulas are perfectly adapted to Miele washing machines and tumble dryers. This allows you to tap the potential of your Miele machines to the full and reduce the burden on the environment at the same time.



# A new era in laundry care

## Miele FashionMaster steam ironing system

### Miele's FashionMaster – ironing partner offering many convenient features

With the perfect combination of hand iron, steam generator and ironing board the often unloved task of ironing turns into an uplifting and enjoyable activity.

The secret behind the FashionMaster is sophisticated technology. The motto during the development: perfect results with minimum effort. You will experience this right from the outset with the patented 1-2-Lift-System<sup>1)</sup>. It assists to set the FashionMaster up with very little effort on your part. Then there is the extremely precise and efficient steam technology which ensures perfectly smoothed garments with ease. The hand iron with a special honeycomb soleplate guarantees excellent steam distribution which results in best smoothing results.

With the powerful Steamer you can apply the benefits of steam generation directly to hanging textiles. A display keeps you informed of the state of the appliance, e.g. when the water tank needs replenishing. The FashionMaster also stands out with its functional and attractive design. Even when folded it is almost too good-looking to be hidden away. It is not surprising that this Miele innovation received awards from several acclaimed design juries.



reddot design award  
winner 2012



product  
design award  
2012

### Goodbye ironing stress. Hello FashionMaster!

Is ironing not one of your favorite pastimes? We can relate to that. It was for this reason we developed an ironing system to make ironing your textiles simpler, faster and more uniformly than ever before.

Ironing with the Miele FashionMaster makes this often unloved task seem far less daunting. Even preparation requires less time and effort: equipped with an ironing table, an iron and a steam generator, the FashionMaster has everything on board. On two floor-friendly rollers, it is as effortless to pull and move around in the home. It even takes the odd step or two in its stride. The innovative technology of the FashionMaster helps you to deal with a mountain of laundry quickly and easily. From a delicate silk blouse to a robust linen jacket, from intricate sequined embroidery to printed clothes, the FashionMaster gets rid of creases in record time. Easy ironing without having to make any compromises.









# Accessories for laundry-care appliances



## Washer and dryer stack

If there is not sufficient space available to install two appliances next to one another, most Miele washing machines and tumble dryers can be conveniently combined as a washer-dryer stack. In this arrangement, the washing machine is always installed under the tumble dryer.


Miele offers various stacking kits for a stable connection between the two appliances. Some, e.g. the WTV 512 model, feature a practical drawer. This drawer is ideal for storing accessories for example or for conveniently resting the laundry basket on whilst loading and unloading the tumble dryer.



## Pedestal with drawer

For ergonomic purposes, washing machines and tumble dryers can be installed on pedestals specifically designed for them – e.g. WTS 510. A pedestal height of 11 7/8 - 13 7/8 in allows you to load and unload your textiles without having to stoop. For a secure installation the appliances are fixed onto the pedestal. The integrated drawer with Push/Pull opening mechanism offers additional storage space for detergents, fragrance pods, and more. Thanks to an anti-slip mat these items cannot slide around when opening or closing the drawer.





#### Washer-dryer stacking kit WTV 512

For the safe installation of a washer-dryer stack with drawer and worktop

- Plenty of storage space thanks to integrated drawer with push/pull function
- WTV height: 4 1/2 in
- For combining a W1 with a T1
- Color: Lotus white
- Item Number: 9351790



#### Washer-dryer stacking kit WTV 502

For a space-saving and safe installation of a washer-dryer stack


- Space-saving WTV stacking height of 1/10 in
- For combining a W1 with a T1
- Color: Lotus white
- Item Number: 9256140



#### Pedestal with drawer WTS 510

With drawer for additional storage space for detergents, fragrance flacons, tumble dryer basket, etc.

- Convenient loading and unloading thanks to 13 7/8 in plinth
- Non-slip liner to prevent contents from sliding around
- For all W1 washing machines and T1 tumble dryers
- Color: Lotus white
- Item Number: 12996075D



#### Tumble dryer basket TRK 555

Ideal for sneakers, children's boots, small woollen textiles or cuddly toys

- Best care for delicate textiles
- Specifically developed for Miele tumble dryers
- Suitable for all T1 tumble dryers
- Item Number: 9614800



#### NEMA Adapter 120V/240V

Adapter for standard NEMA 14-30 outlets  
Converts NEMA 14-30 outlet into two NEMA 5-15 outlets

- Plug washer and dryer into adapter
- Item Number: 10896040



# Caps

The perfect addition for special applications



## 10-pack Caps Collection

The perfect addition for special applications. Introductory pack

- Detergent Caps: Sport, DownCare, Outdoor, WoolCare, SilkCare and UltraDark
- Care Caps: fabric conditioner and proofing agent
- Additive Cap: booster for persistent soiling
- No overdosing thanks to exact portions. For 10 wash loads
- Simply perfect laundry care with Miele.
- Item Number: 10216850



## 9-pack Caps WoolCare

For woollens and delicates.

- Special care based on wheat protein – with color-protection
- Fiber-protection components for protection against felting
- Best wash results at 68/86/104/140°F
- No overdosing thanks to exact portions. For 9 wash loads
- Simply perfect laundry care with Miele.
- Item Number: 10755570



## 9-pack Caps Fabric conditioner

Ideal for towels

- For soft, bouncy laundry
- Fresh, natural fragrance
- No overdosing thanks to exact portions. For 9 wash loads
- Simply perfect laundry care with Miele.

Aqua - pure and thorough cleanliness with a fresh scent

- Item Number: 10813390

Cocoon - for a feeling of peace and harmony

- Item Number: 10813410

Nature - floral aroma and natural, well-balanced fragrance

- Item Number: 10813430



## 6-pack Caps Sport

For sportswear

- Unpleasant smells are neutralized thanks to the odor absorber
- Cleans breathable sportswear with care and is gentle on colors
- Retains the shape of the textiles – also suitable for fleece garments
- No overdosing thanks to exact portions. For 6 wash loads
- Simply perfect laundry care with Miele.
- Item Number: 10756450





### 6-pack Caps Booster

For sportswear

- Unpleasant smells are neutralized thanks to the odor absorber
- Cleans breathable sportswear with care and is gentle on colors
- Retains the shape of the textiles – also suitable for fleece garments
- No overdosing thanks to exact portions. For 6 wash loads
- Simply perfect laundry care with Miele.
- Item Number: 10755980

### 6-pack Caps SilkCare (not illustrated)

Well-suited for silks

- Special fabric care using silk proteins
- Best wash results at 68/86/104/140°F
- No overdosing thanks to exact portions. For 6 wash loads
- Simply perfect laundry care with Miele.
- Item Number: 10756190

### 6-pack Caps DownCare (not illustrated)

Ideal for pillows, sleeping bags or high-quality down-filled items

- Retains elasticity of down
- Also retains breathability of down-filled items
- Feathers do not stick together and remain fluffy
- No overdosing thanks to exact portions. For 6 wash loads
- Simply perfect laundry care with Miele.
- Item Number: 10756370



### 6-pack Caps Outdoor

Perfect for high-quality outdoor and performance clothing

- Very gentle on membranes due to special surfactant combination
- High foaming power – cleans textiles gently on a foam carpet
- Neutralizes smells thanks to odor absorber
- No overdosing thanks to exact portions. For 6 wash loads
- Simply perfect laundry care with Miele.
- Item Number: 10757030

### 3-pack Caps ImpraProtect (not illustrated)

Ideal for sportswear and rainwear

- Effective proofing to protect against water and wind, and to give a dirt-repellent finish
- Retains the breathability of garments
- No overdosing thanks to exact portions. For 3 wash loads
- Simply perfect laundry care with Miele..
- Item Number: 10757720



# UltraPhase 1 and UltraPhase 2

For washing machines and washer-dryers with TwinDos



## UltraPhase 1 and 2 cartridge 1.5 l

2-component detergent for both white textiles and colors

- For brilliant colors and spotlessly white laundry
- Excellent stain removal even at low temperatures
- Dispensing more than required is prevented thanks to automatic dispensing
- Highly effective – for 37 (UltraPhase 1) or 50 (UltraPhase 2) wash loads
- Simply perfect laundry care with Miele.

UltraPhase 1

- Item Number: 1080367


UltraPhase 2

- Item Number: 10803750



### UltraPhase 1 and 2:

Best liquid detergent system on the market. With TwinDos automatic dispensing at the touch of a button for perfect wash results.

 <b>Tested QUALITY</b>	Competence in Textiles · Worldwide
	<p>The endorsed properties for the automatic 2-phase dosing system using Miele UltraPhase 1 and UltraPhase 2 detergents were compared with branded liquid detergents at different temperatures.</p> <p>At 40°C the stain removal was tested against a colour care detergent, and at 60°C the stain removal, degree of whiteness and anti-greying properties were tested against a heavy-duty detergent.</p> <p>The dosing accuracy was confirmed regardless of the washing temperature.</p>
<p>TEST NO: HL 13.2.10991</p> <p><b>AUTOMATIC 2-PHASE DOSING SYSTEM</b></p> <ul style="list-style-type: none"><li>› Stain removal</li><li>› Degree of whiteness</li><li>› Anti-greying</li><li>› Dosing accuracy</li></ul>	<p>www.hohenstein.com</p>

### Tried and tested quality

The German Hohenstein test institute tested the automatic 2-Phase dispensing system in connection with Miele's UltraPhase 1 and UltraPhase 2 detergents. They confirmed excellent wash results in terms of stain removal, the degree of whiteness, the anti-greying effect and accuracy of dispensing.



# Miele fragrance flacons for Miele tumble dryers

For a fresh and long-lasting fragrance – fully automatically



## Feel-good freshness after tumble drying

With your Miele tumble dryer you can now enjoy the superb convenience of a long-lasting and well-balanced fragrance. Miele's fragrances add your personal favorite scent to your laundry during the drying process.

As a result, you get not only especially bouncy laundry, but also laundry that smells great – for up to four weeks.

Choose your very own personal favorite.

## Fragrance Flacon

12.5 ml

For 50 drying cycles

- For fresh, fragrant laundry that lasts for up to four weeks
- For bouncy as well as beautifully fragrant laundry
- Developed 'en Provence' by perfume specialists specifically for Miele

AQUA – pure and thorough cleanliness with a fresh scent

Item Number: 09428840

COCOON – for a feeling of peace and harmony

Item Number: 09428780

NATURE – floral aroma and natural, well-balanced fragrance

Item Number: 09428890



## Fragrance to suit your individual taste – lasting for weeks

### and completely automatically<sup>1)</sup>

The fragrance pod is simply fitted into a holder on the easily accessible fluff filter and distributes an unobtrusive fragrance evenly onto your laundry. The intensity of the fragrance can be adjusted by turning the pod.

For the ultimate freshness experience in every drying cycle!

<sup>1)</sup> One fragrance pod for approx. 50 drying cycles



# Miele

## **U.S.A**

### **Miele, Inc.**

9 Independence Way  
Princeton, New Jersey 08540  
Phone: 800.843.7231  
Fax: 609.419.4290  
[www.mieleusa.com](http://www.mieleusa.com)



[www.mielestore.com](http://www.mielestore.com)