

# Price List

Floor Care







# Welcome to Miele

## IMMER BESSER (forever better) — our pledge

When our two great grandfathers were in the process of founding the Miele company, they had to make sure they stood apart from the competition in order to be successful. There are effectively only two ways of doing this: either by being cheaper than the rest or by being better than the rest. It is not really possible to be both at the same time.

They decided to be "better" than the rest.

Numerous best in class awards and certificates attest to the fact that Miele has continued to renew its commitment to being "immer besser" throughout the past 121 years. However, the millions of satisfied customers around the world are perhaps the most important endorsement.

At the heart of this success lies a continuity of values and goals which are typically only found in companies which have been family-run for generations, rather than in businesses which are guided by the often short-term interests of the stock market.

It is in this sense that Miele has embodied first-class product quality and German engineering since 1899. Miele also stands in equal measure for respect, fairness and mutual esteem towards sales partners, customers, suppliers, employees and neighbors. Buying a Miele is an environmentally friendly decision. We ensure this by using methods of production that save resources as well as by producing products which set new standards in terms of their consumption of electricity, water and detergent — and save you money at the same time.\*

As directors and co-proprietors of the fourth generation of our business we promise you that this will not change.

Dr. Markus Miele

Dr. Reinhard Zinkann

\* Please visit [www.miele-sustainability.com](http://www.miele-sustainability.com) for more information on our efforts and guiding principles.

# Complete Series

## Product Overview



	Complete C3 Brilliant	Complete C3 Marin	Complete C3 Kona
<b>Exterior</b>			
Color	Bronze Pearl	Marine Blue	Obsidian Black
Chrome Trim	•	•	•
<b>Power</b>			
Powerful Miele-Made Vortex Motor™	• (Silence)	• (Silence)	• (Silence)
Max. Power	1200W	1200W	1200W
Sound Insulation	•	•	•
On/Off Control	Foot Switch	Foot Switch	Foot Switch
Power Setting Control	+/- Handle Controls	+/- Foot Switch	+/- Foot Switch
Illuminated Controls Display	•	•	•
Automatic Power Setting	•	•	–
Number of Power Settings	6	6	6
Soft Carpet Setting	–	–	–
Safety Shut-off / Overheat Protection	•	•	•
<b>Floorheads and Accessories</b>			
Pure Suction Combination Floorhead (SBD)	SBD 285-3	Optional	Optional
Turbo Brush Floorhead (STB)	Optional	Optional	Optional
Electro Brush Floorhead (SEB)	SEB 236	SEB 236	SEB 228
Electro Brush Socket	•	•	•
Pure Suction Parquet Floorhead (SBB)	SBB 400-3	SBB 300-3	SBB 300-3
Suction Hose	SES 131 (Electro)	SES 121 (Electro)	SES 121 (Electro)
Telescopic Wand	SET 220 (Electro)	SET 220 (Electro)	SET 220 (Electro)
<b>Integrated Accessories</b>			
Dusting Brush	•	•	•
Upholstery Tool	•	•	•
Crevice Nozzle	•	•	•
Accessory Storage	Integrated	Integrated	Integrated
Flexible Crevice Tool (SFD 20)	–	–	–
Universal Brush (SUB 20)	–	–	–
Mini Turbo Brush (STB 101)	–	–	–
<b>Bags &amp; Filtration</b>			
AirClean Sealed System®	•	•	•
AirClean 3D Efficiency FilterBag™	GN	GN	GN
FilterBag™ Change Indicator	•	•	•
AirClean Filter	Optional	Optional	Optional
Active AirClean Filter	Optional	Optional	Optional
HEPA AirClean Filter	HA 50	HA 50	HA 50
Filter Change Indicator	•	•	–
<b>User conveniences</b>			
Comfort Grip Handle	• (Deluxe)	•	•
Spotlight Handle	–	–	–
360° Swivel (Caster) Wheels	•	•	•
Operating Radius	36ft	36ft	36ft
Park-System	Double, Illuminated	Double	Double
Park Auto-off	•	•	•
Cable Rewind	Comfort One-Touch	Comfort One-Touch	Comfort One-Touch
Long Electrical Cord	23ft	23ft	23ft
Ergonomic Carrying Handle	•	•	•
Protective Bumper	• (Velvet)	•	•
<b>MAP</b>	<b>\$1,499.00</b>	<b>\$1,099.00</b>	<b>\$899.00</b>
<b>List Price</b>	<b>\$1,599.00</b>	<b>\$1,249.00</b>	<b>\$999.00</b>
<b>Material Number</b>	<b>9930720</b>	<b>10014700</b>	<b>10014580</b>



	<b>Complete C3 Calima</b>
<b>Exterior</b>	
Color	Curry Yellow
Chrome Trim	•
<b>Power</b>	
Powerful Miele-Made Vortex Motor™	• (Silence)
Max. Power	1200W
Sound Insulation	•
On/Off Control	Foot Switch
Power Setting Control	+/- Foot Switch
Illuminated Controls Display	•
Automatic Power Setting	-
Number of Power Settings	6
Soft Carpet Setting	-
Safety Shut-off / Overheat Protection	•
<b>Floorheads and Accessories</b>	
Pure Suction Combination Floorhead (SBD)	Optional
Turbo Brush Floorhead (STB)	STB 305-3
Electro Brush Floorhead (SEB)	Optional
Electro Brush Socket	•
Pure Suction Parquet Floorhead (SBB)	SBB 300-3
Suction Hose	• (Two-Colored, Conical)
Telescopic Wand	• (Comfort)
<b>Integrated Accessories</b>	
Dusting Brush	•
Upholstery Tool	•
Crevice Nozzle	•
Accessory Storage	Integrated
Flexible Crevice Tool (SFD 20)	-
Universal Brush (SUB 20)	-
Mini Turbo Brush (STB 101)	-
<b>Bags &amp; Filtration</b>	
AirClean Sealed System®	•
AirClean 3D Efficiency FilterBag™	GN
FilterBag™ Change Indicator	•
AirClean Filter	Optional
Active AirClean Filter	Optional
HEPA AirClean Filter	HA 50
Filter Change Indicator	-
<b>User conveniences</b>	
Comfort Grip Handle	•
Spotlight Handle	-
360° Swivel (Caster) Wheels	•
Operating Radius	36ft
Park-System	Double
Park Auto-off	•
Cable Rewind	Comfort One-Touch
Long Electrical Cord	23ft
Ergonomic Carrying Handle	•
Protective Bumper	•
<b>MAP</b>	
	<b>\$699.00</b>
<b>List Price</b>	
	<b>\$799.00</b>
<b>Material Number</b>	
	<b>10796510</b>

# Compact Series

## Product Overview



	Compact C1 Turbo Team	Compact C1 Pure Suction
<b>Exterior</b>		
Color	Obsidian Black	Lotus White
Color Trim	-	-
<b>Power</b>		
Powerful Miele-Made Vortex Motor™	•	•
Max. Power	1200W	1200W
Sound Insulation	-	-
On/Off Control	Foot Switch	Foot Switch
Power Setting Control	Rotary Dial	Rotary Dial
Illuminated Controls Display	-	-
Automatic Power Setting	-	-
Number of Power Settings	6	6
SoftCarpet Setting	-	-
Safety Shut-off / Overheat Protection	-	-
<b>Floorheads and Accessories</b>		
Pure Suction Combination Floorhead (SBD)	Optional	SBD 285-3
Turbo Brush Floorhead (STB)	STB 305-3	Optional
Electro Brush Floorhead (SEB)	-	-
Electro Brush Socket	-	-
Pure Suction Parquet Floorhead (SBB)	SBB Parquet-3	Optional
Suction Hose	•	•
Telescopic Wand	• (Compact Comfort)	• (Compact Comfort)
<b>Integrated Accessories</b>		
Dusting Brush	•	•
Upholstery Tool	•	•
Crevice Nozzle	•	•
Accessory Storage	VarioClip	VarioClip
<b>Bags &amp; Filtration</b>		
AirClean Sealed System®	•	•
AirClean 3D Efficiency FilterBag™	FJM	FJM
FilterBag™ Change Indicator	•	•
AirClean Filter	SAC 20/30	SAC 20/30
Active AirClean Filter	Optional	Optional
HEPA AirClean Filter	Optional	Optional
Filter Change Indicator	-	-
<b>User conveniences</b>		
Comfort Grip Handle	•	•
360° Swivel (Caster) Wheels	•	•
Operating Radius	29.5ft	29.5ft
Park-System	•	•
Park Auto-off	•	•
Cable Rewind	•	•
Long Electrical Cord	18ft	18ft
Ergonomic Carrying Handle	•	•
Protective Bumper	•	•
<b>MAP</b>	<b>\$499.00</b>	<b>\$399.00</b>
<b>List Price</b>	<b>\$599.00</b>	<b>\$499.00</b>
<b>Material Number</b>	<b>10850080</b>	<b>10636160</b>

# Classic Series

## Product Overview



	Classic C1 Turbo Team	Classic C1 Pure Suction
<b>Exterior</b>		
Color	Tech Blue	Graphite Grey
Color Trim	-	-
<b>Power</b>		
Powerful Miele-Made Vortex Motor™	•	•
Max. Power	1200W	1200W
Sound Insulation	-	-
On/Off Control	Foot Switch	Foot Switch
Power Setting Control	Rotary Dial	Rotary Dial
Illuminated Controls Display	-	-
Automatic Power Setting	-	-
Number of Power Settings	6	6
SoftCarpet Setting	-	-
Safety Shut-off / Overheat Protection	•	•
<b>Floorheads and Accessories</b>		
Pure Suction Combination Floorhead (SBD)	-	SBD 285-3
Turbo Brush Floorhead (STB)	STB 305-3	-
Electro Brush Floorhead (SEB)	-	-
Electro Brush Socket	-	-
Pure Suction Parquet Floorhead (SBB)	SBB Parquet-3	-
Suction Hose	•	•
Telescopic Wand	• (Compact Comfort)	• (Compact Comfort)
<b>Integrated Accessories</b>		
Dusting Brush	•	•
Upholstery Tool	•	•
Crevice Nozzle	•	•
Accessory Storage	VarioClip	VarioClip
Flexible Crevice Tool (SFD 20)	-	-
Universal Brush (SUB 20)	-	-
<b>Bags &amp; Filtration</b>		
AirClean Sealed System®	-	-
AirClean 3D Efficiency FilterBag™	GN	GN
Bagless System	-	-
FilterBag™ Change Indicator	•	•
AirClean Filter	SAC 20/30	SAC 20/30
Active AirClean Filter	Optional	Optional
HEPA AirClean Filter	Optional	Optional
Filter Change Indicator	•	-
<b>User conveniences</b>		
Comfort Grip Handle	•	•
Spotlight Handle	-	-
LED Headlight	-	-
360° Swivel (Caster) Wheels	•	•
Operating Radius	29.5ft	29.5ft
Park-System	•	•
Park Auto-off	-	-
Cable Rewind	•	•
Long Electrical Cord	18ft	18ft
Ergonomic Carrying Handle	•	•
Protective Bumper	•	•
<b>MAP</b>	<b>\$399.00</b>	<b>\$299.00</b>
<b>List Price</b>	<b>\$499.00</b>	<b>\$399.00</b>
<b>Material Number</b>	<b>11181010</b>	<b>11181020</b>

# Cat & Dog Series

## Product Overview



	Complete C3 Cat & Dog	Blizzard CX1 Cat & Dog	Classic C1 Cat & Dog
<b>Exterior</b>			
Color	Lotus White	Lotus White	Lotus White
Chrome Trim	•	–	–
<b>Power</b>			
Powerful Miele-Made Vortex Motor™	• (Silence)	•	•
Max. Power	1200W	1200W	1200W
Bagless Vortex Air Flow Technology	–	•	–
Sound Insulation	•	•	•
On/Off Control	Foot Switch	Foot Switch	Foot Switch
Power Setting (Suction) Control	+/- Foot Switch	Rotary Dial	Rotary Dial
Illuminated Controls Display	•	–	–
Automatic Power Setting	–	–	–
Number of Power Settings	6	4	6
Safety Shut-off / Overheat Protection	•	•	•
<b>Floorheads and Accessories</b>			
Electro Brush Floorhead (SEB)	SEB 228	SEB 228	SEB 228
Electro Brush Socket	•	•	•
Turbo Brush Floorhead (STB)	Optional	Optional	Optional
Pure Suction Combination Floorhead (SBD)	Optional	Optional	Optional
Pure Suction Parquet Floorhead (SBB)	SBB 300-3	SBB 300-3	SBB Parquet-3
Suction Hose	SES 121 (Electro) (Two-Colored)	SES 121 (Electro) (Two-Colored)	SES 116 (Electro)
Telescopic Wand	SET 220 (Electro)	SET 220 (Electro)	SET 220 (Electro)
<b>Integrated Accessories</b>			
Dusting Brush	•	•	•
Upholstery Tool	•	•	•
Crevice Nozzle	•	•	•
Accessory Storage	Integrated	Integrated	VarioClip
<b>Additional Accessories</b>			
Flexible Crevice Tool (SFD 20)	–	–	–
Universal Brush (SUB 20)	–	–	–
Flexible Handheld Mini Turbo Brush	STB 101	STB 101	STB 101
<b>Bags &amp; Filtration</b>			
AirClean Sealed System®	•	–	–
AirClean 3D Efficiency FilterBag™	GN	–	GN
Bagless System	–	•	–
FilterBag™ Change Indicator	•	–	•
AirClean Filter	Optional	–	Optional
Active AirClean Filter	AA 50	–	AA 30
HEPA AirClean Filter	Optional	–	Optional
HEPA Lifetime Filter	–	•	–
ComfortClean	–	•	–
Filter Change Indicator	–	–	–
<b>User conveniences</b>			
Handle Type	Comfort Grip	Electro	Comfort Grip
LED Headlight	–	–	–
360° Swivel (Caster) Wheels	•	•	•
Auto Height Adjustment	–	–	–
SwivelNeck™	–	–	–
Anti-tipping Device	–	–	–
Operating Radius	36ft	33ft	29.5ft
Park-System	Double	•	•
Park Auto-off	•	–	•
Cable Rewind	Comfort One-Touch	Comfort One-Touch	•
Long Electrical Cord	23ft	20ft	18ft
Quick Release Cable Hook	–	–	–
Ergonomic Carrying Handle	•	•	•
Protective Bumper	•	–	•
<b>MAP</b>	<b>\$999.00</b>	<b>\$899.00</b>	<b>\$699.00</b>
<b>List Price</b>	<b>\$1,099.00</b>	<b>\$999.00</b>	<b>\$799.00</b>
<b>Material Number</b>	<b>10014520</b>	<b>10829410</b>	<b>10639470</b>

# Cat & Dog Series

## Product Overview



	<b>Triflex Cat &amp; Dog</b>
<b>Exterior</b>	
Color	Obsidian Black
<b>Performance</b>	
For low to medium pile carpeting and smooth flooring	•
Cleaning performance of a full-size Miele Complete C3 canister vacuum	•
Miele-Made Vortex Motor with 3 adjustable suction settings	•
<b>Filtration</b>	
Mono-Cyclone Vortex Technology	•
Fine Dust Filter	•
Hygiene Lifetime Filter (99.98% Filtration)	-
HEPA Lifetime Filter (99.999%)	•
Dust Bin Capacity	0.5 L
<b>Convenience / Comfort</b>	
Battery-powered, cordless	•
3in1 Design: Power Unit on top, bottom or solo	•
Included Accessories: Upholstery Tool, Crevice Tool, Dusting Brush, Wall Mount	• (+ Electro Compact Handheld Tool)
Power Switch (3 settings, no trigger)	•
Quick Park	•
BrilliantLight LED Headlight	•
Extra VARTA removable battery and charger	-
<b>Additional Details</b>	
Battery Type: VARTA Lithium-Ion, rechargeable	•
Battery charge capacity (watt hours): 63 Wh	•
Max. Power: 275W	•
Voltage output of battery (Volts): 25.2 V	•
Amps (A): 2.5 A	•
Run times	Up to 60 min with PowerUnit Solo (Level 1)
Cleaning area	Up to 1,365 sq. ft.
Recharge time: 4 hours	•
Full vacuum weight (pounds): 7.9 lbs	•
Noise level on hard floor / on carpet (dB(A)): 78 / 80	•
<b>UMRP&amp;MAP/Retail Pricing</b>	
<b>MAP Price</b>	<b>\$699.00</b>
<b>List Price</b>	<b>\$799.00</b>
<b>Material Number</b>	<b>11423900</b>

# Blizzard CX1

## Product Overview



	Blizzard CX1 Electro+	Blizzard CX1 Turbo Team	Blizzard CX1 Pure Suction
<b>Exterior</b>			
Color	Obsidian Black	Tech Blue	Graphite Grey
<b>Power</b>			
Powerful Miele-Made Vortex Motor™	•	•	•
Max. Power	1200W	1200W	1200W
Bagless Vortex Air Flow Technology	•	•	•
Sound Insulation	•	•	•
On/Off Control	Foot Switch	Foot Switch	Foot Switch
Power Setting (Suction) Control	Rotary Dial	Rotary Dial	Rotary Dial
Number of Power Settings	4	4	4
Safety Shut-off / Overheat Protection	•	•	•
<b>Floorheads and Accessories</b>			
Electro Brush Floorhead (SEB)	SEB 228	-	-
Electro Brush Socket	•	-	-
Turbo Brush Floorhead (STB)	Optional	STB 305-3	Optional
Pure Suction Combination Floorhead (SBD)	Optional	Optional	SBD 285-3
Pure Suction Parquet Floorhead (SBB)	SBB 300-3	SBB 300-3	SBB 300-3
Suction Hose	SES 121 (Two-Colored, Electro)	• (Two-Colored, Conical)	• (Two-Colored, Conical)
Telescopic Wand	SET 220 (Electro)	• (Comfort)	• (Comfort)
<b>Integrated Accessories</b>			
Dusting Brush	•	•	•
Upholstery Tool	•	•	•
Crevice Nozzle	•	•	•
Accessory Storage	Integrated	Integrated	Integrated
<b>Filtration</b>			
Bagless System	•	•	•
Hygiene Lifetime Filter	-	-	•
HEPA Lifetime Filter	•	•	-
ComfortClean	•	•	•
<b>User conveniences</b>			
Grip / Handle	• (Electro)	• (Comfort)	• (Comfort)
360° Swivel (Caster) Wheels	•	• (DynamicDrive)	•
Operating Radius	33ft	33ft	33ft
Park-System	•	•	•
Cable Rewind	Comfort One-Touch	Comfort One-Touch	Comfort One-Touch
Long Electrical Cord	20ft	20ft	20ft
Ergonomic Carrying Handle	•	•	•
<b>MAP</b>	<b>\$799.00</b>	<b>\$599.00</b>	<b>\$499.00</b>
<b>List Price</b>	<b>\$899.00</b>	<b>\$699.00</b>	<b>\$599.00</b>
<b>Material Number</b>	<b>10796540</b>	<b>10829400</b>	<b>10829430</b>



# HomeCare Series

## Product Overview



	Complete C3 HomeCare+	Complete C3 HomeCare + SEB 236	Complete C3 HomeCare + SEB 228
<b>Exterior</b>			
Color	Autumn Red	Autumn Red	Autumn Red
Chrome Trim	•	•	•
<b>Power</b>			
Powerful Miele-Made Vortex Motor™	• (Silence)	• (Silence)	• (Silence)
Max. Power	1200W	1200W	1200W
Bagless Vortex Air Flow Technology	–	–	–
Sound Insulation	•	•	•
On/Off Control	Foot Switch	Foot Switch	Foot Switch
Power Setting Control	+/- Handle Controls	+/- Foot Switch	+/- Handle Controls
Illuminated Controls Display	•	•	•
Automatic Power Setting	•	–	–
Number of Power Settings	6	6	6
Safety Shut-off / Overheat Protection	•	•	•
<b>Floorheads and Accessories</b>			
Pure Suction Combination Floorhead (SBD)	SBD 285-3	SBD 285-3	SBD 285-3
Turbo Brush Floorhead (STB)	Optional	Optional	Optional
Electro Brush Floorhead (SEB)	SEB 236	SEB 236	SEB 228
Electro Brush Socket	•	•	•
Pure Suction Parquet Floorhead (SBB)	Optional	Optional	Optional
Suction Hose	SES 131 (Electro)	SES 121 (Electro)	SES 121 (Electro)
Telescopic Wand	SET 220 (Electro)	SET 220 (Electro)	SET 220 (Electro)
<b>Integrated Accessories</b>			
Dusting Brush	•	•	•
Upholstery Tool	•	•	•
Crevice Nozzle	•	•	•
Accessory Storage	Integrated	Integrated	Integrated
Flexible Crevice Tool (SFD 20)	•	•	•
Universal Brush (SUB 20)	•	•	•
<b>Bags &amp; Filtration</b>			
AirClean Sealed System®	•	•	•
AirClean 3D Efficiency FilterBag™	GN	GN	GN
Bagless System	–	–	–
FilterBag™ Change Indicator	•	•	•
AirClean Filter	Optional	Optional	Optional
Active AirClean Filter	Optional	Optional	Optional
HEPA AirClean Filter	HA 50	HA 50	HA 50
HEPA Lifetime Filter	–	–	–
ComfortClean	–	–	–
Filter Change Indicator	•	–	–
<b>User conveniences</b>			
Comfort Grip Handle	• (Deluxe)	• (Deluxe)	• (Deluxe)
LED Headlight	•	•	–
360° Swivel (Caster) Wheels	•	•	•
Auto Height Adjustment	–	–	–
SwivelNeck™	–	–	–
Anti-tipping Device	–	–	–
Operating Radius	36ft	36ft	36ft
Park-System	Double	Double	Double
Park Auto-Off	•	•	•
Cable Rewind	Comfort One-Touch	Comfort One-Touch	Comfort One-Touch
Long Electrical Cord	23ft	23ft	23ft
Quick Release Cable Hook	–	–	–
Ergonomic Carrying Handle	•	•	•
Protective Bumper	•	•	•
<b>List Price</b>	<b>\$1,499.00</b>	<b>\$1,099.00</b>	<b>\$1,049.00</b>
<b>Material Number</b>	<b>10014750</b>	<b>94001420</b>	<b>94001410</b>



	Complete C3 HomeCare + SEB 217	Complete C3 HomeCare Pure Suction	Classic C1 HomeCare
<b>Exterior</b>			
Color	Autumn Red	Autumn Red	Autumn Red
Chrome Trim	•	•	–
<b>Power</b>			
Powerful Miele-Made Vortex Motor™	• (Silence)	• (Silence)	•
Max. Power	1200W	1200W	1200W
Bagless Vortex Air Flow Technology	–	–	–
Sound Insulation	•	•	•
On/Off Control	Foot Switch	Foot Switch	Foot Switch
Power Setting Control	+/- Foot Switch	+/- Foot Switch	Rotary Dial
Illuminated Controls Display	•	•	–
Automatic Power Setting	–	–	–
Number of Power Settings	6	6	6
Safety Shut-off / Overheat Protection	•	•	•
<b>Floorheads and Accessories</b>			
Pure Suction Combination Floorhead (SBD)	SBD 285-3	SBD 285-3	SBD 285-3
Turbo Brush Floorhead (STB)	Optional	–	Optional
Electro Brush Floorhead (SEB)	SEB 217	–	SEB 228
Electro Brush Socket	•	•	•
Pure Suction Parquet Floorhead (SBB)	Optional	SBB 300-3	Optional
Suction Hose	SES 121 (Electro)	•	SES 116 (Electro)
Telescopic Wand	SET 220 (Electro)	•	SET 220 (Electro)
<b>Integrated Accessories</b>			
Dusting Brush	•	•	•
Upholstery Tool	•	•	•
Crevice Nozzle	•	•	•
Accessory Storage	Integrated	Integrated	VarioClip
Flexible Crevice Tool (SFD 20)	•	•	•
Universal Brush (SUB 20)	•	•	•
<b>Bags &amp; Filtration</b>			
AirClean Sealed System®	•	•	–
AirClean 3D Efficiency FilterBag™	GN	GN	GN
Bagless System	–	–	–
FilterBag™ Change Indicator	•	•	•
AirClean Filter	Optional	Optional	SAC 20/30
Active AirClean Filter	Optional	Optional	Optional
HEPA AirClean Filter	HA 50	HA 50	HA 30
HEPA Lifetime Filter	–	–	–
ComfortClean	–	–	–
Filter Change Indicator	–	•	•
<b>User conveniences</b>			
Comfort Grip Handle	• (Deluxe)	• (Deluxe)	•
LED Headlight	–	–	–
360° Swivel (Caster) Wheels	•	•	•
Auto Height Adjustment	–	–	–
SwivelNeck™	–	–	–
Anti-tipping Device	–	–	–
Operating Radius	36ft	36ft	29.5ft
Park-System	Double	Double	Double
Park Auto-Off	•	–	•
Cable Rewind	Comfort One-Touch	Comfort One-Touch	•
Long Electrical Cord	23ft	23ft	18ft
Quick Release Cable Hook	–	–	–
Ergonomic Carrying Handle	•	•	•
Protective Bumper	•	•	•
<b>List Price</b>	<b>\$999.00</b>	<b>\$799.00</b>	<b>\$799.00</b>
<b>Material Number</b>	<b>94001400</b>	<b>11181050</b>	<b>10367690</b>

# HomeCare Series

## Product Overview



	Classic C1 Pure Suction Home Care	Compact C1 HomeCare	Dynamic U1 HomeCare
<b>Exterior</b>			
Color	Autumn Red	Autumn Red	Autumn Red
Chrome Trim	-	-	-
<b>Power</b>			
Powerful Miele-Made Vortex Motor™	•	•	•
Max. Power	1200W	1200W	1200W
Bagless Vortex Air Flow Technology	-	-	-
Sound Insulation	•	-	•
On/Off Control	Foot Switch	Foot Switch	Handle Control
Power Setting Control	Rotary Dial	Rotary Dial	Rotary Dial
Illuminated Controls Display	-	-	-
Automatic Power Setting	-	-	-
Number of Power Settings	6	6	4
Safety Shut-off / Overheat Protection	•	•	•
<b>Floorheads and Accessories</b>			
Pure Suction Combination Floorhead (SBD)	SBD 285-3	SBD 285-3	-
Turbo Brush Floorhead (STB)	-	SBD 205-3	-
Electro Brush Floorhead (SEB)	-	-	Power Plus
Electro Brush Socket	•	-	-
Pure Suction Parquet Floorhead (SBB)	-	Optional	-
Suction Hose	•	•	•
Telescopic Wand	•	•	•
<b>Integrated Accessories</b>			
Dusting Brush	•	•	•
Upholstery Tool	•	•	•
Crevice Nozzle	•	•	•
Accessory Storage	VarioClip	VarioClip	Integrated
Flexible Crevice Tool (SFD 20)	•	-	-
Universal Brush (SUB 20)	•	-	-
<b>Bags &amp; Filtration</b>			
AirClean Sealed System®	-	•	•
AirClean 3D Efficiency FilterBag™	GN	GN	U
Bagless System	-	-	-
FilterBag™ Change Indicator	•	•	•
AirClean Filter	SAC 20/30	SAC 20/30	Optional
Active AirClean Filter	Optional	Optional	Optional
HEPA AirClean Filter	HA 30	Optional	HA 30
HEPA Lifetime Filter	-	-	-
ComfortClean	-	-	-
Filter Change Indicator	•	-	-
<b>User Conveniences</b>			
Comfort Grip Handle	•	•	•
LED Headlight	-	-	•
360° Swivel (Caster) Wheels	•	•	•
Auto Height Adjustment	-	-	•
SwivelNeck™	-	-	•
Anti-tipping Device	-	-	•
Operating Radius	29.5ft	29.5ft	54ft
Park-System	Double	Double	-
Park Auto-Off	-	•	•
Cable Rewind	•	•	Quick Release Cord Hook
Long Electrical Cord	18ft	18ft	39ft
Quick Release Cable Hook	-	-	•
Ergonomic Carrying Handle	•	•	•
Protective Bumper	•	•	-
<b>List Price</b>	<b>\$449.00</b>	<b>\$599.00</b>	<b>\$799.00</b>
<b>Material Number</b>	<b>11262170</b>	<b>10850050</b>	<b>10533350</b>



<b>Triflex HX1 HomeCare</b>	
<b>Exterior</b>	
Color	Ruby Red
<b>Performance</b>	
For low to medium pile carpeting and smooth flooring	•
Cleaning performance of a full-size Miele Complete C3 canister vacuum	•
Miele-Made Vortex Motor with 3 adjustable suction settings	•
<b>Filtration</b>	
Mono-Cyclone Vortex Technology	•
Fine Dust Filter	•
Hygiene Lifetime Filter (99.98% Filtration)	•
HEPA Lifetime Filter (99.999%)	-
Dust Bin Capacity	0.5 L
<b>Convenience / Comfort</b>	
Battery-powered, cordless	•
3in1 Design: Power Unit on top, bottom or solo	•
Included Accessories: Upholstery Tool, Crevice Tool, Dusting Brush, Wall Mount	•
Power Switch (3 settings, no trigger)	•
Quick Park	•
BrilliantLight LED Headlight	-
Extra VARTA removable battery and charger	-
<b>Additional Details</b>	
Battery Type: VARTA Lithium-Ion, rechargeable	•
Battery charge capacity (watt hours): 63 Wh	•
Max. Power: 275W	•
Voltage output of battery (Volts): 25.2 V	•
Amps (A): 2.5 A	•
Run times	Up to 60 min with PowerUnit Solo (Level 1)
Cleaning area	Up to 1,365 sq. ft.
Recharge time: 4 hours	•
Full vacuum weight (pounds): 7.9 lbs	•
Noise level on hard floor / on carpet (dB(A)): 78 / 80	•
<b>UMRP&amp;MAP/Retail Pricing</b>	
List Price	\$699.00
<b>Material Number</b>	<b>11423890</b>



# Triflex HX1 Series

## Product Overview



	Triflex HX1 Pro	Triflex HX1 Graphite Grey	Triflex HX1 Lotus White
<b>Exterior</b>			
Color	Infinity Grey Pearl Finish	Graphite Grey	Lotus White
<b>Performance</b>			
For low to medium pile carpeting and smooth flooring	•	•	•
Cleaning performance of a full-size Miele Complete C3 canister vacuum	•	•	•
Miele-Made Vortex Motor with 3 adjustable suction settings	•	•	•
<b>Filtration</b>			
Mono-Cyclone Vortex Technology	•	•	•
Fine Dust Filter	•	•	•
Hygiene Lifetime Filter (99.98% Filtration)	-	•	•
HEPA Lifetime Filter (99.999%)	•	-	-
Dust Bin Capacity	0.5 L	0.5 L	0.5 L
<b>Convenience / Comfort</b>			
Battery-powered, cordless	•	•	•
3in1 Design: Power Unit on top, bottom or solo	•	•	•
Included Accessories: Upholstery Tool, Crevice Tool, Dusting Brush, Wall Mount	•	•	•
Power Switch (3 settings, no trigger)	•	•	•
Quick Park	•	•	•
BrilliantLight LED Headlight	•	-	-
Extra VARTA removable battery and charger	•	-	-
<b>Additional Details</b>			
Battery Type: VARTA Lithium-Ion, rechargeable	•	•	•
Battery charge capacity (watt hours): 63 Wh	•	•	•
Max. Power: 275W	•	•	•
Voltage output of battery (Volts): 25.2 V	•	•	•
Amps (A): 2.5 A	•	•	•
Run times	Up to 120 min with PowerUnit Solo (Level 1)	Up to 60 min with PowerUnit Solo (Level 1)	Up to 60 min with PowerUnit Solo (Level 1)
Cleaning area	Up to 2,690 sq. ft.	Up to 1,345 sq. ft.	Up to 1,345 sq. ft.
Recharge time: 4 hours	•	•	•
Full vacuum weight (pounds): 7.9 lbs	•	•	•
Noise level on hard floor / on carpet (dB(A)): 78 / 80	•	•	•
<b>UMRP&amp;MAP/Retail Pricing</b>			
<b>MAP Price</b>	<b>\$799.00</b>	<b>\$499.00</b>	<b>\$499.00</b>
<b>List Price</b>	<b>\$899.00</b>	<b>\$599.00</b>	<b>\$599.00</b>
<b>Material Number</b>	<b>11423920</b>	<b>11423880</b>	<b>11423870</b>

# Robot Vacuum Cleaner

## Product Overview



	<b>Scout RX2 Home Vision</b>
<b>Exterior</b>	
Color	Graphite Grey Pearl Finish
<b>System</b>	
Quattro Cleaning System	•
Retractable Corner Brushes	2
Rotary Brush	•
Front Suction	•
Rear Brushless Motor	•
3D Smart Navigation System	•
Digital Ceiling Camera	2
Gyro Sensor	•
Anti-Collision Sensors	7
Anti-Fall Sensors	3
Number of Modes	4
Auto	•
Spot	• (6x6ft area)
Turbo	•
Silent	•
Furniture Protection Technology	•
Timer	• (7 Programs)
<b>Operation</b>	
Touch User Interface	•
Remote Control	•
Mobile Control (Smartphone App)	•
Miele@home	•
WiFiConn@ct	•
MobilControl	•
Home Mapping	•
Home Vision	•
Max Carpet Climb Height	0.7 in
Rechargeable Battery	4,400 mAh Li-ion
Recharge Time	170 min
Cleaning Area	1,600 sq ft
Operating Time	120 min
<b>Dustbox &amp; Filtration</b>	
Dustbox Volume	0.5 L
AirClean Filter	AirClean Plus
<b>Accessories</b>	
Base Charging Station with Adapter	•
Area Demarcation	Magnetic Tape (3.1ft)
Sealing Lip	•
Chevron Style Brush Roll	•
Side Brushes	2
Replacement Filters	1
<b>MAP</b>	<b>\$599.00</b>
<b>List Price</b>	<b>\$699.00</b>
<b>Material Number</b>	<b>10673920</b>



## Combination Floorheads

For Hard Surfaces and Low-Pile Carpet





### **AllTeQ Combination Floorhead SBD 285-3**

- Extendable and retractable bristle strip for use when needed
- Double swivel joint and metal soleplate for easy gliding across surfaces
- Rubberized wheels to prevent scratches on hard floor

---

**Material Number: 07253830**

**MAP: \$69.00**

**List Price: \$79.00**

## Pure Suction Floorheads

For Hard Surfaces Only





### **Parquet Twister XL Floorhead SBB 400-3**

- At 16" wide, large areas of flooring can be vacuumed in a short amount of time
- Includes a flexible double-swivel joint along with soft, natural bristles which glide smoothly over floors

---

**Material Number: 07101160**  
**MAP: \$89.00**  
**List Price: \$99.00**



### **Parquet Twister Floorhead SBB 300-3**

- Features a double-swivel joint which rotates 180 degrees, for quick and easy vacuuming around furniture and obstacles
- Soft, natural bristles allow for easy gliding along smooth surfaces

---

**Material Number: 07155710**  
**MAP: \$69.00**  
**List Price: \$79.00**

# Turbo Brush Floorheads

For Short-Pile Carpet





### **TurboTeQ Floorhead STB 305-3**

- For thorough cleaning of short pile carpets, a rotating roller brush works to loosen dirt in the floor while also collecting hair and threads
- Does not stick to carpets thanks to the air adjustment valve
- No separate connection, powered by the air stream

---

**Material Number: 10455360**

**MAP: \$119.00**

**List Price: \$139.00**



## Electro Brush Floorheads

For Deep-Pile And Dense Carpets



### **Electro Premium Floorhead SEB 236**

- Motor-driven with five-level height adjustment to adjust to different carpet pile depths
- Swivel neck function for extreme maneuverability
- Features an electrical beater bar for removing deep, persistent soil embedded in your carpet
- Integrated LED lighting

---

**Material Number: 07311290**  
**MAP: \$259.00**  
**List Price: \$285.00**



### **Electro Plus Floorhead SEB 228**

- Motor-driven with 14" wide brush roll
- Five-level height adjustment allowing for quick, intensive cleaning of all carpet types
- Swivel neck function for extreme maneuverability
- Features an electrical beater bar for removing deep, persistent soil embedded in your carpet

---

**Material Number: 07359280**  
**MAP: \$209.00**  
**List Price: \$219.00**



### **Electro Comfort Floorhead SEB 217-3**

- Motor-driven with 10.5" wide brush roll
- Swivel neck function for extreme maneuverability
- Features an electrical beater bar for removing deep, persistent soil embedded in your carpet

---

**Material Number: 07250160**  
**MAP: \$160.00**  
**List Price: \$170.00**

## Additional Accessories





### Handheld Mini Turbobrush STB 101

- Powered directly by air stream
- Air adjustment slide for adjusting to different surfaces
- 6" suction inlet with beater bar for fast and efficient removal of hair

**Material Number: 07252850**  
**MAP: \$75.00**  
**List Price: \$85.00**



### Dusting Brush SSP 10

- Features soft, natural bristles to clean delicate surfaces
- An adjustable swivel joint and soft bumper strip allow for easy maneuvering along furniture

**Material Number: 07132710**  
**MAP: \$19.95**  
**List Price: \$19.95**



### Extended Flexible Crevice Tool SFD 20

- Easily reach around furniture and appliances
- Impressive length of 22" with flexible central section
- Fits directly onto the handle of Miele canister vacuum cleaners

**Material Number: 07252100**  
**MAP: \$29.95**  
**List Price: \$29.95**



### Extended Crevice Tool SFD 10

- Excellently suited for cleaning narrow crevices and gaps
- At 12" long, clean behind beds and between car seats with ease
- Fits directly onto the handle of Miele canister vacuum cleaners

**Material Number: 07250050**  
**MAP: \$25.95**  
**List Price: \$25.95**



### Flexible Hose Extension SFS 10

- Provides an additional five feet to the overall cleaning radius while vacuuming
- Fits in between the vacuum handle and suction wand
- Practical storage in the hose sleeve after done vacuuming

\*May only be used with non-electrical hose and wand

**Material Number: 07252210**  
**MAP: \$39.95**  
**List Price: \$39.95**



### Radiator Brush SHB 30

- Durable yet gentle, made from strong and robust synthetic bristles
- Clean difficult-to-reach areas with ease such as radiators, vents, refrigerator coils and air conditioners

**Material Number: 09660490**  
**MAP: \$25.95**  
**List Price: \$25.95**



### Mattress Tool SMD 10

- For cleaning gaps between bed frames, mattresses and sofa cushions
- Features a thread catcher on its underside for easy removal of hair and debris

**Material Number: 07252280**  
**MAP: \$25.95**  
**List Price: \$25.95**



### Wide Upholstery Tool SPD 10

- Extra wide suction nozzle for efficient cleaning of stubborn pet hair, lint and dirt from upholstery and curtains
- Features a wide thread catcher for removal of thread and hair
- Nozzle is adjustable for flexibility

**Material Number: 07252190**  
**MAP: \$29.95**  
**List Price: \$29.95**



### Hygiene Cap SHV 10

- For the separate storage of the vacuum and hose
- This unique cap works with charcoal to neutralize unpleasant odors when the hose is removed from the vacuum
- Easily attached to the suction hose with practical clip connection

\*Replacement should occur on a yearly basis.

**Material Number: 06622030**  
**MAP: \$9.95**  
**List Price: \$9.95**



### Adjustable Universal Brush SUB 20

- Features soft, natural bristles and swivel neck
- Perfect for dusting bookshelves, mantles, moldings, ceiling fans and sculptures
- Includes soft bumper strip to prevent scratches to furniture
- Fits directly onto the handle of Miele canister vacuum cleaners

**Material Number: 07475870**  
**MAP: \$39.95**  
**List Price: \$39.95**




### Spotlight Handle SGC 20

- The single touch of a button prompts the LED lighting in the vacuum handle
- For practical illumination of areas that need to be cleaned
- Nothing will go unnoticed while vacuuming in dark closets or spaces

**Material Number: 09385930**  
**MAP: \$99.95**  
**List Price: \$109.95**



## Triflex HX1 Accessories





### **VARTA® Lithium-Ion Battery HX LA**

- Powerful with seven high-performance cells
- Powered by VARTA®
- Replacing the battery is quick and easy

---

**Material Number: 11384710**  
**MAP: \$159.00**  
**List Price: \$169.00**



### **Charger Cradle HX LS USA**

- Combines maximum convenience with long run times
- The perfect complement for a second battery
- Allows another battery to be charged at the same time

---

**Material Number: 11607500**  
**MAP: \$99.00**  
**List Price: \$109.00**



### **Electro Compact Handheld Brush HX SEB**

- For use on upholstery and car seats
- 6.3" wide
- Powered roller lifts fibers for thorough cleaning

---

**Material Number: 11384950**  
**MAP: \$129.00**  
**List Price: \$139.00**



### **Fine Dust Filter HX FSF**

- Fine dust filter to maintain suction power
- Replacement recommended every 3 years
- Pleated material catches ultrafine dust particles

---

**Material Number: 11385020**  
**MAP: \$39.99**  
**List Price: \$49.99**

## Robot Vacuum Accessories





### Magnetic Strips RX-MB 4

- Defines the areas that you would not like vacuumed
- Can be placed temporarily or permanently to block off rooms or flooring
- The Scout Robot comes equipped with four, 3-foot magnetic strips

**Material Number: 09782660**  
**MAP: \$29.95**  
**List Price: \$34.95**



### AirClean Plus Filter RX2-AP

- Effective filtration of dust particles
- 2-stage filter system safely seals in dust
- To maintain machine performance, change twice a year

**Material Number: 10592080**  
**MAP: \$19.99**  
**List Price: \$24.99**



### Side Brushes RX2-SB

- For thorough cleaning along edges and in corners
- With premium, robust synthetic bristles
- For cleaning hard floors and carpets

**Material Number: 10592090**  
**MAP: \$19.99**  
**List Price: \$24.99**



### Beater Bar RX2-BW

- Rotates to remove stubborn soiling
- With premium, robust synthetic bristles
- For cleaning hard floors and carpets


**Material Number: 10592110**  
**MAP: \$29.99**  
**List Price: \$34.99**



### Sealing Lip Set RX2-DL

- For effective and reliable dust pick-up
- For cleaning hard floors and carpets

**Material Number: 10592100**  
**MAP: \$29.99**  
**List Price: \$34.99**



### Accessories Pack RX2-A

- Covers annual accessory needs with a single purchase at a discounted price
- Includes: 2 AirClean Plus Filters, 1 Right Side Brush, 1 Left Side Brush, 1 Sealing Lip Set, 1 Beater Bar

**Material Number: 10808470**  
**MAP: \$89.99**  
**List Price: \$99.99**

# Original Miele FilterBags™

## Compatibility With Miele Vacuum Cleaners



Type	AirClean 3D Efficiency FJM	AirClean 3D Efficiency GN	AirClean 3D Efficiency U	AirClean KK
<b>Contents</b>	4 Bags + 2 Filters	4 Bags + 2 Filters	4 Bags + 2 Filters	5 Bags + 2 Filters
<b>Color of Dustbag Collar:</b>	Red	Blue	Green	Yellow
<b>Complete C3</b> S 8000 - S 8999		•		
<b>Complete C2</b> S 5000 - S 5999		•		
<b>Complete C1</b> S 700 - S 799	•			
<b>Compact C2</b> S 6000 - S 6999	•			
<b>Compact C1</b> S 4000 - S 4999	•			
<b>Classic C1</b> S 2120 - S 2180		•		
<b>Dynamic U1</b> S 7510 - S 7580			•	
<b>Swing H1</b> S 140 - S 195				•
S 600 - S 658		•		
S 500 - S 558	•			
S 400 - S 456 i		•		
S 300 i - S 381	•			
S 246 i - S 256 i	•			
<b>Material Number</b>	10123220	10123210	10123230	10123240
<b>MAP</b>	\$18.95	\$18.95	\$18.95	\$18.95
<b>List Price</b>	\$20.85	\$20.85	\$20.85	\$20.85

# Original Miele FilterBags™

## Compatibility With Miele Vacuum Cleaners



Type	AirClean 3D XL-Pack GN	AirClean 3D XL-Pack FJM	AirClean 3D Allergy XL-Pack GN	AirClean 3D Allergy XL-Pack FJM
<b>Contents</b>	8 x AirClean GN 3D Efficiency dustbags 2 x motor protection filters 2 x AirClean filters	8 x AirClean FJM 3D Efficiency dustbags 2 x motor protection filters 2 x AirClean filters	8 x AirClean GN 3D Efficiency dustbags 2 x motor protection filters 1 x HEPA AirClean SF-HA 50 Filter	8 x AirClean FJM 3D Efficiency dustbags 2 x motor protection filters 1 x HEPA AirClean SF-HA 50 Filter
<b>Color of Dustbag Collar:</b>	Blue	Red	Blue	Red
<b>Complete C3</b> S 8000 - S 8999	●		●	
<b>Complete C2</b> S 5000 - S 5999	●		●	
<b>Complete C1</b> S 700 - S 799		●		
<b>Compact C2</b> S 6000 - S 6999		●		●
<b>Compact C1</b> S 4000 - S 4999	●			●
<b>Classic C1</b> S 2120 - S 2180	●			
<b>Dynamic U1</b> S 7510 - S 7580				
<b>Swing H1</b> S 140 - S 195				
S 600 - S 658	●			
S 500 - S 558		●		
S 400 - S 456 i	●			
S 300 i - S 381		●		
S 246 i - S 256 i		●		
<b>Material Number</b>	10455150	10455190	11214190	11214240
<b>MAP</b>	\$34.95	\$34.95	\$79.95	\$79.95
<b>List Price</b>	\$48.95	\$48.95	\$89.95	\$89.95

# Original Miele FilterBags™

Compatibility With Miele Vacuum Cleaners



Type	AirClean 3D Efficiency FJM Performance Pack	AirClean 3D Efficiency GN Performance Pack		AirClean 3D Efficiency U Performance Pack
<b>Contents</b>	16 Bags + 4 Pre-Motor Filters +HA 50	16 Bags + 4 Pre-Motor Filters + HA 30 or HA 50		16 Bags + 4 Pre-Motor Filters + HA 30 or HA 50
<b>Color of Dustbag Collar:</b>	Red	Blue		Green
		HA 30	HA 50	
<b>Complete C3</b> S 8000 - S 8999			•	
<b>Complete C2</b> S 5000 - S 5999			•	
<b>Complete C1</b> S 700 - S 799	•			
<b>Compact C2</b> S 6000 - S 6999	•			
<b>Compact C1</b> S 4000- S 4999	•			
<b>Classic C1</b> S 2120 - S 2180		•		
<b>Dynamic U1</b> S 7510 - S 7580				•
<b>Swing H1</b> S 140 - S 195				
S 600 - S 658		•		
S 500 - S 558	•			
S 400 - S 456 i		•		
S 300 i - S 381	•			
S 246 i - S 256 i	•			
<b>Material Number</b>	10512520	10512510	10512500	10512530
<b>MAP</b>	\$99.95	\$99.95	\$99.95	\$99.95
<b>List Price</b>	\$139.95	\$139.95	\$139.95	\$139.95

# Original Miele AirClean Filters

## Compatibility With Miele Vacuum Cleaners



Type	HEPA AirClean Filters		Active AirClean Filters		AirClean Filters	HEPA AirClean Filters	Active Air Clean Filters
	SF-HA 50	SF- HA 30	SF-AA 50	SF-AA 30	SF- SAC 20/30	SF- H 10	SF-AA 10
<b>Complete C3</b> S 8000 - S 8999	•		•		•		
<b>Complete C2</b> S 5000 - S 5999	•		•		•		
<b>Complete C1</b> S 700 - S 799		•		•	•		
<b>Compact C2</b> S 6000 - S 6999	•		•		•		
<b>Compact C1</b> S 4000- S 4999	•		•		•		
<b>Classic C1</b> S 2120 - S 2180		•		•	•		
<b>Dynamic U1</b> S 7510 - S 7580		•		•	•		
<b>Swing H1</b> S 140 - S 195						•	•
S 600 - S 658		•		•	•		
S 500 - S 558		•		•	•		
S 400 - S 456 i		•		•	•		
S 300 i - S 381		•		•	•		
<b>Material Number</b>	09616280	09616270	09616110	09616080	03944711	09884650	07496330
<b>MAP</b>	\$49.95	\$49.95	\$39.95	\$49.95	\$11.95	\$49.95	\$39.95
<b>List Price</b>	\$58.95	\$58.95	\$44.95	\$58.95	\$13.95	\$58.95	\$44.95



# Countertop Coffee Machines

## Product Overview



Model	CM 5300	CM 6150	CM 6350
<b>Construction type</b>			
Countertop bean-to-cup coffee machine	•	•	•
<b>Design</b>			
Control panel	DirectSensor	DirectSensor	DirectSensor
<b>Beverage specialties</b>			
Espresso/Coffee/Long Coffee/Ristretto	•/•/•/•	•/•/•/•	•/•/•/•
Cappuccino/Latte Macchiato/Cafe Latte	•/•/•	•/•/•	•/•/•
Hot Water/Hot Milk/Milk Froth	•/•/•	-/•/•	•/•/•
<b>Consumer benefits</b>			
OneTouch/OneTouch for Two preparation	•/•	•/•	•/•
Flavor preserving conical grinding unit	•	•	•
Second type of coffee possible using ground coffee	•	•	•
Programmable user profiles	-	4	4
Grinding grade adjustable/Grinding grade programmable	•/•	•/•	•/•
Water quantity/Water temperature programmable	•/•	•/•	•/•
Pre-brewing/Milk quantity/Milk froth quantity programmable	•/•/•	•/•/•	•/•/•
Coffee Pot Function	•	•	•
<b>User convenience</b>			
Individual language selection	•	•	•
Height adjustable central spout in inches	3 1/8" – 5 1/2"	3 1/8" – 5 1/2"	3 1/8" – 5 1/2"
Integrated Cup Warmer	-	-	•
BrilliantLight	-	-	•
Capacity of coffee bean container in ounces	7 oz	10.58 oz	10.58 oz
Capacity of waste container in portions	6 portions	10 portions	10 portions
Capacity of water container in ounces	44 oz	61 oz	61 oz
Switch-on time programmable/Switch-off time programmable	•/•	•/•	•/•
Standby time programmable/Time buffer in h	•/-	•/-	•/-
<b>Cleaning convenience</b>			
Convenient cleaning program/ComfortClean	•/•	•/•	•/•
Automatic rinsing of the milk pipework from the water container	-	•	•
Removable milk pipework/brew unit	•/•	•/•	•/•
<b>Safety</b>			
System lock	•	•	•
<b>Technical data</b>			
Appliance dimensions in inches (W x H x D)	9 1/2" x 14 3/16" x 18 1/8"	10" x 14 1/8" x 16 3/4"	10" x 14 1/8" x 16 3/4"
Electrical Requirements	120 V, 60 Hz, 15 Amps	120 V, 60 Hz, 15 Amps	120 V, 60 Hz, 15 Amps
Plug Type	NEMA 5 – 15 plug	NEMA 5 – 15 plug	NEMA 5 – 15 plug
<b>Standard accessories</b>			
Glass/Stainless steel milk flask	-/-	-/-	-/•
Descaling Agent/Cleaning tablets	•/•	•/•	•/•
<b>UMRP &amp; MAP/Retail pricing</b>	<b>\$1,499/\$1,599</b>	<b>\$1,899/\$1,999</b>	<b>\$2,299/\$2,399</b>
<b>Item Number</b>			
Lotus White		10662810	10662840
Obsidian Black	10969250	10662820	10662850
Graphite Grey	10969230	-	10731210

# Coffee Accessories


## Product Overview



### MB-CM-G Glass Milk Container

- For all Miele CM countertop coffee machines
- A second container for intense appliance use
- 0.7 gallon capacity

Item Number: 11574240  
UMRP/MAP Price: \$49  
Retail Pricing: \$49



### Cleaning Brush for Milk Pipework

- Note: Milk pipework is automatically rinsed after each coffee drink is brewed
- This tool allows for manual cleaning to ensure the best hygiene for your machine

Item Number: 07331640  
UMRP/MAP Price: \$15.99  
Retail Pricing: \$15.99



### Glass Milk Flask Storage Lid

- Securely store milk in the glass milk flask for fresh and safe keeping

Item Number: 09327751  
UMRP/MAP Price: \$49  
Retail Pricing: \$49



### CJ1 TopTherm Coffee Pot

- Make and store up to 8 servings of coffee
- Insulated stainless steel for keeping coffee and tea hot

Item Number: 10694310  
UMRP/MAP Price: \$119  
Retail Pricing: \$119



### Milk Flask w/ EasyClick Cap (Left) Glass Milk Flask (Right)

- The Milk Flask w/ EasyClick Cap simply clicks into place at the front of the appliance and is easily removed
- The Glass Milk Flask is used in preparing hot milk and milk froth
- Standard with all built-in coffee machines

Item Number: 09552740 UMRP/ MAP Price: \$139 Retail Price: \$139  
Item Number: 09627120 UMRP/MAP Price: \$99 Retail Price: \$99



### Black Edition - One For All

Perfect for making espresso, coffee, as well as coffee specialties with milk.

- 100% Arabica
- Full-bodied, balanced intensity
- Fair trade / USDA organic certified DE-ÖKO-001, non-EU Agriculture
- Created specifically for Miele coffee machines
- 4 pack of 8.8 oz whole coffee beans roasted in Germany

Item Number: 11030100  
UMRP/MAP Price: \$44.99  
Retail Pricing: \$44.99



### Black Edition - Espresso

Perfect for making espresso.

- 80% Arabica / 20% Robusta
- Intense, strong flavors
- Fair trade / USDA organic certified DE-ÖKO-001, non-EU Agriculture
- Created specifically for Miele coffee machines
- 4 pack of 8.8 oz whole coffee beans roasted in Germany

Item Number: 11029650  
UMRP/MAP Price: \$44.99  
Retail Pricing: \$44.99



### Black Edition - Café Crema

Perfect for making Café Crema.

- 100% Arabica
- Full-bodied
- Fair trade / USDA organic certified DE-ÖKO-001, non-EU Agriculture
- Created specifically for Miele coffee machines
- 4 pack of 8.8 oz whole coffee beans roasted in Germany

Item Number: 11029370  
UMRP/MAP Price: \$44.99  
Retail Pricing: \$44.99



### Black Edition - Decaf

Perfect for making decaf espresso, coffee, as well as coffee specialties with milk.

- 100% Arabica
- Full-bodied, very intense
- Fair trade / USDA organic certified DE-ÖKO-001, non-EU Agriculture
- Created specifically for Miele coffee machines
- 4 pack of 8.8 oz whole coffee beans roasted in Germany

Item Number: 11029870  
UMRP/MAP Price: \$44.99  
Retail Pricing: \$44.99



Miele  
2 Latte macchiatos  
Espresso - Portion 2  
Stop

Miele

# Rotary Ironer

## Product Overview



<b>Model</b>	<b>B 990</b>
<b>Design</b>	
Appliance Color	Lotus White
<b>Perfect Ironing Results</b>	
Temperature Selection to Suit Textiles	•
High Contact Pressure (N/cm <sup>2</sup> )	0.35
Laundry Feed Board for Easy Laundry Feed	•
Convenient Infeed Board with Ample Storage Space	•
Airing Bar for Crease-Free Cooling	•
<b>Time-Saving Ironing</b>	
Roller Length	32 13/4"
Variable Roller Speed	•
Moisture-Absorbing Roller Padding	•
<b>User Convenience</b>	
Effortless Ironing While Seated Possible	•
Free, Unsupported Roller End	•
Clear Controls	•
Wide Foot Control Bar	•
Convenient Folding Mechanism	•
Easily Maneuverable Thanks to Four Casters	•
<b>Safety</b>	
Automatic Finger Guard	•
Emergency Release	•
Good Stability	•
<b>Technical Data</b>	
Dimensions (W x H x D)	39 3/8" x 37" x 16 3/8"
Dimensions When Folded Away (W x H x D)	19 9/16" x 41 1/2" x 15"
Total Connected Load in kW	2.9
Fuse Rating	13 A
Weight	83.8 lbs
Roller Speed	2 – 4.5 m/min
<b>Material Number</b>	
White	7222730
<b>UMRP &amp; MAP / Retail Pricing</b>	<b>\$2,049 / \$2,249</b>

# Rotary Ironer (commercial-grade)

## Product Overview



<b>Model</b>	<b>HM 16- 80 D</b>
<b>Performance Data</b>	
Roller Diameter	6"
Roller Width	32.5"
At 20% Residual Moisture (according to DIN 11902) (yards/h)	14
<b>Controls/Programs</b>	
Clear, Concise and Simple Controls	•
5-Stage Speed Control (ft/min)	6.5 - 15
Individually Adjustable Roller Speed (rpm)	4 - 9
Freely Selectable Temperatures for a Wide Variety of Textiles	•
<b>Features</b>	
Convenient Footswitch Control	•
Temperature Limiter	•
Return Feed	•
Roller Bearings on Both Sides	-
Padding: Polyester Needle Felt with ARAMID Needle Felt Cloth	•
Aluminum Trough	•
Finger Guard	•
Manual Heater Plate Release in Event of Power Failure	•
Heater Indicator Lamp	•
Chrome-Plated Airing Bar for Crease-Free Laundry Cooldown and Airing	•
Rapid Heat-Up and Uniform Heat Distribution Thanks to Aluminm Trough	•
Ample Space for Ironed Laundry	•
<b>Electrical Connection</b>	
Mains Connection	2 AC 208 — 240V, 50 - 60Hz
Heating (kW)	3.1 - 3.7
Total Rated Load (kW)	3.2 - 3.8
Fuse Rating (A)	2 pole 20A
Plug	NEMA 6-20
Steam-Heated	•
Boiler (kW)	0.85
Water Tank Volume (oz)	27
Steam Availability at Start-Up (min)	4
Steam Delivery Time (min)	40
<b>Type</b>	
Space-Saving Installation Against a Wall Possible	•
Fold-Away Design	•
Designed and Tested for Commercial Use/Longevity	•
Casing	White Enamel
External Dimensions (H x W x D)	38" x 39" x 15"
Weight (lbs.)	86
<b>Material Number</b>	
White	10238590
<b>UMRP&amp;MAP / Retail Pricing</b>	<b>\$3,059 / \$3,449</b>

# B 3000

## Product Overview



Design	B 3312	B 3847
Appliance Color	Lotus White	Lotus White
Iron Color	Black/Grey	Black/Lotus White
Ironing Board Color	Grey	Black
Display	Single Line	Single Line
<b>Perfect Ironing Results</b>		
Chrome-Plated Aluminium Honeycomb Soleplate	•	•
Steam Pressure in Bar	3,5	4,0
Vertical Steam	•	•
Stream Pulse / Continuous Steam	•/•	•/•
Steamer	–	•
Active Ironing Table (Inflation and Suction Function)	•	•
2-Stage Fan / Non-Stick Soleplate	–/•	•/•
<b>Time-Saving Ironing</b>		
Water Container Volume in Gallons	0.33	0.33
Removable Water Container	•	•
Ironing Multi-Layered Items	•	•
<b>User Convenience</b>		
All-in-One / 1-2 Lift System	•/•	•/•
Infinitely Variable Height Adjustment with Gas Pressure Stay	33" – 40"	33" – 40"
Selection of Water Hardness / Automatic Fan Switch-On / Switch-Off	•/•	•/•
Fan Memory Function / Prompted Descaling / Automatic Rinsing	•/•/•	•/•/•
Storage Compartment for Iron / Storage Compartment for Power Cord	•/•	•/•
<b>Safety</b>		
CoolDown Function / AutoOff Function	•/•	•/•
<b>Technical Data</b>		
<b>Entire Machine</b>		
Weight in lbs/Gross Weight (incl.packaging) in lbs	64/73	66/75
Dimensions (folded) (W x H x D)	19" x 50" x 15"	19" x 50" x 15"
Dimensions (set up) (W x H x D)	19" x 38" x 58"	19" x 38" x 58"
Dimensions (packaging) (W x H x D)	54" x 18" x 20"	54" x 18" x 20"
Connection Cable	98"	98"
Hand Iron	•	•
<b>Steamer</b>		
Brush Attachment	–	•
<b>Rated Loads</b>		
Rated Voltage (V)	120	120
Fuse Rating (A)/Rated Load (kW)/ Nominal Rating (W)	15/1,7/1700	15/1,7/1700
<b>Accessories Supplied</b>		
Non-Stick Soleplate/Steamer/Basic Ironing Table Cover	•/–/•	•/•/–
Premium Ironing Table Cover (Particularly Heat Resistant)	–	•
Steam Hose Holder/Mains Connection Cable Holder	•/•	•/•
Test Strips to Test Water Hardness/Descaling Tablets	•/•	•/•
<b>Optional Accessories</b>		
Steamer/Premium Ironing Table Cover/Basic Ironing Table Cover	•/•/•	•/•/•
<b>UMRP&amp;MAP / Retail Pricing</b>	<b>\$1,999 / \$2,199</b>	<b>\$2,499 / \$2,699</b>
<b>Material Number</b>	10526750	10526780

# Miele Cleaning Products

## Cooking and Coffee



### Oven Cleaner - 16.9 fl oz

Material Number: 10162910  
UMRP/MAP: \$12.99  
Retail Pricing: \$12.99



### Ceramic and Stainless Steel Cleaner - 8.5 fl oz

Material Number: 10173130  
UMRP/MAP: \$12.99  
Retail Pricing: \$12.99



### Descaling tablets 6 units

Material Number: 10178350  
UMRP/MAP Price: \$19.99  
Retail Pricing: \$19.99



### Cleaning tablets 10 tabs

Material Number: 11201250  
UMRP/MAP Price: \$19.99  
Retail Pricing: \$19.99



### Cleaning agent for milk pipework 100 packets

Material Number: 10182210  
UMRP/MAP Price: \$39.99  
Retail Pricing: \$39.99



### Silicon grease for percolator unit

Material Number: 05132001  
UMRP/MAP Price: \$11.99  
Retail Pricing: \$11.99



### DGClean

Material Number: 10172760  
UMRP/MAP Price: \$14.99  
Retail Pricing: \$14.99

# Miele Cleaning Products

## Dishwasher



### CC2 Dishwasher Talets - 60 Tabs

Material Number: 11295860  
UMRP/MAP Price: \$29.99  
Retail Pricing: \$29.99

### PowerDisk for G7000 DW (Single)

Material Number: 11346690  
UMRP/MAP Price: \$12.99  
Retail Pricing: \$12.99

### Set PowerDisk for G7000 DW (6 Units)

Material Number: 11346700  
UMRP/MAP Price: \$69.99  
Retail Pricing: \$69.99



### CC2 Dishwasher Salt

Material Number: 10248600  
UMRP/MAP Price: \$12.99  
Retail Pricing: \$12.99

### CC2 Rinse Aid

Material Number: 10198910  
UMRP/MAP Price: \$10.99  
Retail Pricing: \$10.99

### Dishwasher Conditioner

Material Number: 09959340  
UMRP/MAP Price: \$12.99  
Retail Pricing: \$12.99



### CC2 Dishwasher Freshener

Material Number: 10118510  
UMRP/MAP Price: \$9.99  
Retail Pricing: \$9.99

# Miele Cleaning Products

## Laundry



### UltraWhite Powder - 5.5 lbs, 48 loads

Material Number: 10459720  
UMRP/MAP Price: \$29.99  
Retail Pricing: \$29.99



### UltraColor Powder - 4 lbs, 48 loads

Material Number: 10459790  
UMRP/MAP Price: \$29.99  
Retail Pricing: \$29.99



### UltraColor Liquid - 2 L, 33 loads

Material Number: 10223700  
UMRP/MAP Price: \$19.99  
Retail Pricing: \$19.99



### Sensitive Skin Powder - 5.5 lbs, 48 loads

Material Number: 10459870  
UMRP/MAP Price: \$29.99  
Retail Pricing: \$29.99



### WoolCare - 1.5 L, 37 loads

Material Number: 11517950  
UMRP/MAP Price: \$24.99  
Retail Pricing: \$24.99



### Fabric Softener - 1.5 L, 50 loads

Material Number: 11518280  
UMRP/MAP Price: \$12.99  
Retail Pricing: \$12.99



### Down Detergent - 250 ml, 13 loads

Material Number: 10225720  
UMRP/MAP Price: \$19.99  
Retail Pricing: \$19.99



### Sportswear Detergent - 250 ml, 13 loads

Material Number: 10225930  
UMRP/MAP Price: \$19.99  
Retail Pricing: \$19.99



### Outdoor Detergent - 250 ml, 13 loads

Material Number: 10226470  
UMRP/MAP Price: \$19.99  
Retail Pricing: \$19.99

# Miele Cleaning Products

## Laundry



### **Fabric Protector - 250 ml, 4 loads**

Material Number: 10240630  
UMRP/MAP Price: \$19.99  
Retail Pricing: \$19.99



### **Descaler for Washing Machines and Dishwashers**

Material Number: 10130990  
UMRP/MAP Price: \$12.99  
Retail Pricing: \$12.99



# Miele Cleaning Products

## Laundry (W1)



### Ultraphase 1

Material Number: 11504560  
UMRP/MAP: \$19.99  
Retail Pricing: \$19.99



### Ultraphase 2

Material Number: 10803750  
UMRP/MAP: \$19.99  
Retail Pricing: \$19.99



### Ultraphase Set

Material Number: 11504740  
UMRP/MAP: \$94.99  
Retail Pricing: \$94.99



### Ultraphase 1 Sensitive

Material Number: 10923660  
UMRP/MAP: \$22.99  
Retail Pricing: \$22.99



### Ultraphase 2 Sensitive

Material Number: 10923680  
UMRP/MAP: \$22.99  
Retail Pricing: \$22.99



### TwinDosCare

Material Number: 11171450  
UMRP/MAP: \$15.99  
Retail Pricing: \$15.99



### Woolcare Capsules

Material Number: 10755570  
UMRP/MAP: \$9.99  
Retail Pricing: \$9.99



### UltraDark Capsules

Material Number: 10755680  
UMRP/MAP: \$9.99  
Retail Pricing: \$9.99



### Aqua Capsules

Material Number: 10755290  
UMRP/MAP: \$8.99  
Retail Pricing: \$8.99

# Miele Cleaning Products

## Laundry (W1)



### Cocoon Capsules

Material Number: 10755520  
UMRP/MAP: \$8.99  
Retail Pricing: \$8.99



### Nature Capsules

Material Number: 10755460  
UMRP/MAP: \$8.99  
Retail Pricing: \$8.99



### Sport Capsules

Material Number: 10756450  
UMRP/MAP: \$9.99  
Retail Pricing: \$9.99



### Booster Capsules

Material Number: 10755980  
UMRP/MAP: \$9.99  
Retail Pricing: \$9.99



### DownCare Capsules

Material Number: 10756370  
UMRP/MAP: \$9.99  
Retail Pricing: \$9.99



### Outdoor Capsules

Material Number: 10757030  
UMRP/MAP: \$9.99  
Retail Pricing: \$9.99



### ImpraProtect Capsules

Material Number: 10757720  
UMRP/MAP: \$19.99  
Retail Pricing: \$19.99



### SilkCare Capsules

Material Number: 10756190  
UMRP/MAP: \$9.99  
Retail Pricing: \$9.99



### CottonRepair Capsules

Material Number: 10757450  
UMRP/MAP: \$19.99  
Retail Pricing: \$19.99

# Miele Cleaning Products

## Laundry (T1)



### Aqua Pods

Material Number: 10813390  
UMRP/MAP: \$14.99  
Retail Pricing: \$14.99

### Cocoon Pods

Material Number: 10813430  
UMRP/MAP: \$14.99  
Retail Pricing: \$14.99

### Nature Pods

Material Number: 10813410  
UMRP/MAP: \$14.99  
Retail Pricing: \$14.99



Miele, Inc.  
9 Independence Way  
Princeton, NJ 08540

[mieleusa.com](http://mieleusa.com)  
[moreinfo@mieleusa.com](mailto:moreinfo@mieleusa.com)

800.843.7231

Visit one of Miele's Experience Centers:

Beverly Hills  
Boca Raton  
Chicago  
Coral Gables  
Manhattan  
Princeton  
San Francisco  
Scottsdale  
Seattle  
Tysons Corner