



nere are none

The most innovative dishwasher we have ever built.

The Miele G 7000 Dishwashers dispense automatically and start by themselves.

Having the time and freedom to do the things that matter to you the most is more important than ever. With Miele, you'll experience expanded flexibility - leaving the 'work' to your dishwasher. Thanks to AutoDos with integrated PowerDisk®and AutoStart technology, perfect results are achieved...automatically!



Smart Solutions

Enjoy helpful functions designed to make your life easier:

I AutoStart: Use the Miele@mobile app to automatically start your dishwasher at pre-determined times.

I MobileControl: Simply start your G 7000 Dishwasher using the free Miele@mobile app – from anywhere at any time.

I ShopConn@ct: Order detergent such as PowerDisks® with the Miele@mobile app with only a few clicks.

FlexLine Baskets

The new G 7000 FlexLine Dishwasher Baskets offer incredible flexibility for loading and cleaning all kinds of dishware and utensils perfectly. One of many examples: with movable sections, the 3D MultiFlex Tray makes space where there wasn't any before.







G 7000 Dishwashers can do what no conventional dishwasher can. With the AutoDos cleaning system,
Miele has developed a true innovation. The integrated
PowerDisk® automatically dispenses the correct amount of detergent in accordance with the selected program and degree of soiling. The perfect interaction between cleaning, drying, and gentle handling – that's what it takes to achieve optimum results.



The PowerDisk®

The PowerDisk* revolutionizes dishwashing. It turns several times to ensure that the ideal quantity of powder detergent is always dispensed in accordance with the selected program and the degree of soiling.

Particularly practical: the contents of one PowerDisk* **last for** approximately **one month** – around 20 cycles*.



The detergent

A special dishwasher deserves special detergent. Here too, Miele thought ahead and developed a powder detergent that precisely complements the G 7000 Dishwashers, each enabling the other to work to their full potential.

You can also enjoy maximum user convenience – either using the automatic AutoDos dispensing system or dispensing tabs (or powder) via the standard dispenser.




The result

Thanks to the innovative AutoDos cleaning system with PowerDisk* you can achieve outstanding results. Whether cleaning, drying, or gently treating your dishware – the performance of the new G 7000 Dishwashers meets the highest of ctandards.

All this whilst ensuring maximum flexibility and convenience.

* based on avererage household use.







AutoStart

With the new AutoStart feature and the Miele@mobile app you can set G 7000 Dishwashers to automatically start at one or several pre-determined times. Thanks to AutoDos with integrated PowerDisk® there is always detergent available so the appliance can get to work completely autonomously. Starting it manually is no longer required. And running out of clean dishware because you forgot to press the start button is now a thing of the past.



MobileControl

Monitor, start, and control your G 7000 Dishwasher conveniently with your smartphone or tablet from wherever you are at the moment. With the free Miele@mobile app you can keep an eye on the fill level of the PowerDisk® or the time remaining on your current program.



ShopConn@ct

You no longer have to remember to buy detergent. The free Miele@mobile app makes it easy for you to order new PowerDisks* and have them conveniently delivered to your home.

New space to improve cleaning results.

The new FlexLine Baskets open up previously unimagined possibilities.

The new G 7000 Dishwashers create new space for perfect cleaning.

The right-hand section of the new 3D MultiFlex Tray can be lowered to accommodate small items such as espresso cups and shallow bowls. And the left-hand section can be moved to provide space for long-stem glasses in the upper basket. Split rows of hinged spikes in the upper basket allow bowls to be perfectly positioned with optimum spacing. In combination with the innovative AutoDos system, this achieves better results than ever before.

FlexLine Baskets New

FlexCare



3D MultiFlex Tray

Experience unique flexibility for perfect utensil and dishware care. The height, width, and depth of the tray are adjustable to suit any type of load. The height-adjustable side section ensures that you can easily position small items too. And a movable side section even enables you to position long-stem glasses in the upper basket.

Glass Holders and Cup Racks

The FlexCare Glass Holders and Cup Racks have been redesigned for greater flexibility and convenience. The FlexCare Glass Holders in the lower basket are ideal for long-stem glasses and now feature a MultiClip – perfect for accommodating light plastic items. A completely new feature is the FlexCare Cup Rack in the upper basket – ideal for cups as well as for long-stem glasses.

Flexible Upper Basket Configuration

The upper basket has been equipped with split-hinged rows of spikes. Allowing you to adapt the space to meet your individual needs. Ensuring optimal cleaning and drying results.





G 7000 Dishwashers

Product Overview







Model number	G 7106 SCU	G 7156 SCVi	G 7156 SCVi SF
Design Overview			
Width	24"	24"	24"
Pre-finished - (Clean Touch Steel™)	•	-	-
Integrated - (Clean Touch Steel™ and Black Controls)	_	-	-
Fully integrated - (Clean Touch Steel™ Panel and Handle)			•
Fully integrated - (Custom Panel and Handle Ready)		•	
Control Panel			
Control Panel location	Front	Тор	Тор
DirectSelect	•	•	•
DirectSensor		-	_
M Touch Vi	<u> </u>	<u> </u>	<u> </u>
M Touch S			
Programs			
Number of Wash Programs	7	7	. 7
Options			
Express / IntenseZone / AutoDos	●/●/-	●/●/-	●/●/-
ExtraClean / ExtraDry	•/•	●/●	●/●
Basket Design			
Lower	ExtraComfort	ExtraComfort	ExtraComfort
Upper	ExtraComfort	ExtraComfort	ExtraComfort
Cutlery			
3D MultiFlex tray	•		<u>•</u>
Other Features			
Water Softener		•	•
BrilliantLight	<u> </u>		<u> </u>
WifiConn@ct	<u> </u>		_
Knock2open	<u> </u>		
AutoStart function	<u> </u>		<u> </u>
ADA Compliant	_	-	-

G 7000 Dishwashers

Product Overview







Model number	G 7316 SCU	G 7366 SCVi	G 7366 SCVi SF
Design Overview			
Width	24"	24"	24"
Pre-finished - (Clean Touch Steel™)	•	_	_
Integrated - (Clean Touch Steel™ and Black Controls)	_	_	_
Fully integrated - (Clean Touch Steel™ Panel and Handle)	_	_	•
Fully integrated - (Custom Panel and Handle Ready)		•	
Control Panel			
Control Panel location	Front	Тор	Тор
DirectSelect	-	-	_
DirectSensor	•	•	•
M Touch Vi	-	-	_
M Touch S			_
Programs			
Number of Wash Programs	9	9	9
Options			
Express / IntenseZone / AutoDos	●/●/●	●/●/●	●/●/●
ExtraClean / ExtraDry	●/●	●/●	●/●
Basket Design			
Lower	ExtraComfort	ExtraComfort	ExtraComfort
Upper	ExtraComfort	ExtraComfort	ExtraComfort
Cutlery			
3D MultiFlex tray	•	•	•
Other Features			
Water Softener	•	•	•
BrilliantLight	_	-	_
WifiConn@ct	•	•	•
Knock2open		-	-
AutoStart function	•	•	•
ADA Compliant			_

G 7000 Dishwashers

Product Overview







Model number	G 7516 SCi	G 7566 SCVi	G 7566 SCVi SF
Design Overview			
Width	24"	24"	24"
Pre-finished - (Clean Touch Steel™)	_	_	_
Integrated - (Clean Touch Steel™ and Black Controls)	•	-	-
Fully integrated - (Clean Touch Steel™ Panel and Handle)			•
Fully integrated - (Custom Panel and Handle Ready)	_	•	_
Control Panel			
Control Panel location	Front	Тор	Тор
DirectSelect	_	_	-
DirectSensor	•	•	•
M Touch Vi	<u> </u>		
M Touch S			<u> </u>
Programs			
Number of Wash Programs	12	12	12
Options			
Express / IntenseZone / AutoDos	●/●/●	●/●/●	●/●/●
ExtraClean / ExtraDry	●/●	●/●	●/●
Basket Design			
Lower	MaxiComfort	MaxiComfort	MaxiComfort
Upper	MaxiComfort	MaxiComfort	MaxiComfort
Cutlery			
3D MultiFlex tray	<u> </u>	<u> </u>	
Other Features			
Water Softener	•	•	•
BrilliantLight		•	•
WifiConn@ct	<u> </u>	•	•
Knock2open		_	_
AutoStart function	<u> </u>	<u>•</u>	•
ADA Compliant	_	_	_

G 7000 Dishwashers

Product Overview





Model number	G 7591 SCVi K2O	G 7596 SCVi K2O
Design Overview		
Width	24"	24"
Pre-finished - (Clean Touch Steel™)	_	_
Integrated - (Clean Touch Steel™ and Black Controls)	-	-
Fully integrated - (Clean Touch Steel™ Panel and Handle)	-	_
Fully integrated - (Custom Panel and Handle Ready)	•	•
Control Panel		
Control Panel location	Тор	Тор
DirectSelect	_	_
DirectSensor	•	•
M Touch Vi		
M Touch S	_	_
Programs		
Number of Wash Programs	12	12
Options		
Express / IntenseZone / AutoDos	•/•/•	●/●/●
ExtraClean / ExtraDry	•/•	•/•
Basket Design		
Lower	MaxiComfort	MaxiComfort
Upper	MaxiComfort	MaxiComfort
Cutlery		
3D MultiFlex tray	<u> </u>	•
Other Features		
Water Softener		•
BrilliantLight	<u> </u>	•
WifiConn@ct	<u> </u>	•
Knock2open	•	•
AutoStart function	<u>•</u>	•
ADA Compliant	•	_

G 7000 Dishwashers

Product Overview





Model number	G 7916 SCi	G 7966 SCVi K2O
Design Overview		
Width	24"	24"
Pre-finished - (Clean Touch Steel™)	_	-
Integrated - (Clean Touch Steel™ and Black Controls)	•	-
Fully integrated - (Clean Touch Steel™ Panel and Handle)	_	-
Fully integrated - (Custom Panel and Handle Ready)		•
Control Panel		
Control Panel location	Front	Тор
DirectSelect	_	-
DirectSensor		_
M Touch Vi		
M Touch S	•	_
Programs		
Number of Wash Programs	_ 12	_ 12
Options		
Express / IntenseZone / AutoDos	●/●/●	●/●/●
ExtraClean / ExtraDry	●/●	●/●
Basket Design		
Lower	MaxiComfort	MaxiComfort
Upper	MaxiComfort	MaxiComfort
Cutlery		
3D MultiFlex tray		
Other Features		
Water Softener		•
BrilliantLight		•
WifiConn@ct		•
Knock2open		•
AutoStart function	<u>•</u>	<u>•</u>
ADA Compliant	_	-



