

Generation 6000

Model Comparison Overview 2020



ContourLine in Clean Touch Steel™



PureLine in Obsidian Black



PureLine in Clean Touch Steel™



PureLine in Graphite Grey



PureLine in Brilliant White


Generation 6000 — Design Options


DESIGN OPTIONS					
ContourLine Clean Touch Steel™	PureLine Clean Touch Steel™	PureLine Graphite Grey	PureLine Brilliant White	PureLine Obsidian Black	
					
					
					SensorTronic
					DirectSelect



Generation 6000 — Trim Kits

TRIM KITS					
ContourLine Clean Touch Steel™	ContourLine Clean Touch Steel™	PureLine Clean Touch Steel™	PureLine Graphite Grey	PureLine Brilliant White	PureLine Obsidian Black
OPTIONAL USE					
24" Convection Oven	24" Convection Oven + 24" DGC XXL (H 6x60 B & BP, DGC 6x6x XXL)				
					
27" Trim Kit EBA 6767 09632220	30" Trim Kit EBA 6768-USA 10706070	30" Trim Kit EBA 6868-USA 10706090	—	30" Trim Kit EBA 6868-USA 10706150	30" Trim Kit EBA 6868-USA 10706100
OPTIONAL USE					
Steam Oven, Combi-Steam Oven, Speed Oven					
					
27" Trim Kit EBA 6707 10178290	30" Trim Kit EBA 6708 09221320	30" Trim Kit EBA 6808 09221320	30" Trim Kit EBA 6808 10754520	30" Trim Kit EBA 6808 CND 09221330	30" Trim Kit EBA 6808 09863860
OPTIONAL USE					
Microwave Oven, Coffee System					
					
27" Trim Kit EBA 6707 MC 10178300	30" Trim Kit EBA 6708 MC 09767510	30" Trim Kit EBA 6808 MC 09767500	30" Trim Kit EBA 6808 MC 10754520	30" Trim Kit EBA 6808 MC 09767530	30" Trim Kit EBA 6808 MC 09863810

DIRECTSELECT CONTROL PANEL					
					
ContourLine Clean Touch Steel™	PureLine Clean Touch Steel™	PureLine Graphite Grey	PureLine Brilliant White	PureLine Obsidian Black	
PRODUCT					
—	—	—	—	—	24" Convection Oven
—	—	—	—	—	24" Convection Oven (Self Clean)
—	H 6281 BP 10773320	—	—	—	30" Discovery Convection Oven
H 6180 BP 09769420	H 6280 BP 09769440	—	H 6280 BP 09863740	H 6280 BP 09863620	30" Convection Oven
—	—	—	—	—	30" Convection Double Oven
H 6100 BM 09769620	H 6200 BM 09769630	—	H 6200 BM 09862980	H 6200 BM 09862950	24" Speed Oven
—	—	—	—	—	30" Speed Oven
—	—	—	—	—	24" Steam Oven
—	—	—	—	—	24" Combi-Steam Oven XL
—	—	—	—	—	24" Combi-Steam Oven XL (plumbed)
—	—	—	—	—	24" Combi-Steam Oven XXL
—	—	—	—	—	24" Combi-Steam Oven XXL (plumbed)
M 6040 SC 09762410 M 6160 TC 09762450	M 6040 SC 09762410 M 6260 TC 09762430	—	—	—	24" Microwave Oven
CVA 6401 09676900	CVA 6401 09676900	—	CVA 6401 09869070	CVA 6401 09869050	24" Coffee System
CVA 6405 09676910	CVA 6405 09676910	—	—	—	24" Coffee System (plumbed)

SENSORTRONIC CONTROL PANEL					
					
					
ContourLine Clean Touch Steel™	PureLine Clean Touch Steel™	PureLine Graphite Grey	PureLine Brilliant White	PureLine Obsidian Black	
H 6560 B 09769400	—	—	—	—	24" Convection Oven
H 6560 BP 09769410	H 6600 BM 09770690	—	H 6680 BP 09863750	H 6680 BP 09863640	24" Convection Oven (Self Clean)
—	—	—	—	—	30" Discovery Convection Oven
H 6580 BP 09769450	H 6680 BP 09769460	—	H 6680 BP 09863750	H 6680 BP 09863640	30" Convection Oven
—	—	—	—	—	30" Convection Double Oven
H 6500 BM 09770670	H 6600 BM 09770690	—	H 6660 BP 09862880	H 6660 BP 09862850	24" Speed Oven
H 6570 BM 10486200	H 6670 BM 10486330	—	—	—	30" Speed Oven
DG 6500 09682270	DG 6600 09682300	—	—	—	24" Steam Oven
DGC 6500-1 10256670	DGC 6600-1 10256720	—	DGC 6600-1 10256710	DGC 6600-1 10256740	24" Combi-Steam Oven XL
—	—	—	—	—	24" Combi-Steam Oven XL (plumbed)
—	—	—	—	—	24" Combi-Steam Oven XXL
—	—	—	—	—	24" Combi-Steam Oven XXL (plumbed)
—	—	—	—	—	24" Microwave Oven
CVA 6401 09676900	CVA 6401 09676900	—	CVA 6401 09869070	CVA 6401 09869050	24" Coffee System
CVA 6405 09676910	CVA 6405 09676910	—	—	—	24" Coffee System (plumbed)

M TOUCH CONTROL PANEL					
					
					
ContourLine Clean Touch Steel™	PureLine Clean Touch Steel™	PureLine Graphite Grey	PureLine Brilliant White	PureLine Obsidian Black	
					PRODUCT
—	—	—	—	—	24" Convection Oven
—	—	—	—	—	24" Convection Oven (Self Clean)
—	—	—	—	—	30" Discovery Convection Oven
H 6780-2 BP 10751970	H 6880-2 BP 10752160	H 6880-2 BP 10904390	H 6880-2 BP 10752070	H 6880-2 BP 10752150	30" Convection Oven
H 6780-2 BP2 10751980	H 6880-2 BP2 10752010	—	—	H 6880-2 BP2 10752020	30" Convection Double Oven
H 6700 BM 09769640	H 6800 BM 09769650	H 6800 BM 10754800	H 6800 BM 09660040	H 6800 BM 09863020	24" Speed Oven
H 6700 BM 09769640	H 6870 BM 10486340	H 6870 BM 10754770	H 6870 BM 10486350	H 6870 BM 10486360	30" Speed Oven
—	—	—	—	—	24" Steam Oven
DGC 6700-1 10256750	DGC 6800-1 10256780	DGC 6800-1 10753960	DGC 6800-1 10256770	DGC 6800-1 10256800	24" Combi-Steam Oven XL
DGC 6705-1 10256760	DGC 6805-1 10256810	—	—	—	24" Combi-Steam Oven XL (plumbed)
DGC 6760 10265740	DGC 6860 10220980	—	DGC 6860 10221000	DGC 6860 10221010	24" Combi-Steam Oven XXL
DGC 6765 10265750	DGC 6865 10221030	—	DGC 6865 10221050	DGC 6865 10221060	24" Combi-Steam Oven XXL (plumbed)
—	—	—	—	—	24" Microwave Oven
CVA 6800 09676920	CVA 6800 09676920	—	—	—	24" Coffee System
CVA 6805 09676930	CVA 6805 09676930	CVA 6805 10735650	CVA 6805 09676950	CVA 6805 09869100	24" Coffee System (plumbed)

WARMING DRAWER COMPARISON					
 ESW 6114 - 24"	 ESW 6114 - 24"	 ESW 6214 GRGR - 24"	 ESW 6214 BRWS - 24"	 ESW 6214 OBSW - 24"	
 ESW 6214 - 24"	 ESW 6214 - 24"				
 ESW 6580 - 30"					FASCIA PANEL Width 30" (757 mm) Height 10 ¹³ / ₁₆ " (275 mm)
 ESW 6780 - 30"	 ESW 6880 - 30"	 ESW 6880 GRGR - 30"	 ESW 6880 BRWS - 30"	 ESW 6880 OBSW - 30"	
 ESW 6585 - 30"	 ESW 6885 - 30"	 ESW 6885 GRGR - 30"	 ESW 6885 BRWS - 30"	 ESW 6885 OBSW - 30"	FASCIA PANEL Width 30" (757 mm) Height 9 ³ / ₁₆ " (234 mm)
ContourLine Clean Touch Steel™	PureLine Clean Touch Steel™	PureLine Graphite Grey	PureLine Brilliant White	PureLine Obsidian Black	
ESW 6114 09682550	ESW 6114 09682550	—	—	—	24" Warming Drawer
ESW 6214 9682560	ESW 6214 9682560	ESW 6214 10754040	ESW 6214 09739970	ESW 6214 10034510	24" Warming Drawer
ESW 6580 09685080	—	—	—	—	30" Warming Drawer
ESW 6780 09685110	ESW 6880 09685120	ESW 6880 10754210	ESW 6880 09714250	ESW 6880 10034540	30" Warming Drawer
ESW 6585 10653740	ESW 6885 10653750	ESW 6885 10754230	ESW 6885 10653770	ESW 6885 10653760	30" Warming Drawer
ESW 6380 FB Custom Panel 9685060					30" FB Warming Drawer

VACUUM SEALING DRAWER					
 ContourLine Clean Touch Steel™	 PureLine Clean Touch Steel™				
		PureLine Graphite Grey	PureLine Brilliant White	PureLine Obsidian Black	
EVS 6114 10683060	EVS 6114 10683060	—	—	—	24" Vacuum Sealing Drawer

HANDLES

Clean Touch Steel™	Clean Touch Steel™	Clean Touch Steel™/Grey	Chrome/Brilliant White	Clean Touch Steel™/Black
Comfort Handle	ComfortSwivel Handle	Silhouette Handles		
				
DS6708 EDST 09828380	DS 6718 EDST/SWIVELING 09828390	DS 6808 EDST 09828400	DS 6808 CHROM 09828410	DS 6808 FR NA KD 09615950

SIGNATURE HANDLES

Brilliant White	Obsidian Black	Brilliant White	Obsidian Black
Classic Handles		Gold Handles	
			
DS 6808 BRWS 10083290	DS 6808 OBSW 10083280	DS 6808 GOLD BRWS 0083330	DS 6808 GOLD OBSW 10083320

Nature Handles		Vitro Handles	
	—		
DS 6808 NATURE BRWS 10083360	—	DS 6808 VITRO BRWS 10083390	DS 6808 VITRO OBSW Obsidian Black