

**Miele**

# Miele Dishwashers

## Model Comparison

### Overview 2022



DISCOVER MORE.  
NO APP REQUIRED.

# INTEGRATION OPTIONS

---

Choose the right model for you and your home. Miele offers the ultimate in convenience and seamless design integration.

## Pre-Finished (“U”) Models

Pre-finished models are complete with control and door panel. Generally, these models are available in Clean Touch Steel™.



## Semi Integrated (“i”) Models

Integrated dishwashers have a visible control panel and are designed to fit with a custom door panel that reflects the cabinetry decor of your kitchen. Alternatively, Miele offers Clean Touch Steel™ panels for a more professional look.



## Fully Integrated (“Vi”) Models

These units can either disappear into your cabinetry by adding a custom front panel or stand out as a robust appliance with a full Clean Touch Steel™ panel. The elegant stainless steel or black glass control panel is integrated on top of the door and is only visible when the door is ajar.



## Fully Integrated (“SF”) Models

For convenience, Miele offers fully integrated, pre-finished models that are already equipped with a Clean Touch Steel™ door panel, a 4-inch and 6-inch toe-kick and either a straight door handle or a pocket handle.



# CLEAN TOUCH STEEL™ DISHWASHER PANELS

		<i>SlimLine</i>	<i>G 5000 and 7000</i>
	<i>Semi Integrated</i>		<p>Material number: 10986720 (Full Size) Description: GFV 60/60 -7 6" toekick</p> <p>Material number: 10986730 (Full Size) Description: GFV 60/65 -7 4" toekick</p>
	<i>Fully Integrated (4")</i>	<p>Material number: 11573740 (Slimline) Description: GFVi 453/77 - 7 4" toekick / no handle</p>	<p>Material number: 10986750 (Full Size) Description: GFVi 701/77 4" toekick / no handle</p> <p>Material number: 12074350 (Full Size) Description: GFVi 710/77 4" toekick / GEN7 PureLine Handle</p> <p>Material number: 12074450 (Full Size) Description: GFVi 711/77 4" toekick / GEN7 ContourLine Handle</p> <p>Material number: 12074470 (Full Size) Description: GFVi 712/77 4" toekick / Range Panel (GEN7 handle)</p> <p>Material number: 11750840 (Full Size) Description: GFVi 709/77 4" toekick / Pocket handle</p>
	<i>Fully Integrated (6")</i>	<p>Material number: 11526970 (Slimline) Description: GFVi 453/72 - 7 6" toekick / no handle</p>	<p>Material number: 10986740 (Full Size) Description: GFVi 701/72 6" toekick / no handle</p> <p>Material number: 12074400 (Full Size) Description: GFVi 711/72 6" toekick / GEN7 ContourLine handle</p>

# PRE-FINISHED MODELS



	<b>PRE-FINISHED</b>		
	24"	24"	24"
Clean Touch Steel™	G 5006 SCU 11636690	G 7106 SCU 11387580	G 7316 SCU 11388020

<b>DESIGN</b>			
Controls	DirectSelect	DirectSelect	DirectSensor
Handle Type	Integrated handle	Integrated handle	Integrated handle
Cutlery Tray	Original	3D MultiFlex	3D MultiFlex

<b>FEATURES</b>			
Water Softener		•	•
Miele@Mobile			•
AutoOpen Drying		•	•
AutoDos			•
BrilliantLight			

<b>PROGRAMS</b>			
Normal	•	•	•
QuickIntenseWash	•	•	•
Pots & Pans	•	•	•
SaniWash	•	•	•
Rinse & Hold	•	•	•
China & Crystal		•	•
Extra Quiet			•
Filters			•
Clean Machine			•
Economy			
Energy Saver			
Tall Items			
Glass - No Rinse Aid			
Sensor Wash			

<b>OPTIONS</b>			
Delay Start	•	•	•
Express	•	•	•
FlexiTimer			•
IntenseZone		•	•
ExtraDry	•	•	•
ExtraClean	•	•	•

# SEMI INTEGRATED (i) MODELS



<b>SEMI INTEGRATED</b>		
	24"	24"
Custom Panel Ready	G 7516 SCi 11388120	G 7916 SCi 11388290

<b>DESIGN</b>		
Controls	DirectSensor	M Touch S
Handle Type	Integrated handle	Integrated handle
Cutlery Tray	3D MultiFlex	3D MultiFlex

<b>FEATURES</b>		
Water Softener	•	•
Miele@Mobile	•	•
AutoOpen Drying	•	•
AutoDos	•	•
BrilliantLight	•	•

<b>PROGRAMS</b>		
Normal	•	•
QuickIntenseWash	•	•
Pots & Pans	•	•
SaniWash	•	•
Rinse & Hold	•	•
China & Crystal	•	•
Extra Quiet	•	•
Filters	•	•
Clean Machine	•	•
Economy	•	•
Energy Saver	•	•
Tall Items		•
Glass - No Rinse Aid		•
Sensor Wash	•	•

<b>OPTIONS</b>		
Delay Start	•	•
Express	•	•
FlexiTimer	•	•
IntenseZone	•	•
ExtraDry	•	•
ExtraClean	•	•

# FULLY INTEGRATED (SF) MODELS



## FULLY INTEGRATED (SF)

	24"	24"	24"	24"	24"
Clean Touch Steel™ with Handle	G 5056 SCVi SF 11695330	G 5266 SCVi SF 11636750	G 7156 SCVi SF 12055090	G 7366 SCVi SF 12055100	G 7566 SCVi SF 12055110
Clean Touch Steel™ with Pocket Handle	G 5056 SCVi SFP 11636730	G 5266 SCVi SFP 11695340			

## DESIGN

Controls	DirectSelect	DirectSelect	DirectSelect	DirectSensor	DirectSensor
Handle Type	PureLine	PureLine	GEN7 ContourLine	GEN7 ContourLine	GEN7 ContourLine
	Pocket Handle	Pocket Handle			
Cutlery Tray	Original	3D MultiFlex	3D MultiFlex	3D MultiFlex	3D MultiFlex

## FEATURES

Water Softener		•	•	•	•
Miele@Mobile				•	•
AutoOpen Drying		•	•	•	•
AutoDos				•	•
BrilliantLight					•

## PROGRAMS

Normal	•	•	•	•	•
QuickIntenseWash	•	•	•	•	•
Pots & Pans	•	•	•	•	•
SaniWash	•	•	•	•	•
Rinse & Hold	•	•	•	•	•
China & Crystal			•	•	•
Extra Quiet				•	•
Filters				•	•
Clean Machine				•	•
Economy					•
Energy Saver					•
Tall Items					
Glass - No Rinse Aid					
Sensor Wash					•

## OPTIONS

Delay Start	•	•	•	•	•
Express	•	•	•	•	•
FlexiTimer				•	•
IntenseZone			•	•	•
ExtraDry	•	•	•	•	•
ExtraClean	•	•	•	•	•



## HIGHLIGHTS\*



### AutoDos

AutoDos with integrated PowerDisk®, automatically dispenses the correct amount of detergent in accordance with the selected program and degree of soiling.



### Clean Touch Steel™

This innovative finish resists fingerprints, scratches and smudges. A special treatment stands up to aggressive handling – keeping the exterior cleaner and easier to maintain.



### AutoStart

No matter where you are, use the Miele@mobile app to automatically start your dishwasher at pre-determined times.



### FlexLine Baskets

These baskets offer incredible flexibility for loading and cleaning all kinds of dishware and utensils.



### WifiConn@ct

For your convenience, use your WiFi to remotely operate and monitor your dishwasher at any time.



### MultiFlex Cutlery Tray

With movable sections, the 3D MultiFlex Tray makes space where there wasn't any before.



### Knock2Open

Our dishwashers can be perfectly integrated into handleless kitchens – the door opens automatically by tapping twice.



### ExtraQuiet

This program reduces the sound emissions of the dishwasher cycle to whisper quiet levels.



### M Touch S/VI

M Touch controls are both easy-to-operate and navigate. An intuitive swipe of the screen will quickly lead you to your desired selection.



### BrilliantLight

4 powerful LED lights illuminate the dishwasher from the inside out – creating a crystal clear appearance.



### QuickIntenseWash

Excellent cleaning and drying results for normally soiled dishware in 58 minutes.



### SaniWash

When hygiene is especially important, this program offers temperatures high enough to remove germs from baby bottles, chopping boards, utensils, etc.

\*Highlights depend on model.